

Box set of hexagonal nuts **DIN934**

Steel

BOX-SHNA

- Boxes of standard DIN934 nuts DIN934
- Chromed steel

Application

- Ideal for the maintenance department



- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M3	0,50
100	M4	0,70
100	M5	0,80
100	M6	1,00
100	M8	1,25
50	M10	1,50
50	M12	1,75
25	M14	2,00
20	M16	2,00
10	M18	2,50
10	M20	2,50
5	M24	3,00

DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Quantity per box	Price each
BOX-SHNA	670 washers	69,17 €

Fax 0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

209

Our other products



ACL-APB
Closing system,
Magnetic door stop



GG2
Ground spur gear,
Heat treated steel



PFC
Fixed foot, Levelling
support for small
parts



RURt
Wheel pivoting with
central hole,
Polyurethane -
Aluminium rim (Free




R206
Extra-thick die spring,
Extra-heavy



M0
Wheel, Bronze



DG1
Double spur gear,
Steel 20NCD2



B
Bevel gear - Steel
60C40, 1:1



T2
Synchronous pulley,
T2.5 moulded plastic
(nylon)



PPG
Indexing plunger,
With horizontal
mounting flange



GE32
Sprung toggle latch
with connecting link,
Standard



DOMI120
DOMILINE -
Accessories, Turntable

Complementary products



SHN
Six-sided nut - DIN
934, Steel (Class 6|8)



BOX-NINA
Self locking nut - DIN
985, Box set of steel
nuts



BOX-WM
Washer - DIN 125,
Box set of steel
washers