

Boxed set of cylindrical dowel pins **DIN6325**

Steel dowel pins

BOXDH

- Steel pins conforming to DIN6325


Applications

- Ideal for maintenance or workshop applications



Box contents

Quantity	ØD	L
100	2	10
50	2	32
100	3	10
50	3	20
100	4	10
30	4	24
50	5	12
40	5	24
30	5	36
50	6	10
40	6	16
30	6	20
25	6	30
20	6	40
30	8	20
20	8	40
20	10	24
10	10	40
10	12	40



✓ INCREASED STOCK

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Quantity per box	Stock*	Price each
BOX-DH	805 pieces	✓	128,45 €

*Depending on availability - Dimensions in mm

Our other products



VML
Stainless steel
hexagonal headed
thumb screw, Male



PSG15
Spur gear - precision
range, Stainless steel
316



KITdog
24V DC motorisation
kit, Worm and wheel



CHAK
Hi-Klik™ indent
hinge, Hi-Klik™ -
Detent hinge



ZDB
Machined plastic
bevel gear, 2:1



CHAE3030PA
Square decorative
screwed hinges,
Polyamide



NPTF20
Fixed tube carrier,
Fixed Ø10 to Ø14



MEP
Revolving handle for
handwheel, Fixed



VLBS
Folding lifting ring for
welding, Folding - for



CHML63
Worm and wheel gear
reducer, up to 138



DIV_SS
Stainless steel locking
bolt, With grip -



UGPC
Actuator guide kit,
Short bearing

Complementary products



DH
Dowel pin, Solid DIN
6325