

# Pressed stainless steel bearing for light loads

2 mounting holes


BPPSS

- Pressed sheet steel housing
- Material: stainless steel

## Application

- Mounting a simple bearing, suitable for light loads only

**NEW:**  
stainless steel  
range



## DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	H	A	E	B	S	G	W	Bolt size	B1	N	Weight (kg)	Stock*	Price each 1 to 5
BPP204/SS	20	25,4	98	76	32	9	3,2	50	M8	25	7	0,22	✓	18,10 €
BPP205/SS	25	28,6	108	86	32	11	4	56	M10	27	7,5	0,29	✓	24,19 €
BPP206/SS	30	33,3	117	95	38	11	4	66	M10	30	8	0,43	✓	27,74 €
BPP207/SS	35	39,7	129	106	42	11	5	78	M10	32	8,5	0,63	-	52,39 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

**HPC** SUPPLEMENT 2019

99

## Our other products



CHA135  
Screwed hinge, 135 degrees



RPCpl  
Fixed castor with plate, Steel - Polyamide



ACLEPP  
Right angled bracket for aluminium profile, 8 holes



H0  
Crossed helical gear crossed axis at 90°, Steel 20NCD2




RURt  
Swivel castor with central hole, Polyurethane - Aluminium rim (Free



BFM2  
Flanged bronze nut, Bronze - 2 threads



RAGFLOW  
Floway2® roller track, Roller track



LVTMFC  
Device for controlling limit switches, For mini-actuator LVT



AT10-32ECO  
AT type timing pulley, Economy range - AT10 aluminium



M0  
Worm and wheel set, Unhardened steel



BOXsap  
Boxed set of spring pins ISO8752, Boxed set - Split ISO 8752



CHAK  
Hi-Klik™ indent hinge, Hi-Klik™ - Detent hinge

## Complementary products



BPFss  
Pressed stainless steel flange bearing, Stainless steel



BPF Lss  
Pressed stainless steel flange bearing, Stainless steel



BPP  
Pressed steel flanged bearing for light loads, Sheet steel



UCP\_SS  
Stainless steel pillow block bearing, Stainless steel