

End cap for round tube

Stock Pla

BPTR

Black plastic

- Material: black technopolymer

Info.

- Dimensions are given as a guide and are subject to change
- Not sold individually, please contact us for details



DISCOUNTS


Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	External tube Ø	Tube thickness	Stock*	Price each 1 to 59
BPTR-10	10	1-2	✓	0,16 €
BPTR-12	12	1-2	✓	0,16 €
BPTR-13	13	1-2	-	0,16 €
BPTR-14	14	1-2	✓	0,20 €
BPTR-15	15	1-2	✓	0,31 €
BPTR-16	16	1-2	✓	0,20 €
BPTR-18	18	1-2	✓	0,25 €
BPTR-19	19	1-2	-	0,20 €
BPTR-20	20	1-2	✓	0,25 €
BPTR-21	21	1-2	✓	0,25 €
BPTR-22	22	1-2	✓	0,25 €
BPTR-23	23	1-2,5	-	0,25 €
BPTR-25	25	1-3	✓	0,31 €
BPTR-27	27	1-3	✓	0,40 €
BPTR-28	28	1-2	✓	0,40 €
BPTR-30	30	1-2	✓	0,48 €
BPTR-32	32	1-2	✓	0,59 €
BPTR-34	34	1-3	✓	0,65 €
BPTR-35	35	1-2	-	0,78 €
BPTR-36	36	1-2	✓	0,78 €
BPTR-38	38	1-3,5	✓	0,84 €

Part number	External tube Ø	Tube thickness	Stock*	Price each 1 to 59
BPTR-40	40	1-3	✓	0,95 €
BPTR-42/1-2	42	1-2	✓	1,04 €
BPTR-42/2-4	42	2-4	✓	1,11 €
BPTR-45	45	1-3,5	✓	1,84 €
BPTR-48	48	1,2-3,6	✓	1,84 €
BPTR-50	50	1-2	✓	1,84 €
BPTR-52	52	1,5-3,5	-	2,03 €
BPTR-55	55	1-3	-	2,17 €
BPTR-60/1,5-3	60	1,5-3	✓	2,66 €
BPTR-60/3-4	60	3-4	✓	2,75 €
BPTR-65	65	1,5-3,5	-	On request
BPTR-70	70	2-4,5	-	2,87 €
BPTR-75	75	1-3,5	-	On request
BPTR-76	76	1,6-4	-	3,25 €
BPTR-80	80	1,5-3	-	3,35 €
BPTR-90	90	2,5-5	✓	5,31 €
BPTR-95	95	1,5-4	-	On request
BPTR-100	100	2-4,5	✓	5,83 €
BPTR-102	102	2-4	-	6,05 €
BPTR-105	105	2-4,5	-	On request
BPTR-110	110	2-4,5	-	7,06 €
BPTR-120	120	2-4	-	7,81 €

*Depending on availability - Dimensions in mm

Our other products



CT

Telescopic universal joint, Normal duty



BOX-TOR-B

Box set of Nitrile O-rings in nitrile, 20.38 x 1.78mm to 50.16 x 5.34



NIN

Self-locking nut, A2 Stainless steel



LR

Precision locknut, Precision locknut



S_ZZ

Deep groove ball bearing, Stainless steel



PCS_PA6

Plastic sprocket, 12.7mm (DIN 08B-1)



DOMI30

Accessories, Fixing kit



TBD

Manual leadscrew table with opposing threads, 40kg



UTKswr

Utilitak® V rail, V rail



BLHB30

Right angled gearbox, bored shafts, up to



PAT123

Pressed stainless steel articulating foot



CHALss

Piano hinge, Stainless steel

Complementary products



BTC

End cap for square tube, Standard



BPTR_M

End cap with threaded insert for round tube, With threaded insert