

Spring plunger with internal hexagonal socket

With pressure pin

BSM
BSMP
BSMss

- Three versions to choose from
- Materials:
Body: blackened steel (class 5.8) or stainless steel (303)
Pin: steel, stainless steel or plastic




Steel body and pin



Steel body plastic pin



Stainless steel body and pin



Uses

- Locating
- Retaining

DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+	400+
Disc.	List	-5%	-10%	-15%	-30%	-50%	On request

Part number	ØD	ØD1	L	H	T	T1	N	S	Pressure (N)		Price each 1 to 5	
									F1 initial	F2 final		
Steel body / steel pin												
BSM3	M3	1,0	10	1,5	1,5	1,0	0,4	0,7	0,5	3	✓	9,01 €
BSM4	M4	1,5	15	1,5	2,0	0,6	0,6	1,3	5	16	✓	6,91 €
BSM5	M5	2,4	18	2,3	2,0	0,8	0,8	1,5	6	20	✓	6,73 €
BSM6	M6	2,7	20	2,5	2,5	1,0	1,0	2,0	7	20	✓	6,97 €
BSM8	M8	3,5	22	3,0	3,0	1,4	1,2	2,5	9	35	✓	8,22 €
BSM10	M10	4,0	22	3,0	3,5	1,4	1,6	3,0	9	35	✓	9,20 €
BSM12	M12	6,0	28	4,0	5,0	2,0	2,0	4,0	10	55	✓	12,02 €
BSM16	M16	7,5	32	5,0	6,0	2,5	2,5	5,0	45	100	✓	13,27 €
BSM20	M20	10,0	40	7,0	8,0	3,0	2,5	6,0	60	120	✓	15,70 €
BSM24	M24	12,0	52	10,0	10,0	3,0	2,5	8,0	80	160	-	25,28 €
Steel body / plastic pin												
BSM4P	M4	1,5	15	1,5	2,0	1,0	0,6	1,3	5	16	✓	8,03 €
BSM5P	M5	2,4	18	2,3	2,0	0,6	0,8	1,5	6	20	✓	7,83 €
BSM6P	M6	2,7	20	2,5	2,5	0,8	1,0	2,0	7	20	✓	8,03 €
BSM8P	M8	3,5	22	3,0	3,0	1,0	1,2	2,5	9	35	✓	9,36 €
BSM10P	M10	4,0	22	3,0	3,5	1,4	1,6	3,0	9	35	-	11,20 €
BSM12P	M12	6,0	28	4,0	5,0	1,4	2,0	4,0	10	55	-	14,15 €
BSM16P	M16	7,5	32	5,0	6,0	2,0	2,5	5,0	45	100	-	17,30 €
Stainless steel body / stainless steel pin												
BSM5SS	M5	2,4	18	2,3	2,0	0,8	0,8	1,5	5	17	✓	19,83 €
BSM6SS	M6	2,7	20	2,5	2,5	1,0	1,0	2,0	6	17	✓	19,78 €
BSM8SS	M8	3,5	22	3,0	3,0	1,4	1,2	2,5	7	29	✓	22,03 €
BSM10SS	M10	4,0	22	3,0	3,5	1,4	1,6	3,0	8	31	✓	30,06 €
BSM12SS	M12	6,0	28	4,0	5,0	2,0	2,0	4,0	10	47	✓	40,70 €

*Depending on availability - Dimensions in mm

Our other products



CLG2

Spur gear, Moulded plastic (nylon)



BPFL

Flange bearing, Sheet steel



RHT

High Temperature wheel, up to 200kg



BPM_LOK

Slotted spring plunger with ball tip, LONG-LOK - Stainless steel 303



MPB

Spacer, Brass



TSM T10M

Timing belt per metre, T10 Steel cored polyurethane



DOMI_MD

DOMILINE - Rotating table, 40/1



KB_WW

Linear bearing, Economy range



RTL450

Locking Assembly, High torque



MURP1932

Mini profile-mounted adjusting unit, 19x32mm



CHA_GC_95S

Stainless steel garnet hinge, To be welded



PR821

Idler sprocket, Ranges 821 and 805

Complementary products



BSM

Spring plunger with pressure pin, steel body and pin



BSM_LOK

Spring plunger with pressure pin, LONG-LOK - stainless steel 303 body and pin



BSM

Spring plunger with pressure pin, steel body, plastic pin



BSM_LOK

Spring plunger with pressure pin, LONG-LOK - steel body and pin