

# End cap for rectangular tube

Stock Pla

## BTC

## Black plastic

- Material: black technopolymer

### Info.

- Dimensions are given as a guide and are subject to change
- Not sold individually, please contact us for details.



### DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	Ext. Ø of tube	Tube thickness	Stock*	Price each 1 to 59
BTC20-10	20x10	1-2	-	0,20 €
BTC20-15	20x15	1-2	-	0,25 €
BTC25-10	25x10	1-2	-	0,31 €
BTC25-15	25x15	1-2,5	✓	0,31 €
BTC25-20	25x20	1-3	-	0,31 €
BTC30-10	30x10	1-2	-	0,41 €
BTC30-15	30x15	1-3	✓	0,41 €
BTC30-20	30x20	1-3	✓	0,45 €
BTC30-25	30x25	1-3	-	On request
BTC35-10	35x10	1-2	-	On request
BTC35-20	35x20	1-3	✓	0,57 €
BTC35-25	35x25	1-3	-	On request
BTC35-30	35x30	1-1,5	-	1,26 €
BTC40-10	40x10	1,5-2	-	On request
BTC40-15	40x15	1-2	-	0,57 €
BTC40-20/1-2	40x20	1-3	-	0,76 €
BTC40-25	40x25	1-3	-	0,82 €
BTC40-30	40x30	1-3	-	0,88 €
BTC40-35	40x35	1-3	-	On request
BTC45-15	45x15	1-2	-	On request
BTC45-20	45x20	1-3	-	On request
BTC45-25	45x25	1,5-3	-	On request
BTC45-30	45x30	1-2,5	-	On request
BTC45-35	45x35	1-3,5	-	On request
BTC50-10	50x10	1-2	-	0,88 €
BTC50-20	50x20	1-3	-	0,94 €
BTC50-25	50x25	1-3	✓	1,00 €
BTC50-30/1,5-2	50x30	1-3	-	On request
BTC50-30/3	50x30	3-5	-	On request
BTC50-35	50x35	1-3,5	-	On request
BTC50-40	50x40	1-3	-	1,37 €
BTC55-34	55x34	1,5-4	-	On request

Part number	Ext. Ø of tube	Tube thickness	Stock*	Price each 1 to 59
BTC55-40	55x40	1,5-4	-	On request
BTC60-15	60x15	1-2	-	1,26 €
BTC60-20	60x20	1-3	-	1,31 €
BTC60-25	60x25	1-3	-	1,43 €
BTC60-30	60x30	1-3	✓	1,50 €
BTC60-35	60x35	1,5-3,5	-	On request
BTC60-40/1-3	60x40	1-3	✓	1,97 €
BTC60-40/4-5	60x40	3-5	-	3,87 €
BTC60-50	60x50	1,5-3,5	-	2,70 €
BTC70-20	70x20	1-3,5	-	On request
BTC70-25	70x25	1-2,5	-	On request
BTC70-30	70x30	1-3	-	2,39 €
BTC70-40/1,5-2	70x40	1-3	-	2,81 €
BTC80-20	80x20	1-3	-	2,33 €
BTC80-30/1-2,5	80x30	1-2,5	-	2,39 €
BTC80-30/2,5-4	80x30	2,5-4	-	2,46 €
BTC80-40/1-3	80x40	1-3	✓	2,59 €
BTC80-40/3,2-4	80x40	3,2-5	-	On request
BTC80-50	80x50	1,5-4	✓	5,52 €
BTC80-60/2,5-3	80x60	1,5-3,5	-	5,81 €
BTC80-60/5	80x60	3,5-5	-	8,14 €
BTC100-40	100x40	1,5-4	✓	6,86 €
BTC100-50/2-3	100x50	2-3	✓	7,10 €
BTC100-50/3,2-5	100x50	1,5-4,5	-	On request
BTC120-30	120x30	1-2,5	-	7,40 €
BTC120-40/2	120x40	2	-	13,80 €
BTC120-40/3-5	120x40	3-5	-	7,87 €
BTC120-60	120x60	1,5-5	✓	8,44 €
BTC120-80/2-3	120x80	2-5	-	11,60 €
BTC120-80/5-8	120x80	5-8	✓	11,60 €
BTC140-80	140x80	2-4,5	-	14,86 €
BTC150-100	150x100	1,5-5	-	18,05 €


\*Depending on availability - Dimensions in mm

HPC WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products




BMF

Knurled knob - female, Knurled - through threaded



PTRSS

Idler chain sprocket, For hostile environments



PF15

Worm and wheel gear reducer, up to 3,75 Nm




MSP38

Masterplate® glueable insert Ø38, Cylindrical Ø38 with tapped ins...



ZG0

Plastic spur gear, Machined plastic (delrin)



RPP8

RPP heavy duty timing belt, RPP8



LACT\_SS

Adjustable Stainless steel cam lever, Male



SHA

Handwheel without handle, Polyamide



CLLCLLP

Clevis components, long version, Steel -



RAGFLOWsupport

Floway2® Roller track accessory, Roller



MDB\_MTB

Moulded plastic bevel gear (nylon), 2:1



LRR

Catch-plate for latch, Catch-plate

## Complementary products



BTC

End cap for square tube, Standard



BPTR

End cap for round tube, Standard