
Cylindrical elasto mount

B-ZY

Male / female mounting

- ***Radial elasticity greater than axial elasticity***
- *Cylinder worked under compression or shearing*
- *Materials*
  core: Steel plates
  cylinder: Rubber
- ***Hardness: NK 55-60 shore A***
- *Working temp: -40°C to +70°C*

From size M3 upwards




Uses

- *Dampens sound and vibrations*

Info.

- ***Not sold individually, please contact us for details***
- *Values for loads and rigidity are given as a guide only*





DISCOUNTS Ⓐ

Qty	1+	6+	20+	40+	100+	200+
Disc.	List	-10%	-15%	-20%	-25%	On request

DISCOUNTS Ⓑ

Qty	1+	6+	10+	15+	20+	50+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØG	ØD	H	T	Compression stiffness (N/mm)	Compression Max. load (N)	Shearing stiffness (N/mm)	Shearing Max. load (N)	Stock*	Price each 1 to 5
B-ZY3-8-8	M3	8	8	6	-	-	-	-	✔	Ⓐ 4,03 €
B-ZY4-10-10	M4	10	10	10	48	43	10	35	✔	Ⓐ 2,06 €
B-ZY4-10-15	M4	10	15	10	29	43	5	15	✔	Ⓐ 2,19 €
B-ZY4-15-15	M4	15	15	10	67	95	15	35	✔	Ⓐ 2,06 €
B-ZY4-15-20	M4	15	20	10	-	-	-	-	✔	Ⓐ 2,16 €
B-ZY4-15-30	M4	15	30	15	-	-	-	-	✔	Ⓐ 2,30 €
B-ZY5-15-15	M5	15	15	8	67	95	15	35	✔	Ⓐ 2,16 €
B-ZY6-20-15	M6	20	15	18	130	170	24	60	✔	Ⓐ 2,40 €
B-ZY6-20-20	M6	20	20	18	-	-	-	-	✔	Ⓐ 2,39 €
B-ZY6-20-25	M6	20	25	18	61	170	11	60	✔	Ⓐ 2,50 €
B-ZY6-25-15	M6	25	15	18	-	-	-	-	✔	Ⓐ 2,73 €
B-ZY6-25-20	M6	25	20	18	130	280	30	95	✔	Ⓐ 3,07 €
B-ZY6-25-25	M6	25	25	18	-	-	-	-	✔	Ⓐ 3,17 €
B-ZY6-25-30	M6	25	30	18	71	280	19	95	✔	Ⓐ 3,42 €
B-ZY8-30-15	M8	30	15	20	525	400	58	140	✔	Ⓐ 3,75 €
B-ZY8-30-20	M8	30	20	20	235	400	42	140	✔	Ⓐ 3,99 €
B-ZY8-30-25	M8	30	25	20	-	-	-	-	✔	Ⓐ 4,33 €
B-ZY8-30-30	M8	30	30	20	113	400	28	140	✔	Ⓐ 4,64 €
B-ZY8-30-40	M8	30	40	20	106	400	13	140	✔	Ⓐ 5,21 €
B-ZY8-40-25	M8	40	25	23	-	-	-	-	✔	Ⓐ 5,24 €
B-ZY8-40-30	M8	40	30	23	234	650	49	250	✔	Ⓐ 5,89 €
B-ZY8-40-40	M8	40	40	23	147	650	23	250	✔	Ⓐ 6,78 €
B-ZY10-40-30	M10	40	30	28	-	-	-	-	✔	Ⓐ 6,34 €
B-ZY10-50-20	M10	50	20	28	857	1000	110	400	✔	Ⓐ 7,68 €
B-ZY10-50-25	M10	50	25	28	-	-	-	-	✔	Ⓐ 8,92 €
B-ZY10-50-30	M10	50	30	28	395	1000	73	400	✔	Ⓐ 8,50 €
B-ZY10-50-40	M10	50	40	28	273	1000	58	400	✔	Ⓐ 8,69 €
B-ZY10-50-45	M10	50	45	28	-	-	-	-	-	Ⓐ 8,90 €
B-ZY10-50-50	M10	50	50	28	210	1000	37	400	✔	Ⓐ 9,51 €
B-ZY10-60-40	M10	60	40	28	-	-	-	-	-	Ⓐ 12,82 €
B-ZY10-70-45	M10	70	45	28	-	-	-	-	-	Ⓐ 19,25 €
B-ZY12-60-40	M12	60	40	33	-	-	-	-	✔	Ⓑ 8,48 €
B-ZY12-75-25	M12	75	25	37	-	-	-	-	✔	Ⓑ 10,00 €
B-ZY12-75-40	M12	75	40	37	735	2300	118	850	✔	Ⓑ 10,25 €
B-ZY12-75-50	M12	75	50	37	530	2300	101	850	-	Ⓑ 12,98 €
B-ZY12-75-55	M12	75	55	37	417	2300	78	850	-	Ⓑ 13,52 €
B-ZY16-100-40	M16	100	40	41	2160	4200	283	1600	-	Ⓑ 20,34 €
B-ZY16-100-55	M16	100	55	41	892	4200	145	1600	-	Ⓑ 23,11 €
B-ZY16-100-60	M16	100	60	41	843	4200	142	1600	-	Ⓑ 24,27 €
B-ZY16-100-75	M16	100	75	41	-	-	-	-	-	Ⓑ 30,52 €

**Depending on availability - Dimensions in mm*

Our other products



Machined plastic bevel gear , 2:1



Foot for the food industry, Stainless steel - 3-A standard




Idler for slat top chain, Range 821



Sleeve for splined ball shaft, Chariot - from 514 N to 15386 N




Indexing plunger mini, miniature



Steel bevel gear, 1:1



Right angled gearbox, double output shafts, up to 30 Nm



2A motorised linear actuator, 2 amperes



Steel bevel gear, 2:1



Moulded plastic bevel gear (nylon), 3:1




Motor-gearbox 12V and 24V DC, from 0.1 to 2 Nm



Three-lobed knob, Thermoplastic / Brass or stainless steel insert

Complementary products



Stainless steel cylindrical elasto mount, Stainless steel



Cylindrical elasto mount, Steel



Stainless steel cylindrical elasto mount, Stainless steel



Diabolo shaped elasto mount, Steel