Stainless steel elasto mount

B-ZYss

Male / female fixing

- ***Radial elasticity greater than axial elasticity***
- *Cylinder worked under compression and shearing*
- *Materials:*
  core: stainless steel A2 plates
  cylinder: rubber
- ***Hardness: NK 55-60 shore A***
- *Working temp: -40°C to +70°C*


Uses

- *Noise and vibration dampening*


Info.

- ***Not sold individually, please contact us for details***
- *Values for loads and rigidity are given as a guide only*





From size M3 upwards



Compression

Compression
Shearing

Shearing

DISCOUNTS Ⓐ

Qty	1+	6+	20+	40+	100+
Disc.	List	-10%	-15%	-20%	On request

DISCOUNTS Ⓑ

Qty	1+	6+	10+	15+	20+	50+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØG	ØD	H	T	Compression stiffness (N/mm)	Compression Max. load (N)	Shearing stiffness (N/mm)	Shearing Max. load (N)	Stock*	Price each 1 to 5
B-ZY3-8-8/SS	M3	8	8	6	-	-	-	-	✔	Ⓐ 5,99 €
B-ZY4-10-10/SS	M4	10	10	10	48	43	10	35	✔	Ⓐ 3,14 €
B-ZY4-10-15/SS	M4	10	15	10	29	43	5	15	✔	Ⓐ 3,44 €
B-ZY4-15-15/SS	M4	15	15	10	67	95	15	35	✔	Ⓐ 3,07 €
B-ZY4-15-20/SS	M4	15	20	10	-	-	-	-	✔	Ⓐ 3,27 €
B-ZY4-15-30/SS	M4	15	30	15	-	-	-	-	✔	Ⓐ 3,38 €
B-ZY5-15-15/SS	M5	15	15	8	67	95	15	35	✔	Ⓐ 3,38 €
B-ZY6-20-15/SS	M6	20	15	18	130	170	24	60	✔	Ⓐ 3,62 €
B-ZY6-20-20/SS	M6	20	20	18	-	-	-	-	✔	Ⓐ 3,70 €
B-ZY6-20-25/SS	M6	20	25	18	61	170	11	60	✔	Ⓐ 3,70 €
B-ZY6-25-15/SS	M6	25	15	18	-	-	-	-	✔	Ⓐ 4,00 €
B-ZY6-25-20/SS	M6	25	20	18	130	280	30	95	✔	Ⓐ 4,63 €
B-ZY6-25-25/SS	M6	25	25	18	-	-	-	-	✔	Ⓐ 5,48 €
B-ZY6-25-30/SS	M6	25	30	18	71	280	19	95	✔	Ⓐ 4,82 €
B-ZY8-30-15/SS	M8	30	15	20	525	400	58	140	✔	Ⓐ 5,93 €
B-ZY8-30-20/SS	M8	30	20	20	235	400	42	140	✔	Ⓐ 5,65 €
B-ZY8-30-25/SS	M8	30	25	20	-	-	-	-	✔	Ⓐ 6,60 €
B-ZY8-30-30/SS	M8	30	30	20	113	400	28	140	✔	Ⓐ 6,70 €
B-ZY8-30-40/SS	M8	30	40	20	106	400	13	140	✔	Ⓐ 7,26 €
B-ZY8-40-25/SS	M8	40	25	23	-	-	-	-	✔	Ⓐ 7,87 €
B-ZY8-40-30/SS	M8	40	30	23	234	650	49	250	✔	Ⓐ 8,25 €
B-ZY8-40-40/SS	M8	40	40	23	147	650	23	250	-	Ⓐ 9,68 €
B-ZY10-40-30/SS	M10	40	30	28	-	-	-	-	✔	Ⓐ 9,09 €
B-ZY10-50-20/SS	M10	50	20	28	857	1000	110	400	✔	Ⓐ 12,64 €
B-ZY10-50-25/SS	M10	50	25	28	-	-	-	-	✔	Ⓐ 12,86 €
B-ZY10-50-30/SS	M10	50	30	28	395	1000	73	400	✔	Ⓐ 12,63 €
B-ZY10-50-40/SS	M10	50	40	28	273	1000	58	400	✔	Ⓐ 13,88 €
B-ZY10-50-45/SS	M10	50	45	28	-	-	-	-	✔	Ⓐ 13,72 €
B-ZY10-50-50/SS	M10	50	50	28	210	1000	37	400	✔	Ⓐ 15,44 €
B-ZY10-60-40/SS	M10	60	40	28	-	-	-	-	-	Ⓐ 18,20 €
B-ZY10-70-45/SS	M10	70	45	28	-	-	-	-	-	Ⓐ 26,69 €
B-ZY12-60-40/SS	M12	60	40	33	-	-	-	-	✔	Ⓑ 17,16 €
B-ZY12-75-25/SS	M12	75	25	37	-	-	-	-	✔	Ⓑ 20,67 €
B-ZY12-75-40/SS	M12	75	40	37	735	2300	118	850	✔	Ⓑ 22,75 €
B-ZY12-75-50/SS	M12	75	50	37	530	2300	101	850	-	Ⓑ 26,87 €
B-ZY12-75-55/SS	M12	75	55	37	417	2300	78	850	-	Ⓑ 27,38 €
B-ZY16-100-40/SS	M16	100	40	41	2160	4200	283	1600	-	Ⓑ 48,53 €
B-ZY16-100-55/SS	M16	100	55	41	892	4200	145	1600	-	Ⓑ 53,30 €
B-ZY16-100-60/SS	M16	100	60	41	843	4200	142	1600	-	Ⓑ 54,88 €
B-ZY16-100-75/SS	M16	100	75	41	-	-	-	-	-	Ⓑ 63,64 €

**Depending on availability - Dimensions in mm*

Our other products


BTCW

Cap for square tube to be welded, To be welded


FF10

Offset spur gear reducer, from 0.78 to 3.70 Nm


AT5-25ECO

AT type timing pulley, Economy range - AT5 aluminium


DOMI50

Accessories, Plate


AT10-32ECO

AT type timing pulley, Economy range - AT10 aluminium


UTKswc

Utilitrak® 3 wheels carriage, Series V precision steel wheel


MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm


DILC

Indexing plunger with cam, with cam


AC156-157

Strike for toggle latch, 25.5mm


PRF-SCREEN-5

Screen support, Support with 5 axes of rotation


PITAss

Locking bolt, with T handle


CHINV

Invisible hinge, Invisible - Opening up to 90°

Complementary products


BZY


Cylindrical elasto mount, Steel


AZY_SS

Stainless steel cylindrical elasto mount, Stainless steel


AZY

Cylindrical elasto mount, Steel


EZY

Cylindrical stop, Steel