

- Steel cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø5mm
- Braiding: 1+6 stands of 19 wires for Ø6mm+



1+6

Strands of 7 wires



1+6

Stands of 19 wires

### DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-10%	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each 1 to 2
CAB1.5-100/B	1,5	7x7	145	100	0,98	✓	42,67 €
CAB2-15/B	2,0	7x7	258	15	0,28	✓	10,20 €
CAB2-25/B	2,0	7x7	258	25	0,42	✓	16,73 €
CAB2-50/B	2,0	7x7	258	50	0,85	✓	26,35 €
CAB2-100/B	2,0	7x7	258	100	1,66	-	44,01 €
CAB2.5-15/B	2,5	7x7	410	15	0,38	-	10,64 €
CAB2.5-50/B	2,5	7x7	410	50	1,35	✓	28,93 €
CAB2.5-100/B	2,5	7x7	410	100	2,52	-	49,31 €
CAB2.5-250/B	2,5	7x7	410	250	6,32	-	114,41 €
CAB3-15/B	3,0	7x7	581	15	0,57	✓	12,78 €
CAB3-25/B	3,0	7x7	581	25	0,93	✓	20,94 €
CAB3-50/B	3,0	7x7	581	50	1,86	-	34,90 €
CAB3-100/B	3,0	7x7	581	100	3,85	✓	60,23 €
CAB4-15/B	4,0	7x7	1030	15	0,99	✓	18,67 €
CAB4-25/B	4,0	7x7	1030	25	1,80	✓	26,69 €
CAB4-50/B	4,0	7x7	1030	50	3,32	-	50,53 €
CAB4-100/B	4,0	7x7	1030	100	6,53	-	92,53 €
CAB5-15/B	5,0	7x7	1620	15	1,53	✓	24,40 €
CAB5-25/B	5,0	7x7	1620	25	2,54	-	38,82 €
CAB5-50/B	5,0	7x7	1620	50	5,43	-	73,76 €
CAB5-100/B	5,0	7x7	1620	100	10,40	-	138,21 €
CAB6-15/B	6,0	7x19	2140	15	2,26	✓	38,21 €
CAB6-25/B	6,0	7x19	2140	25	3,70	✓	57,22 €
CAB6-50/B	6,0	7x19	2140	50	7,48	-	105,19 €
CAB6-100/B	6,0	7x19	2140	100	14,16	-	195,02 €
CAB7-15/B	7,0	7x19	3450	15	2,98	-	51,51 €
CAB7-25/B	7,0	7x19	3450	25	5,00	-	82,33 €
CAB7-50/B	7,0	7x19	3450	50	10,00	-	153,06 €
CAB8-15/B	8,0	7x19	3810	15	3,88	✓	54,52 €
CAB8-25/B	8,0	7x19	3810	25	6,76	-	84,96 €
CAB8-50/B	8,0	7x19	3810	50	12,96	-	161,26 €
CAB9-50/B	9,0	7x19	4830	50	16,62	-	199,89 €
CAB10-25/B	10,0	7x19	5960	25	10,30	-	129,21 €

\*Depending on availability - Dimensions in mm

- Stainless steel (316) cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø6mm



1+6  
strands of 7 wires

### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each
CAB2-15/SS	2,0	7x7	230	15	0,26	✓	38,47 €
CAB2-25/SS	2,0	7x7	230	25	0,44	✓	56,82 €
CAB2-100/SS	2,0	7x7	230	100	1,68	-	190,71 €
CAB3-15/SS	3,0	7x7	517	15	0,58	✓	41,26 €
CAB3-25/SS	3,0	7x7	517	25	0,96	-	61,97 €
CAB3-100/SS	3,0	7x7	517	100	3,67	-	229,25 €
CAB4-15/SS	4,0	7x7	916	15	1,04	✓	65,62 €
CAB4-25/SS	4,0	7x7	916	25	1,72	-	107,64 €
CAB4-100/SS	4,0	7x7	916	100	6,54	-	399,84 €
CAB5-15/SS	5,0	7x7	1445	15	1,62	✓	86,36 €
CAB5-25/SS	5,0	7x7	1445	25	3,00	-	143,39 €
CAB5-100/SS	5,0	7x7	1445	100	10,00	-	542,89 €
CAB6-15/SS	6,0	7x7	2070	15	2,34	✓	130,03 €
CAB6-25/SS	6,0	7x7	2070	25	3,75	-	214,56 €
CAB6-100/SS	6,0	7x7	2070	100	14,45	-	821,72 €

\*Depending on availability - Dimensions in mm

## Our other products



BL15

Right angled gearbox,  
from 1.10 to 6 Nm



DOMI30

Accessories, Fixing kit



ZDB

Machined plastic  
bevel gear , 2:1



BAC110

Swivel storage bin,  
Storage bin



EX

Optional shaft for E-  
type gear reducers, E  
Gearboxes double  
sided ou...



HLA28

Right angle spiro  
bevel gearbox, Up to  
182Nm



BUH77

Motor-gearbox 12V  
and 24V DC, from 0.1  
to 2 Nm



ES

Simple support base  
(bipod), Plastic




DILC

Indexing plunger with  
cam, with cam



BABreglable

Adjustable ball pin  
hardened stainless  
steel, adjustable



VKM

Square steel nut,  
Steel - 1 thread



PSG1

Spur gear - precision  
range, Case hardened  
steel 20NCD2

## Complementary products



CCL

Standard wire  
thimble, Steel



SCA

Flat cable clamp,  
Steel



ERC

Quick fitting cable  
terminal, Eye version



ERF

Quick fitting threaded  
cable terminal, Cable  
terminal with  
threaded ...