

- Steel cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø5mm
- Braiding: 1+6 stands of 19 wires for Ø6mm+



1+6

Strands of 7 wires



1+6

Stands of 19 wires

DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-10%	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each 1 to 2
CAB1.5-100/B	1,5	7x7	145	100	0,98	✓	42,67 €
CAB2-15/B	2,0	7x7	258	15	0,28	✓	10,20 €
CAB2-25/B	2,0	7x7	258	25	0,42	✓	16,73 €
CAB2-50/B	2,0	7x7	258	50	0,85	✓	26,35 €
CAB2-100/B	2,0	7x7	258	100	1,66	-	44,01 €
CAB2.5-15/B	2,5	7x7	410	15	0,38	-	10,64 €
CAB2.5-50/B	2,5	7x7	410	50	1,35	✓	28,93 €
CAB2.5-100/B	2,5	7x7	410	100	2,52	-	49,31 €
CAB2.5-250/B	2,5	7x7	410	250	6,32	-	114,41 €
CAB3-15/B	3,0	7x7	581	15	0,57	✓	12,78 €
CAB3-25/B	3,0	7x7	581	25	0,93	✓	20,94 €
CAB3-50/B	3,0	7x7	581	50	1,86	-	34,90 €
CAB3-100/B	3,0	7x7	581	100	3,85	✓	60,23 €
CAB4-15/B	4,0	7x7	1030	15	0,99	✓	18,67 €
CAB4-25/B	4,0	7x7	1030	25	1,80	✓	26,69 €
CAB4-50/B	4,0	7x7	1030	50	3,32	-	50,53 €
CAB4-100/B	4,0	7x7	1030	100	6,53	-	92,53 €
CAB5-15/B	5,0	7x7	1620	15	1,53	✓	24,40 €
CAB5-25/B	5,0	7x7	1620	25	2,54	-	38,82 €
CAB5-50/B	5,0	7x7	1620	50	5,43	-	73,76 €
CAB5-100/B	5,0	7x7	1620	100	10,40	-	138,21 €
CAB6-15/B	6,0	7x19	2140	15	2,26	✓	38,21 €
CAB6-25/B	6,0	7x19	2140	25	3,70	✓	57,22 €
CAB6-50/B	6,0	7x19	2140	50	7,48	-	105,19 €
CAB6-100/B	6,0	7x19	2140	100	14,16	-	195,02 €
CAB7-15/B	7,0	7x19	3450	15	2,98	-	51,51 €
CAB7-25/B	7,0	7x19	3450	25	5,00	-	82,33 €
CAB7-50/B	7,0	7x19	3450	50	10,00	-	153,06 €
CAB8-15/B	8,0	7x19	3810	15	3,88	✓	54,52 €
CAB8-25/B	8,0	7x19	3810	25	6,76	-	84,96 €
CAB8-50/B	8,0	7x19	3810	50	12,96	-	161,26 €
CAB9-50/B	9,0	7x19	4830	50	16,62	-	199,89 €
CAB10-25/B	10,0	7x19	5960	25	10,30	-	129,21 €

*Depending on availability - Dimensions in mm

- Stainless steel (316) cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø6mm



1+6
strands of 7 wires


DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each
CAB2-15/SS	2,0	7x7	230	15	0,26	✓	38,47 €
CAB2-25/SS	2,0	7x7	230	25	0,44	✓	56,82 €
CAB2-100/SS	2,0	7x7	230	100	1,68	-	190,71 €
CAB3-15/SS	3,0	7x7	517	15	0,58	✓	41,26 €
CAB3-25/SS	3,0	7x7	517	25	0,96	-	61,97 €
CAB3-100/SS	3,0	7x7	517	100	3,67	-	229,25 €
CAB4-15/SS	4,0	7x7	916	15	1,04	✓	65,62 €
CAB4-25/SS	4,0	7x7	916	25	1,72	-	107,64 €
CAB4-100/SS	4,0	7x7	916	100	6,54	-	399,84 €
CAB5-15/SS	5,0	7x7	1445	15	1,62	✓	86,36 €
CAB5-25/SS	5,0	7x7	1445	25	3,00	-	143,39 €
CAB5-100/SS	5,0	7x7	1445	100	10,00	-	542,89 €
CAB6-15/SS	6,0	7x7	2070	15	2,34	✓	130,03 €
CAB6-25/SS	6,0	7x7	2070	25	3,75	-	214,56 €
CAB6-100/SS	6,0	7x7	2070	100	14,45	-	821,72 €

*Depending on availability - Dimensions in mm

Our other products



T5M T10M

T type timing belt per metre, T10 Steel cored polyurethane



PGT

Sliding profile, Sliding panel support



ERC

Quick fitting cable terminal, Fork



PRF4545

Standard aluminium profile, 45 x 45 mm



HLA28

Right angle spiro bevel gearbox, Up to 182Nm



NRV

Orthogonal support clamp, Orthogonal support clamp



SSB

Stainless steel bevel gear, 1:1



BOX-TOR-ORFS

Box set of Nitrile O-rings NBR90Sh A, 7.65 x 1.78mm to 37.82 x 1.78



F7-I

Multifunction display, With internal sensor



SVG

Adjustable latch clamp with strike plate, Stroke from



SCA_SS

Stainless steel flat cable clamp, Stainless steel



TCC_SS

Stainless steel rigging screw (hook/hook), Stainless steel

Complementary products



CCLSS

Stainless steel wire thimble, Stainless steel



SCA_SS

Stainless steel flat cable clamp, Stainless steel



PPC_{SS}

Pad eye on mounting plate squarred, Stainless steel



ERC

Quick fitting cable terminal, Fork