

- Steel cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø5mm
- Braiding: 1+6 stands of 19 wires for Ø6mm+



1+6

Strands of 7 wires



1+6

Stands of 19 wires

DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-10%	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each 1 to 2
CAB1.5-100/B	1,5	7x7	145	100	0,98	✓	42,67 €
CAB2-15/B	2,0	7x7	258	15	0,28	✓	10,20 €
CAB2-25/B	2,0	7x7	258	25	0,42	✓	16,73 €
CAB2-50/B	2,0	7x7	258	50	0,85	✓	26,35 €
CAB2-100/B	2,0	7x7	258	100	1,66	-	44,01 €
CAB2.5-15/B	2,5	7x7	410	15	0,38	-	10,64 €
CAB2.5-50/B	2,5	7x7	410	50	1,35	✓	28,93 €
CAB2.5-100/B	2,5	7x7	410	100	2,52	-	49,31 €
CAB2.5-250/B	2,5	7x7	410	250	6,32	-	114,41 €
CAB3-15/B	3,0	7x7	581	15	0,57	✓	12,78 €
CAB3-25/B	3,0	7x7	581	25	0,93	✓	20,94 €
CAB3-50/B	3,0	7x7	581	50	1,86	-	34,90 €
CAB3-100/B	3,0	7x7	581	100	3,85	✓	60,23 €
CAB4-15/B	4,0	7x7	1030	15	0,99	✓	18,67 €
CAB4-25/B	4,0	7x7	1030	25	1,80	✓	26,69 €
CAB4-50/B	4,0	7x7	1030	50	3,32	-	50,53 €
CAB4-100/B	4,0	7x7	1030	100	6,53	-	92,53 €
CAB5-15/B	5,0	7x7	1620	15	1,53	✓	24,40 €
CAB5-25/B	5,0	7x7	1620	25	2,54	-	38,82 €
CAB5-50/B	5,0	7x7	1620	50	5,43	-	73,76 €
CAB5-100/B	5,0	7x7	1620	100	10,40	-	138,21 €
CAB6-15/B	6,0	7x19	2140	15	2,26	✓	38,21 €
CAB6-25/B	6,0	7x19	2140	25	3,70	✓	57,22 €
CAB6-50/B	6,0	7x19	2140	50	7,48	-	105,19 €
CAB6-100/B	6,0	7x19	2140	100	14,16	-	195,02 €
CAB7-15/B	7,0	7x19	3450	15	2,98	-	51,51 €
CAB7-25/B	7,0	7x19	3450	25	5,00	-	82,33 €
CAB7-50/B	7,0	7x19	3450	50	10,00	-	153,06 €
CAB8-15/B	8,0	7x19	3810	15	3,88	✓	54,52 €
CAB8-25/B	8,0	7x19	3810	25	6,76	-	84,96 €
CAB8-50/B	8,0	7x19	3810	50	12,96	-	161,26 €
CAB9-50/B	9,0	7x19	4830	50	16,62	-	199,89 €
CAB10-25/B	10,0	7x19	5960	25	10,30	-	129,21 €

*Depending on availability - Dimensions in mm

- Stainless steel (316) cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø6mm



1+6
strands of 7 wires

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each
CAB2-15/SS	2,0	7x7	230	15	0,26	✓	38,47 €
CAB2-25/SS	2,0	7x7	230	25	0,44	✓	56,82 €
CAB2-100/SS	2,0	7x7	230	100	1,68	-	190,71 €
CAB3-15/SS	3,0	7x7	517	15	0,58	✓	41,26 €
CAB3-25/SS	3,0	7x7	517	25	0,96	-	61,97 €
CAB3-100/SS	3,0	7x7	517	100	3,67	-	229,25 €
CAB4-15/SS	4,0	7x7	916	15	1,04	✓	65,62 €
CAB4-25/SS	4,0	7x7	916	25	1,72	-	107,64 €
CAB4-100/SS	4,0	7x7	916	100	6,54	-	399,84 €
CAB5-15/SS	5,0	7x7	1445	15	1,62	✓	86,36 €
CAB5-25/SS	5,0	7x7	1445	25	3,00	-	143,39 €
CAB5-100/SS	5,0	7x7	1445	100	10,00	-	542,89 €
CAB6-15/SS	6,0	7x7	2070	15	2,34	✓	130,03 €
CAB6-25/SS	6,0	7x7	2070	25	3,75	-	214,56 €
CAB6-100/SS	6,0	7x7	2070	100	14,45	-	821,72 €

*Depending on availability - Dimensions in mm

Our other products



FBL4004_K7
Brush strip per meter
PA6 fibres Ø0.3 to
Ø0.5, Black polyamide
6 -...



GLP
Small 6 lobe threaded
handle - male,
Technopolymer -
Stainless steel




HTD14M_85
HTD Heavy duty
timing pulley, HTD14
Cast



PRF_PGN
Door handle for
aluminium profile,
Handle with lock
suitable



INS_SS
Self tapping stainless
steel insert, 316
stainless steel



RPP5
RPP heavy duty
timing belt, RPP5



BIM
Indexing plunger mini,
miniature




BOX-SHNA
Hexagonal nut -
DIN934, Box set of
steel nuts



PPRss
Pad eye on mounting
plate round, Stainless
steel



EHD04
Internal epicyclic
servo reducers, from
3.4 to 7 Nm



GMC
Flat profile - Round
guide, Flat profile -
round guide



PRF_PL_4590
Joining plate for
aluminium profile,
Joint plate - 45x90
mm

Complementary products



CCL
Standard wire
thimble, Steel



SCA
Flat cable clamp,
Steel



ERC
Quick fitting cable
terminal, Eye version



ERF
Quick fitting threaded
cable terminal, Cable
terminal with
threaded ...