

- Steel cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø5mm
- Braiding: 1+6 stands of 19 wires for Ø6mm+



1+6

Strands of 7 wires



1+6

Stands of 19 wires

DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-10%	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each 1 to 2
CAB1.5-100/B	1,5	7x7	145	100	0,98	✓	42,67 €
CAB2-15/B	2,0	7x7	258	15	0,28	✓	10,20 €
CAB2-25/B	2,0	7x7	258	25	0,42	✓	16,73 €
CAB2-50/B	2,0	7x7	258	50	0,85	✓	26,35 €
CAB2-100/B	2,0	7x7	258	100	1,66	-	44,01 €
CAB2.5-15/B	2,5	7x7	410	15	0,38	-	10,64 €
CAB2.5-50/B	2,5	7x7	410	50	1,35	✓	28,93 €
CAB2.5-100/B	2,5	7x7	410	100	2,52	-	49,31 €
CAB2.5-250/B	2,5	7x7	410	250	6,32	-	114,41 €
CAB3-15/B	3,0	7x7	581	15	0,57	✓	12,78 €
CAB3-25/B	3,0	7x7	581	25	0,93	✓	20,94 €
CAB3-50/B	3,0	7x7	581	50	1,86	-	34,90 €
CAB3-100/B	3,0	7x7	581	100	3,85	✓	60,23 €
CAB4-15/B	4,0	7x7	1030	15	0,99	✓	18,67 €
CAB4-25/B	4,0	7x7	1030	25	1,80	✓	26,69 €
CAB4-50/B	4,0	7x7	1030	50	3,32	-	50,53 €
CAB4-100/B	4,0	7x7	1030	100	6,53	-	92,53 €
CAB5-15/B	5,0	7x7	1620	15	1,53	✓	24,40 €
CAB5-25/B	5,0	7x7	1620	25	2,54	-	38,82 €
CAB5-50/B	5,0	7x7	1620	50	5,43	-	73,76 €
CAB5-100/B	5,0	7x7	1620	100	10,40	-	138,21 €
CAB6-15/B	6,0	7x19	2140	15	2,26	✓	38,21 €
CAB6-25/B	6,0	7x19	2140	25	3,70	✓	57,22 €
CAB6-50/B	6,0	7x19	2140	50	7,48	-	105,19 €
CAB6-100/B	6,0	7x19	2140	100	14,16	-	195,02 €
CAB7-15/B	7,0	7x19	3450	15	2,98	-	51,51 €
CAB7-25/B	7,0	7x19	3450	25	5,00	-	82,33 €
CAB7-50/B	7,0	7x19	3450	50	10,00	-	153,06 €
CAB8-15/B	8,0	7x19	3810	15	3,88	✓	54,52 €
CAB8-25/B	8,0	7x19	3810	25	6,76	-	84,96 €
CAB8-50/B	8,0	7x19	3810	50	12,96	-	161,26 €
CAB9-50/B	9,0	7x19	4830	50	16,62	-	199,89 €
CAB10-25/B	10,0	7x19	5960	25	10,30	-	129,21 €

*Depending on availability - Dimensions in mm

- Stainless steel (316) cable sold by the reel
- Braiding: 1+6 strands of 7 wires up to Ø6mm



1+6
strands of 7 wires

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each
CAB2-15/SS	2,0	7x7	230	15	0,26	✓	38,47 €
CAB2-25/SS	2,0	7x7	230	25	0,44	✓	56,82 €
CAB2-100/SS	2,0	7x7	230	100	1,68	-	190,71 €
CAB3-15/SS	3,0	7x7	517	15	0,58	✓	41,26 €
CAB3-25/SS	3,0	7x7	517	25	0,96	-	61,97 €
CAB3-100/SS	3,0	7x7	517	100	3,67	-	229,25 €
CAB4-15/SS	4,0	7x7	916	15	1,04	✓	65,62 €
CAB4-25/SS	4,0	7x7	916	25	1,72	-	107,64 €
CAB4-100/SS	4,0	7x7	916	100	6,54	-	399,84 €
CAB5-15/SS	5,0	7x7	1445	15	1,62	✓	86,36 €
CAB5-25/SS	5,0	7x7	1445	25	3,00	-	143,39 €
CAB5-100/SS	5,0	7x7	1445	100	10,00	-	542,89 €
CAB6-15/SS	6,0	7x7	2070	15	2,34	✓	130,03 €
CAB6-25/SS	6,0	7x7	2070	25	3,75	-	214,56 €
CAB6-100/SS	6,0	7x7	2070	100	14,45	-	821,72 €

*Depending on availability - Dimensions in mm

Our other products



MSP19

Masterplate®
glueable insert,
Cylindrical with nut



GMK17_BR

Clamp for guiding
profile, Rounded only
- double



SERB

Universal latch key,
Universal latch key



BH02

Single housed bearing
assembly, Bearing
secured with circlips



BOX-TOR-G

Box set of Nitrile O-
rings, 3.00 x 1.50mm
to 30.20 x 3.00



FF40

Offset spur gear
reducer, from 59 to
210 Nm



BPL

Ball transfer unit,
Light



VELM4

Screw-on for hook-and-
loop, Polyamide



H0

Crossed helical gear
crossed axis à 90°,



RJUM01

Closed polymer
DryLin®R bearing,



GCB880

Curved track for plate
chain, Ranges 880



HW_HT

Half-rail guide, Rail

Complementary products



CCL

Standard wire
thimble, Steel



SCA

Flat cable clamp,
Steel



ERC

Quick fitting cable
terminals, Eye version



ERF

Quick fitting threaded
cable terminal, Cable
terminal with
threaded ...