
Galvanised steel cable

Ste

CAB — 7x7 or 7x19 Metal core

- **Steel cable sold by the reel**
- Braiding: 1+6 strands of 7 wires up to Ø5mm
- Braiding: 1+6 stands of 19 wires for Ø6mm+





1+6
Strands of 7 wires



1+6
Stands of 19 wires

DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-10%	-15%	On request

Part number	Ø cable	Construction	Breaking strenght (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each 1 to 2
CAB1.5-100/B	1,5	7x7	145	100	0,98	✔	45,32 €
CAB2-15/B	2,0	7x7	258	15	0,28	✔	11,08 €
CAB2-25/B	2,0	7x7	258	25	0,42	✔	18,18 €
CAB2-50/B	2,0	7x7	258	50	0,85	✔	28,32 €
CAB2-100/B	2,0	7x7	258	100	1,66	-	46,75 €
CAB2.5-15/B	2,5	7x7	410	15	0,38	-	11,56 €
CAB2.5-50/B	2,5	7x7	410	50	1,35	-	31,09 €
CAB2.5-100/B	2,5	7x7	410	100	2,52	-	55,42 €
CAB2.5-250/B	2,5	7x7	410	250	6,32	-	128,59 €
CAB3-15/B	3,0	7x7	581	15	0,57	✔	13,90 €
CAB3-25/B	3,0	7x7	581	25	0,93	✔	22,77 €
CAB3-50/B	3,0	7x7	581	50	1,86	-	37,50 €
CAB3-100/B	3,0	7x7	581	100	3,85	✔	67,69 €
CAB4-15/B	4,0	7x7	1030	15	0,99	✔	20,63 €
CAB4-25/B	4,0	7x7	1030	25	1,80	✔	31,43 €
CAB4-50/B	4,0	7x7	1030	50	3,32	-	58,81 €
CAB4-100/B	4,0	7x7	1030	100	6,53	-	104,00 €
CAB5-15/B	5,0	7x7	1620	15	1,53	✔	32,05 €
CAB5-25/B	5,0	7x7	1620	25	2,54	-	46,41 €
CAB5-50/B	5,0	7x7	1620	50	5,43	--	89,16 €
CAB5-100/B	5,0	7x7	1620	100	10,40	-	155,34 €
CAB6-15/B	6,0	7x19	2140	15	2,26	✔	46,52 €
CAB6-25/B	6,0	7x19	2140	25	3,70	✔	69,67 €
CAB6-50/B	6,0	7x19	2140	50	7,48	-	137,94 €
CAB6-100/B	6,0	7x19	2140	100	14,16	-	237,47 €
CAB7-15/B	7,0	7x19	3450	15	2,98	-	57,89 €
CAB7-25/B	7,0	7x19	3450	25	5,00	-	96,39 €
CAB7-50/B	7,0	7x19	3450	50	10,00	-	179,20 €
CAB8-15/B	8,0	7x19	3810	15	3,88	✔	76,60 €
CAB8-25/B	8,0	7x19	3810	25	6,76	-	123,34 €
CAB8-50/B	8,0	7x19	3810	50	12,96	-	234,12 €
CAB9-50/B	9,0	7x19	4830	50	16,62	-	280,84 €
CAB10-25/B	10,0	7x19	5960	25	10,30	-	193,64 €

*Depending on availability - Dimensions in mm

PVC covered galvanised steel cable

7x7 or 7x19 metal core

CAB/PVC

- ***Steel cable sold in rolls with anti-UV transparent PVC coating***
- *Braiding*
  > Ø5mm : 1 + 6 strands of 7 wires
  Ø6mm > : 1 + 6 strands of 19 wires

Applications


- *Plastic reel*
- *Outdoor applications*


Option

- *100m reels*

Info

- *Remove the PVC protection on the area concerned if cable is being crimped*





7x19



7x7

DISCOUNTS

Qty	1+	3+	10+
Disc.	Net	-10%	On request

Part number	Cable Ø	ØExt	Type of braiding	Breaking strength (kg)	Length (metre)	Weight of reel (kg)	Price each 1 to 2
CAB2-25/PVC	2	3	7x7	280	25	0,57	26,73 €
CAB3-25/PVC	3	5	7x7	630	25	1,39	38,08 €
CAB4-25/PVC	4	6	7x7	1120	25	2,25	46,18 €
CAB6-25/PVC	6	8	7x19	2351	25	4,42	98,32 €

All dimensions in mm

Stainless steel cable

CABss — 7x7 Metal core

- ***Stainless steel (316) cable sold by the reel***
- *Braiding: 1+6 strands of 7 wires up to Ø6mm*





1+6
strands of 7 wires

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ø cable	Construction	Breaking strength (kg)	Length (m)	Weight per reel (kg)	Stock*	Price each
CAB2-15/SS	2,0	7x7	230	15	0,26	✔	32,47 €
CAB2-25/SS	2,0	7x7	230	25	0,44	✔	46,78 €
CAB2-100/SS	2,0	7x7	230	100	1,68	-	157,03 €
CAB3-15/SS	3,0	7x7	517	15	0,58	✔	34,82 €
CAB3-25/SS	3,0	7x7	517	25	0,96	✔	51,03 €
CAB3-100/SS	3,0	7x7	517	100	3,67	-	188,77 €
CAB4-15/SS	4,0	7x7	916	15	1,04	✔	55,39 €
CAB4-25/SS	4,0	7x7	916	25	1,72	-	88,64 €
CAB4-100/SS	4,0	7x7	916	100	6,54	-	329,24 €
CAB5-15/SS	5,0	7x7	1445	15	1,62	✔	79,11 €
CAB5-25/SS	5,0	7x7	1445	25	3,00	-	125,45 €
CAB5-100/SS	5,0	7x7	1445	100	10,00	-	447,04 €
CAB6-15/SS	6,0	7x7	2070	15	2,34	✔	109,75 €
CAB6-25/SS	6,0	7x7	2070	25	3,75	-	181,09 €
CAB6-100/SS	6,0	7x7	2070	100	14,45	-	676,63 €


**Depending on availability - Dimensions in mm*

Swaging sleeve for fitting cable

To crimp a wire rope

CABMA

- **Sleeve for fitting cable with metal core**
- Complies with standard 13411-3 from CAB2-MA/B
- Temperature range: max 100 °C
- Material:
  Crude Aluminium



Application

- For making retaining cables.
- For use with sheathed cable, remove the sheath along the length of the crimp to obtain a proper crimp.
  Important:
- Not suitable for lifting
- Not suitable for stainless steel cable

Info

- Cutting and crimping Tool CAB-TOOL

Accessories

- Pliers **CAB**TOOL **(tome 1 p.422)**



Application example

DISCOUNTS

Qty	1+	3+	5+
Disc.	Price	-10%	On request

Part number	For metal cable Diameter	For metal cable	Qty per lot	Price each 1 to 2
CAB1.5-MA/B	1.5	CAB1.5	100	23,02 €
CAB2-MA/B	2	CAB2	100	29,56 €
CAB2.5-MA/B	2.5	CAB2.5	100	42,66 €
CAB3-MA/B	3	CAB3	100	34,85 €
CAB4-MA/B	4	CAB4	100	50,32 €
CAB5-MA/B	5	CAB5	100	70,45 €

Dimensions in mm

Fitting cable tools


CABTOOL — Cutting and crimping tools

- ***Swaging and cable cutting pliers***
- *Material:*
  Steel, red paint


Application

- *For manual crimping of aluminium sleeves* **CAB-MA** *on fitting cables*
- *For cutting* **CAB** *fitting cables to length.*






CAB-TOOL-M1



CAB-TOOL-C1



CAB-TOOL-M2
CAB-TOOL-M3



CAB-TOOL-C2

DISCOUNTS

Qty	1+	2+	3+
Disc.	Price	-10%	On request

Part number	For sleeve	For metal cable diameter	Length L	Weight (kg)	Price each
Hand swage tool					
CAB-TOOL-M1	CAB1.5-MA	1,5	230	0,350	57,49 €
	CAB2-MA	2			
CAB-TOOL-M2	CAB2-MA	2	440	1,030	183,21 €
	CAB2,5-MA	2,5			
	CAB3-MA	3			
CAB-TOOL-M3	CAB2-MA	2	660	2,610	235,33 €
	CAB2,5-MA	2,5			
	CAB3-MA	3			
	CAB4-MA	4			
	CAB5-MA	5			
Cable-cutting tool					
CAB-TOOL-C1		1 to 4	200	0,273	40,60 €
CAB-TOOL-C2		1 to 6	450	1,80	68,40 €

Dimensions in mm