Wide plate chain stainless steel

Range 805

CAP805ss

- ***Ideal for moving large or heavy loads***
- *Completely smooth surface*
- *With double hinge*
- *Materials:*
  Plates: polished cold-laminated stainless steel (30HRc min.)
  Pin: special stainless steel (41-44HRc)
- *Operating temp.: -40°C to +260°C (+120°C in humid environments)*
- *Length 3048mm (80 plates)*





Advantages


- *Large width*
- *High carrying capacity*

Associated products

- *Drive sprocket* **PT821**
- *Idler sprocket* **PR821**
- *Idler* **DBL805**







DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	Width K (mm)	Length (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP805-190/SS	190,5	3048	19000	5,8	252,74 €

Dimensions in mm

Our other products



MAX26

Motor-gearbox 12V and 24V DC, from 0,075 to 0,6Nm




MET

Cylindrical sintered bronze bush, Self-lubricating sintered bronze



HDSS

Needle roller double universal joint - Stainless steel, Heavy duty



PCF2

Conical flexible mount, Oval base plate



SLVVlok

Vertical toggle clamp, Vertical toggle clamp / vertical foot



CHAE4060PA

Decorative asymmetric screwed hinge, Polyamide



SSE

Stainless steel spherical bearing, Stainless steel / PTFE



CHB

Worm and wheel gear reducer, up to 73 Nm




PCS62SS

Chain sprocket - Stainless steel, 15.875mm (DIN



PSP

Support profile, Panel support



RPPM

RPP type belt per metre, RPP14 Steel cored polyurethane



DOG316

Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm

Complementary products




PT821

Drive sprocket for slat top chain, Ranges 821 and 805



PR821

Idler sprocket for slat top chain, Ranges 821 and 805



PRL

Wear strip for slat top chain, L profile to be clipped