
Compression spring DIN 2095


CD
Ø0,5-Ø0,8

Stainless steel piano wire

- ***Materials:***
  Piano wire: stainless steel conforming to DIN 17224, Stainless steel 1.4310 (301)
- *Wound: right hand*
- *Ends:*
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm squared and ground
- *Loads: Load values indicated are based on a life of 50,000 cycles at 50% of max. load*
- *Tolerances: All sizes and strengths in accordance with DIN 2095 (Grade 2)*

100+ pieces Contact us





Info.

- *Please contact us for custom made springs for your application. (Minimum order quantities may apply)*

DISCOUNTS

Qty	1+	5+	25+	50+	100+
Disc.	List	-10%	-20%	-30%	On request

Part number	Wire Ød	External Ø Do	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2110	0,50	3,00	3,50	4,40	9,94	0,90	8,93	✔	9,32 €
CD2111	0,50	3,00	5,50	6,10	6,37	1,40	8,93	✔	9,32 €
CD2112	0,50	3,00	8,50	8,70	4,12	2,20	8,93	✔	9,32 €
CD2113	0,50	3,00	12,50	12,00	2,81	3,00	8,93	✔	9,32 €
CD2114	0,50	3,00	18,50	17,50	1,90	4,70	8,93	✔	9,32 €
CD2115	0,50	3,70	3,50	5,50	4,78	1,80	8,59	-	9,32 €
CD2116	0,50	3,70	5,50	7,90	3,03	2,80	8,59	✔	9,32 €
CD2117	0,50	3,70	8,50	11,50	1,96	4,40	8,59	✔	9,32 €
CD2118	0,50	3,70	12,50	16,00	1,34	6,20	8,59	✔	9,32 €
CD2119	0,50	3,70	18,50	23,50	0,90	9,50	8,59	✔	9,32 €
CD2120	0,50	4,50	3,50	7,00	2,43	3,30	8,00	✔	9,32 €
CD2121	0,50	4,50	5,50	10,00	1,55	4,90	8,00	✔	9,32 €
CD2122	0,50	4,50	8,50	15,00	1,00	7,90	8,00	✔	9,32 €
CD2123	0,50	4,50	12,50	21,50	0,68	11,70	8,00	✔	9,32 €
CD2124	0,50	4,50	18,50	31,00	0,46	17,00	8,00	✔	9,32 €
CD2125	0,50	5,50	3,50	9,40	1,25	5,50	6,91	✔	9,32 €
CD2126	0,50	5,50	5,50	14,00	0,80	8,60	6,91	✔	9,32 €
CD2127	0,50	5,50	8,50	20,50	0,52	12,90	6,91	✔	9,32 €
CD2128	0,50	5,50	12,50	30,00	0,35	19,40	6,91	✔	9,32 €
CD2129	0,50	5,50	18,50	44,50	0,23	29,40	6,91	✔	9,32 €

**Depending on availability - Dimensions in mm*

Part number	Wire Ød	External Ø Do	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2130	0,50	6,80	3,50	13,50	0,63	9,20	5,64	✔	9,32 €
CD2131	0,50	6,80	5,50	20,00	0,40	14,00	5,64	✔	9,32 €
CD2132	0,50	6,80	8,50	30,00	0,26	21,30	5,64	✔	9,32 €
CD2133	0,50	6,80	12,50	44,00	0,18	31,80	5,64	✔	9,32 €
CD2134	0,50	6,80	18,50	65,00	0,12	47,60	5,64	✔	9,32 €
CD2135	0,63	3,83	3,50	5,50	12,04	1,50	18,00	-	9,32 €
CD2136	0,63	3,83	5,50	7,80	7,64	2,40	18,00	✔	9,32 €
CD2137	0,63	3,83	8,50	11,00	4,96	3,50	18,00	✔	9,32 €
CD2138	0,63	3,83	12,50	15,50	3,38	5,20	18,00	✔	9,32 €
CD2139	0,63	3,83	18,50	22,50	2,28	7,80	18,00	-	9,32 €
CD2140	0,63	4,63	3,50	6,70	6,15	2,40	14,80	✔	9,32 €
CD2141	0,63	4,63	5,50	9,60	3,91	3,80	14,80	✔	9,32 €
CD2142	0,63	4,63	8,50	14,00	2,53	5,80	14,80	✔	9,32 €
CD2143	0,63	4,63	12,50	20,00	1,72	8,70	14,80	✔	9,32 €
CD2144	0,63	4,63	18,50	29,00	1,16	12,80	14,80	✔	9,32 €
CD2145	0,63	5,63	3,50	8,50	3,17	4,20	13,30	✔	9,32 €
CD2146	0,63	5,63	5,50	12,50	2,02	6,70	13,30	✔	9,32 €
CD2147	0,63	5,63	8,50	18,50	1,30	10,30	13,30	✔	9,32 €
CD2148	0,63	5,63	12,50	26,00	0,88	14,70	13,30	✔	9,32 €
CD2149	0,63	5,63	18,50	38,50	0,60	22,30	13,30	✔	9,32 €
CD2150	0,63	6,93	3,50	11,50	1,57	6,90	10,70	✔	9,32 €
CD2151	0,63	6,93	5,50	17,00	1,00	10,80	10,70	✔	9,32 €
CD2152	0,63	6,93	8,50	25,50	0,65	16,60	10,70	✔	9,32 €
CD2153	0,63	6,93	12,50	36,50	0,44	24,20	10,70	✔	9,32 €
CD2154	0,63	6,93	18,50	54,00	0,29	36,30	10,70	✔	9,32 €
CD2155	0,63	8,63	3,50	16,00	0,76	10,90	8,60	✔	9,32 €
CD2156	0,63	8,63	5,50	24,50	0,49	17,40	8,60	✔	9,32 €
CD2157	0,63	8,63	8,50	37,00	0,32	26,80	8,60	✔	9,32 €
CD2158	0,63	8,63	12,50	55,00	0,21	40,70	8,60	✔	9,32 €
CD2159	0,63	8,63	18,50	80,50	0,15	59,90	8,60	✔	9,32 €
CD2160	0,80	4,80	3,50	6,90	15,92	1,70	27,40	⏳	9,67 €
CD2161	0,80	4,80	5,50	9,70	10,20	2,70	27,40	✔	9,67 €
CD2162	0,80	4,80	8,50	14,00	6,59	4,20	27,40	✔	9,67 €
CD2163	0,80	4,80	12,50	19,50	4,48	6,00	27,40	✔	9,67 €
CD2164	0,80	4,80	18,50	28,00	3,02	8,90	27,40	✔	9,67 €
CD2165	0,80	5,80	3,50	8,30	8,19	2,70	22,30	⏳	9,67 €
CD2166	0,80	5,80	5,50	12,00	5,21	4,30	22,30	✔	9,67 €
CD2167	0,80	5,80	8,50	17,50	3,37	6,60	22,30	✔	9,67 €
CD2168	0,80	5,80	12,50	24,50	2,29	9,40	22,30	✔	9,67 €
CD2169	0,80	5,80	18,50	36,00	1,55	14,50	22,30	✔	9,67 €
CD2170	0,80	7,10	3,50	10,50	4,10	4,90	20,60	✔	9,67 €
CD2171	0,80	7,10	5,50	15,50	2,60	7,80	20,60	✔	9,67 €
CD2172	0,80	7,10	8,50	23,00	1,68	12,10	20,60	✔	9,67 €
CD2173	0,80	7,10	12,50	33,00	1,14	17,90	20,60	✔	9,67 €
CD2174	0,80	7,10	18,50	48,00	0,77	26,50	20,60	✔	9,67 €

*Depending on availability - Dimensions in mm


Compression spring DIN 2095


CD
Ø0,8-Ø1,6

Stainless steel piano wire

- ***Materials:***
  Piano wire: stainless steel conforming to DIN 17224, Stainless steel 1.4310 (301)
- Wound: right hand
- Ends:
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm squared and ground
- Loads: Load values indicated are based on a life of 50,000 cycles at 50% of max. load
- Tolerances: All sizes and strengths in accordance with DIN 2095 (Grade 2)

100+ pieces Contact us





Info.

- Please contact us for custom made springs for your application. (Minimum order quantities may apply)

DISCOUNTS

Qty	1+	5+	25+	50+	100+
Disc.	List	-10%	-20%	-30%	On request

Part number	Wire Ød	External Ø Do	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2175	0,80	8,80	3,50	14,50	1,99	8,40	16,70	✔	9,67 €
CD2176	0,80	8,80	5,50	21,50	1,27	13,10	16,70	✔	9,67 €
CD2177	0,80	8,80	8,50	32,00	0,82	20,00	16,70	✔	9,67 €
CD2178	0,80	8,80	12,50	47,00	0,56	30,30	16,70	✔	9,67 €
CD2179	0,80	8,80	18,50	68,00	0,38	44,20	16,70	✔	9,67 €
CD2180	0,80	10,80	3,50	20,00	1,03	13,10	13,20	✔	9,32 €
CD2181	0,80	10,80	5,50	30,00	0,65	20,20	13,20	✔	9,32 €
CD2182	0,80	10,80	8,50	45,50	0,42	31,20	13,20	✔	9,32 €
CD2183	0,80	10,80	12,50	66,00	0,28	46,10	13,20	✔	9,32 €
CD2184	0,80	10,80	18,50	96,50	0,20	68,00	13,20	-	9,67 €
CD2185	1,00	6,00	3,50	8,50	20,00	1,90	38,00	-	12,31 €
CD2186	1,00	6,00	5,50	12,00	12,72	3,00	38,00	✔	12,31 €
CD2187	1,00	6,00	8,50	17,00	8,22	4,40	38,00	✔	12,31 €
CD2188	1,00	6,00	12,50	24,00	5,59	6,60	38,00	✔	12,31 €
CD2189	1,00	6,00	18,50	34,50	3,78	9,90	38,00	✔	12,31 €
CD2190	1,00	7,30	3,50	10,00	9,94	2,70	29,00	✔	12,31 €
CD2191	1,00	7,30	5,50	14,50	6,35	4,40	29,00	✔	12,31 €
CD2192	1,00	7,30	8,50	21,50	4,11	7,20	29,00	✔	12,31 €
CD2193	1,00	7,30	12,50	30,50	2,80	10,60	29,00	✔	12,31 €
CD2194	1,00	7,30	18,50	43,50	1,89	15,20	29,00	✔	12,31 €

*Depending on availability - Dimensions in mm

Part number	Wire Ød	External Ø Do	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2195	1,00	9,00	3,50	13,00	4,88	5,70	28,00	✔	12,31 €
CD2196	1,00	9,00	5,50	19,00	3,10	8,90	28,00	✔	12,31 €
CD2197	1,00	9,00	8,50	28,50	2,00	14,20	28,00	✔	12,31 €
CD2198	1,00	9,00	12,50	40,50	1,37	20,60	28,00	✔	12,31 €
CD2199	1,00	9,00	18,50	59,00	0,93	30,70	28,00	✔	12,31 €
CD2200	1,00	11,00	3,50	17,50	2,49	9,50	23,00	✔	12,31 €
CD2201	1,00	11,00	5,50	26,00	1,59	14,80	23,00	✔	12,31 €
CD2202	1,00	11,00	8,50	39,00	1,03	23,00	23,00	✔	12,31 €
CD2203	1,00	11,00	12,50	56,00	0,70	33,60	23,00	✔	12,31 €
CD2204	1,00	11,00	18,50	81,50	0,47	49,50	23,00	✔	12,31 €
CD2205	1,00	13,50	3,50	24,00	1,28	14,60	19,00	✔	12,31 €
CD2206	1,00	13,50	5,50	36,50	0,82	23,10	19,00	✔	12,31 €
CD2207	1,00	13,50	8,50	55,50	0,52	36,10	19,00	✔	12,31 €
CD2208	1,00	13,50	12,50	80,50	0,35	53,10	19,00	✔	12,31 €
CD2209	1,00	13,50	18,50	115,00	0,24	75,60	19,00	✔	12,31 €
CD2210	1,25	7,55	3,50	12,00	24,93	4,80	114,00	✔	11,85 €
CD2211	1,25	7,55	5,50	17,00	15,49	7,20	114,00	✔	11,85 €
CD2212	1,25	7,55	8,50	25,00	10,10	11,20	114,00	✔	11,85 €
CD2213	1,25	7,55	12,50	35,50	6,95	16,30	114,00	✔	11,85 €
CD2214	1,25	7,55	18,50	51,50	4,63	24,20	114,00	✔	11,85 €
CD2215	1,25	9,25	3,50	15,00	12,30	7,60	90,00	✔	11,85 €
CD2216	1,25	9,25	5,50	22,00	7,66	11,50	90,00	✔	11,85 €
CD2217	1,25	9,25	8,50	33,00	5,01	18,10	90,00	✔	11,85 €
CD2218	1,25	9,25	12,50	47,50	3,40	26,50	90,00	✔	11,85 €
CD2219	1,25	9,25	18,50	69,00	2,31	39,00	90,00	✔	11,85 €
CD2220	1,25	11,25	3,50	20,00	6,09	12,30	73,00	✔	11,85 €
CD2221	1,25	11,25	5,50	29,50	3,87	18,70	73,00	✔	11,85 €
CD2222	1,25	11,25	8,50	44,50	2,51	29,30	73,00	✔	11,85 €
CD2223	1,25	11,25	12,50	64,00	1,71	42,90	73,00	✔	11,85 €
CD2224	1,25	11,25	18,50	93,50	1,15	63,50	73,00	✔	11,85 €
CD2225	1,25	13,75	3,50	27,00	3,12	18,80	59,00	✔	11,85 €
CD2226	1,25	13,75	5,50	41,50	1,98	29,90	59,00	✔	11,85 €
CD2227	1,25	13,75	8,50	62,50	1,28	46,00	59,00	✔	11,85 €
CD2228	1,25	13,75	12,50	90,50	0,88	67,40	59,00	✔	11,85 €
CD2229	1,25	13,75	18,50	130,00	0,59	97,10	59,00	✔	11,85 €
CD2230	1,25	17,25	3,50	40,50	1,49	31,40	46,00	✔	11,85 €
CD2231	1,25	17,25	5,50	62,00	0,94	49,10	46,00	✔	11,85 €
CD2232	1,25	17,25	8,50	94,00	0,62	75,50	46,00	✔	11,85 €
CD2233	1,25	17,25	12,50	140,00	0,41	114,00	46,00	✔	11,85 €
CD2234	1,25	17,25	18,50	205,00	0,27	168,00	46,00	✔	11,85 €
CD2235	1,60	9,60	3,50	14,50	32,00	5,50	182,00	✔	11,17 €
CD2236	1,60	9,60	5,50	21,50	20,38	8,90	182,00	✔	11,17 €
CD2237	1,60	9,60	8,50	31,50	13,23	13,60	182,00	✔	11,17 €
CD2238	1,60	9,60	12,50	45,00	8,93	20,20	182,00	✔	11,17 €
CD2239	1,60	9,60	18,50	65,50	6,06	30,30	182,00	✔	11,17 €

*Depending on availability - Dimensions in mm


Compression spring DIN 2095

CD
Ø1,6-Ø2

Stainless steel piano wire

- ***Materials***:
  Piano wire: stainless steel conforming to DIN 17224, Stainless steel 1.4310 (301)
- Wound: right hand
- Ends:
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm squared and ground
- Loads: Load values indicated are based on a life of 50,000 cycles at 50% of max. load
- Tolerances: All sizes and strengths in accordance with DIN 2095 (Grade 2)
- Custom designs: Please contact us for custom made springs for your application. (Minimum order quantities may apply)





DISCOUNTS


Qty	1+	5+	25+	50+	100+
Disc.	List	-10%	-20%	-30%	On request


Part number	Wire Ød	External ØDo	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2240	1,60	11,60	3,50	18,50	16,42	9,10	146,00	✔	11,17 €
CD2241	1,60	11,60	5,50	27,00	10,44	13,80	146,00	✔	11,17 €
CD2242	1,60	11,60	8,50	40,50	6,76	21,60	146,00	✔	11,17 €
CD2243	1,60	11,60	12,50	58,50	4,58	32,00	146,00	✔	11,17 €
CD2244	1,60	11,60	18,50	85,00	3,10	47,10	146,00	✔	11,17 €
CD2245	1,60	14,10	3,50	24,00	8,38	14,00	116,00	✔	11,17 €
CD2246	1,60	14,10	5,50	36,00	5,35	21,90	116,00	✔	11,17 €
CD2247	1,60	14,10	8,50	53,50	3,47	33,40	116,00	✔	11,17 €
CD2248	1,60	14,10	12,50	78,00	2,34	50,00	116,00	✔	11,17 €
CD2249	1,60	14,10	18,50	115,00	1,58	75,10	116,00	✔	11,17 €
CD2250	1,60	17,60	3,50	34,00	3,99	23,00	91,00	✔	11,17 €
CD2251	1,60	17,60	5,50	51,50	2,53	36,00	91,00	✔	11,17 €
CD2252	1,60	17,60	8,50	77,50	1,65	55,30	91,00	✔	11,17 €
CD2253	1,60	17,60	12,50	110,00	1,12	78,80	91,00	✔	11,17 €
CD2254	1,60	17,60	18,50	165,00	0,76	120,00	91,00	✔	11,17 €
CD2255	1,60	21,60	3,50	48,00	2,04	35,60	73,00	✔	9,72 €
CD2256	1,60	21,60	5,50	73,50	1,31	55,90	73,00	✔	9,72 €
CD2257	1,60	21,60	8,50	110,00	0,85	84,50	73,00	✔	9,72 €
CD2258	1,60	21,60	12,50	165,00	0,58	129,00	73,00	✔	16,33 €
CD2259	1,60	21,60	18,50	240,00	0,39	188,00	73,00	✔	16,33 €
CD2260	2,00	12,00	3,50	18,00	40,00	6,80	273,00	✔	10,14 €
CD2261	2,00	12,00	5,50	26,50	25,52	10,90	273,00	✔	10,14 €
CD2262	2,00	12,00	8,50	38,50	16,51	16,50	273,00	✔	10,14 €
CD2263	2,00	12,00	12,50	55,00	11,20	24,40	273,00	✔	10,14 €
CD2264	2,00	12,00	18,50	79,50	7,67	36,10	273,00	✔	10,14 €
CD2265	2,00	14,50	3,50	22,50	20,55	10,80	218,00	✔	10,14 €
CD2266	2,00	14,50	5,50	33,00	13,06	16,60	218,00	✔	10,14 €
CD2267	2,00	14,50	8,50	49,50	8,43	26,00	218,00	✔	10,14 €
CD2268	2,00	14,50	12,50	71,00	5,75	38,00	218,00	✔	11,18 €
CD2269	2,00	14,50	18,50	105,00	3,88	57,80	218,00	✔	11,18 €

*Depending on availability - Dimensions in mm

- ***Material:***
  Piano springs: Stainless steel conforming to DIN17224, Stainless steel 1.4310 (301)
- *Right hand wound*
- *Ends:*
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm, squared and ground
- *Operating temperature : 60°C max*
- *These springs are recommended for static or medium dynamic loads*
- *Tolerances: All the dimensions and load values given conform to DIN2095 (Grade 2)*

25+ pieces Contact us





Info.

- *These springs are not preset*
- *Free length Lo will reduce slightly after first operations under load*
- *For custom made springs, please contact us (Minimum quantity may apply)*

DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-5%	-20%	On request

Part number	Wire Ød	External ØDo	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2270	2,00	18,00	3,5	30,00	9,77	17,50	170,00	✔	8,81 €
CD2271	2,00	18,00	5,5	45,00	6,22	27,30	170,00	✔	8,81 €
CD2272	2,00	18,00	8,5	68,00	4,03	42,50	170,00	✔	8,81 €
CD2273	2,00	18,00	12,5	98,00	2,74	62,10	170,00	✔	9,09 €
CD2274	2,00	18,00	18,5	145,00	1,86	93,60	170,00	✔	9,64 €
CD2275	2,00	22,00	3,5	41,00	5,01	27,40	137,00	✔	8,81 €
CD2276	2,00	22,00	5,5	62,00	3,19	42,80	137,00	✔	8,81 €
CD2277	2,00	22,00	8,5	94,00	2,05	66,40	137,00	✔	9,09 €
CD2278	2,00	22,00	12,5	135,00	1,40	96,20	137,00	✔	9,64 €
CD2279	2,00	22,00	18,5	200,00	0,95	144,00	137,00	-	9,64 €
CD2280	2,00	27,00	3,5	58,00	2,56	43,00	110,00	✔	8,81 €
CD2281	2,00	27,00	5,5	88,50	1,63	67,10	110,00	-	9,09 €
CD2282	2,00	27,00	8,5	135,00	1,06	104,00	110,00	✔	9,64 €
CD2283	2,00	27,00	12,5	195,00	0,71	151,00	110,00	-	9,64 €
CD2284	2,00	27,00	18,5	290,00	0,49	227,00	110,00	-	10,22 €
CD2285	2,20	11,00	3,5	16,20	85,89	3,50	292,00	-	9,10 €
CD2286	2,20	11,00	5,5	23,00	54,58	5,30	292,00	-	9,10 €
CD2287	2,20	11,00	9,5	36,50	31,67	9,10	292,00	-	9,10 €
CD2288	2,20	11,00	15,5	56,80	19,38	15,10	292,00	-	9,10 €

**Depending on availability - Dimensions in mm*


Compression spring DIN 2095


CD Ø2,2-Ø3,2

Stainless steel piano wire

- ***Material :***
  Piano springs: Stainless steel conforming to DIN17224, Stainless steel 1.4310 (301)
- *Right hand wound*
- *Ends:*
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm, squared and ground
- *Operating temperature : 60°C max*
- *These springs are recommended for static or medium dynamic loads*
- *Tolerances: All the dimensions and load values given conform to DIN2095 (Grade 2)*

25+ pieces Contact us





Info.

- *These springs are not preset*
- *Free length Lo will reduce slightly after first operations under load*
- *For custom made springs, please contact us (Minimum quantity may apply)*

DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-5%	-20%	On request

Part number	Wire Ød	External ØDo	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2289	2,20	15,00	3,50	20,00	27,88	7,60	222,00	✔	9,10 €
CD2290	2,20	15,00	5,50	30,20	17,77	12,50	222,00	✔	9,10 €
CD2291	2,20	15,00	9,50	48,90	10,27	21,60	222,00	✔	9,10 €
CD2292	2,20	24,00	3,50	39,20	5,64	25,00	142,00	✔	9,10 €
CD2293	2,20	24,00	5,50	59,10	3,60	39,50	142,00	✔	9,10 €
CD2294	2,50	15,00	3,50	22,00	50,12	8,00	402,00	✔	9,34 €
CD2295	2,50	15,00	5,50	32,00	31,93	12,50	402,00	✔	9,34 €
CD2296	2,50	15,00	8,50	47,50	20,64	19,70	402,00	-	9,34 €
CD2297	2,50	15,00	12,50	67,50	13,98	28,80	402,00	✔	9,34 €
CD2298	2,50	15,00	18,50	98,00	9,43	42,90	402,00	✔	9,34 €
CD2299	2,50	18,50	3,50	27,50	23,83	12,90	313,00	✔	9,34 €
CD2300	2,50	18,50	5,50	41,00	15,16	20,50	313,00	✔	9,34 €
CD2301	2,50	18,50	8,50	61,00	9,85	31,70	313,00	✔	9,34 €
CD2302	2,50	18,50	12,50	88,00	6,68	46,90	313,00	✔	9,34 €
CD2303	2,50	18,50	18,50	130,00	4,51	71,10	313,00	✔	9,66 €
CD2304	2,50	22,50	3,50	36,00	12,21	20,50	251,00	✔	9,34 €
CD2305	2,50	22,50	5,50	54,00	7,77	32,10	251,00	✔	9,34 €
CD2306	2,50	22,50	8,50	81,50	5,02	50,00	251,00	✔	9,34 €
CD2307	2,50	22,50	12,50	120,00	3,42	75,70	251,00	✔	9,66 €
CD2308	2,50	22,50	18,50	175,00	2,31	111,00	251,00	✔	9,66 €

**Depending on availability - Dimensions in mm*

Part number	Wire Ød	External ØDo	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2309	2,50	27,50	3,5	49,00	6,26	32,20	200,00	✔	9,34 €
CD2310	2,50	27,50	5,5	74,50	3,99	50,50	200,00	✔	9,34 €
CD2311	2,50	27,50	8,5	115,00	2,58	80,20	200,00	✔	9,34 €
CD2312	2,50	27,50	12,5	165,00	1,75	116,00	200,00	✔	9,66 €
CD2313	2,50	27,50	18,5	240,00	1,19	169,00	200,00	-	9,66 €
CD2314	2,50	34,50	3,5	71,50	2,99	52,20	156,00	✔	9,66 €
CD2315	2,50	34,50	5,5	110,00	1,91	82,10	156,00	✔	9,66 €
CD2316	2,50	34,50	8,5	170,00	1,23	129,00	156,00	✔	9,66 €
CD2317	2,50	34,50	12,5	245,00	0,83	87,00	156,00	-	9,66 €
CD2318	2,50	34,50	18,5	360,00	0,57	276,00	156,00	-	9,97 €
CD2319	2,80	14,00	3,5	20,50	109,50	4,10	446,00	-	10,22 €
CD2320	2,80	14,00	5,5	29,00	66,48	6,70	446,00	-	10,22 €
CD2321	2,80	14,00	9,5	45,90	40,27	11,10	446,00	-	10,22 €
CD2322	2,80	14,00	15,5	71,40	24,68	18,00	446,00	-	10,22 €
CD2323	2,80	20,00	3,5	27,20	30,16	11,00	326,00	✔	11,35 €
CD2324	2,80	20,00	5,5	39,50	19,20	17,00	326,00	-	10,22 €
CD2325	2,80	20,00	9,5	64,20	11,11	29,00	326,00	✔	10,22 €
CD2326	2,80	30,00	3,5	47,00	7,63	29,00	222,00	4	10,22 €
CD2327	2,80	30,00	5,5	70,70	4,85	45,00	222,00	4	10,22 €
CD2328	3,20	19,20	3,5	27,50	63,84	9,70	620,00	-	10,22 €
CD2329	3,20	19,20	5,5	40,00	40,69	15,10	620,00	-	10,22 €
CD2330	3,20	19,20	8,5	59,00	26,36	23,60	620,00	-	10,22 €
CD2331	3,20	19,20	12,5	83,50	17,86	34,50	620,00	4	10,22 €
CD2332	3,20	19,20	18,5	120,00	12,13	50,60	620,00	-	10,22 €
CD2333	3,20	23,20	3,5	33,50	32,77	15,00	496,00	-	10,22 €
CD2334	3,20	23,20	5,5	49,50	20,80	23,60	496,00	✔	10,22 €
CD2335	3,20	23,20	8,5	74,00	13,48	36,90	496,00	✔	10,22 €
CD2336	3,20	23,20	12,5	105,00	9,18	53,40	496,00	✔	10,22 €
CD2337	3,20	23,20	18,5	155,00	6,19	81,80	496,00	✔	10,22 €
CD2338	3,20	28,20	3,5	42,50	16,68	23,40	396,00	✔	10,22 €
CD2339	3,20	28,20	5,5	63,50	10,62	37,20	396,00	✔	10,22 €
CD2340	3,20	28,20	8,5	94,50	6,89	57,40	396,00	✔	10,22 €
CD2341	3,20	28,20	12,5	135,00	4,68	83,40	396,00	✔	10,22 €
CD2342	3,20	28,20	18,5	200,00	3,16	127,00	396,00	✔	10,55 €
CD2343	3,20	35,20	3,5	58,50	8,00	38,70	310,00	4	10,22 €
CD2344	3,20	35,20	5,5	88,50	5,08	61,10	310,00	-	10,22 €
CD2345	3,20	35,20	8,5	135,00	3,28	96,20	310,00	✔	10,55 €
CD2346	3,20	35,20	12,5	190,00	2,24	136,00	310,00	-	10,55 €
CD2347	3,20	35,20	18,5	280,00	1,51	203,00	310,00	-	10,55 €
CD2348	3,20	43,20	3,5	82,00	4,09	60,80	247,00	-	10,22 €
CD2349	3,20	43,20	5,5	125,00	2,60	95,30	247,00	-	10,22 €
CD2350	3,20	43,20	8,5	190,00	1,68	148,00	247,00	-	10,22 €
CD2351	3,20	43,20	12,5	275,00	1,14	216,00	247,00	-	10,55 €
CD2352	3,20	43,20	18,5	405,00	0,77	321,00	247,00	-	10,55 €

*Depending on availability - Dimensions in mm


Compression spring DIN 2095


CD
Ø4-Ø6,3

Stainless steel piano wire

- ***Material :***
  Piano springs: Stainless steel conforming to DIN17224, Stainless steel 1.4310 (301)
- *Right hand wound*
- *Ends:*
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm, squared and ground
- *Operating temperature : 60°C max*
- *These springs are recommended for static or medium dynamic loads*
- *Tolerances: All the dimensions and load values given conform to DIN2095 (Grade 2)*

25+ pieces Contact us





Info.

- *These springs are not preset*
- *Free length Lo will reduce slightly after first operations under load*
- *For custom made springs, please contact us (Minimum quantity may apply)*

DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-5%	-20%	On request

Part number	Wire Ød	External ØDo	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2353	4,00	24,00	3,50	33,50	79,94	11,30	918,00	✔	35,20 €
CD2354	4,00	24,00	5,50	49,00	50,87	18,00	918,00	✔	35,20 €
CD2355	4,00	24,00	8,50	72,00	32,93	27,80	918,00	✔	35,20 €
CD2356	4,00	24,00	12,50	105,00	22,41	43,30	918,00	-	34,06 €
CD2357	4,00	24,00	18,50	150,00	15,07	62,30	918,00	-	34,02 €
CD2358	4,00	29,00	3,50	41,00	40,93	18,10	732,00	-	33,79 €
CD2359	4,00	29,00	5,50	60,50	26,02	28,30	732,00	✍	33,79 €
CD2360	4,00	29,00	8,50	89,50	16,84	43,50	732,00	✔	33,79 €
CD2361	4,00	29,00	12,50	130,00	1,46	65,50	732,00	✔	36,69 €
CD2362	4,00	29,00	18,50	185,00	7,75	92,90	732,00	-	36,69 €
CD2363	4,00	36,00	3,50	53,50	19,54	29,50	572,00	-	33,79 €
CD2364	4,00	36,00	5,50	79,50	12,39	46,20	572,00	✔	33,79 €
CD2365	4,00	36,00	8,50	120,00	8,03	72,80	572,00	✔	33,79 €
CD2366	4,00	36,00	12,50	170,00	5,45	104,00	572,00	4	33,79 €
CD2367	4,00	36,00	18,50	250,00	3,69	156,00	572,00	-	34,75 €
CD2368	4,00	44,00	3,50	71,00	10,02	45,80	458,00	✔	33,79 €
CD2369	4,00	44,00	5,50	105,00	6,36	69,90	458,00	-	33,79 €
CD2370	4,00	44,00	8,50	160,00	4,11	110,00	458,00	-	34,20 €
CD2371	4,00	44,00	12,50	235,00	2,80	165,00	458,00	-	34,85 €
CD2372	4,00	44,00	18,50	340,00	1,89	240,00	458,00	-	34,85 €

**Depending on availability - Dimensions in mm*

Part number	Wire Ød	External ØDo	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Stock*	Price each 1 to 4
CD2373	4,00	44,00	18,50	340,00	1,89	240,00	458,00	-	33,79 €
CD2374	4,00	54,00	3,50	99,00	5,11	71,60	367,00	-	33,79 €
CD2375	4,00	54,00	5,50	150,00	3,26	111,00	367,00	-	34,20 €
CD2376	4,00	54,00	8,50	230,00	2,10	175,00	367,00	-	34,85 €
CD2377	4,00	54,00	12,50	335,00	1,43	257,00	367,00	-	35,94 €
CD2378	4,00	54,00	18,50	490,00	0,97	379,00	367,00	-	33,79 €
CD2379	5,00	30,00	3,50	41,00	100,23	13,40	1348,00	-	33,79 €
CD2380	5,00	30,00	5,50	60,00	63,59	21,50	1348,00	-	34,70 €
CD2381	5,00	30,00	8,50	87,50	41,11	32,60	1348,00	-	34,70 €
CD2382	5,00	30,00	12,50	125,00	27,99	48,30	1348,00	-	37,17 €
CD2383	5,00	30,00	18,50	180,00	18,87	71,00	1348,00	-	33,79 €
CD2384	5,00	37,00	3,50	51,00	47,59	22,30	1053,00	✔	34,70 €
CD2385	5,00	37,00	5,50	75,00	30,31	34,80	1053,00	-	34,70 €
CD2386	5,00	37,00	8,50	110,00	19,63	52,50	1053,00	-	35,10 €
CD2387	5,00	37,00	12,50	160,00	13,30	79,50	1053,00	-	37,03 €
CD2388	5,00	37,00	18,50	230,00	9,01	115,00	1053,00	-	33,79 €
CD2389	5,00	45,00	3,50	64,00	24,34	34,40	843,00	-	34,75 €
CD2390	5,00	45,00	5,50	95,50	15,49	54,40	843,00	-	35,10 €
CD2391	5,00	45,00	8,50	140,00	10,02	81,60	843,00	-	36,13 €
CD2392	5,00	45,00	12,50	205,00	6,82	124,00	843,00	-	37,48 €
CD2393	5,00	45,00	18,50	300,00	4,60	184,00	843,00	-	34,75 €
CD2394	5,00	55,00	3,50	85,00	12,46	54,10	674,00	-	34,75 €
CD2395	5,00	55,00	5,50	130,00	7,94	86,80	674,00	-	36,13 €
CD2396	5,00	55,00	8,50	195,00	5,14	133,00	674,00	-	37,17 €
CD2397	5,00	55,00	12,50	280,00	3,50	194,00	674,00	-	38,62 €
CD2398	5,00	55,00	18,50	410,00	2,36	287,00	674,00	-	34,75 €
CD2399	5,00	68,00	3,50	120,00	6,24	87,70	535,00	-	35,10 €
CD2400	5,00	68,00	5,50	180,00	3,98	135,00	535,00	-	37,48 €
CD2401	5,00	68,00	8,50	275,00	2,57	210,00	535,00	-	37,49 €
CD2402	5,00	68,00	12,50	395,00	1,74	304,00	535,00	-	40,71 €
CD2403	5,00	68,00	18,50	585,00	1,18	455,00	535,00	-	34,70 €
CD2404	6,30	38,30	3,50	50,00	120,40	15,00	1990,00	-	34,70 €
CD2405	6,30	38,30	5,50	75,00	76,50	26,00	1990,00	-	37,48 €
CD2406	6,30	38,30	8,50	110,00	49,60	41,00	1990,00	-	37,49 €
CD2407	6,30	38,30	12,50	155,00	32,70	58,00	1990,00	-	39,56 €
CD2408	6,30	38,30	18,50	225,00	22,80	88,00	1990,00	-	34,70 €
CD2409	6,30	46,30	3,50	60,00	61,60	24,00	1590,00	-	36,13 €
CD2410	6,30	46,30	5,50	90,00	39,20	40,00	1590,00	-	37,03 €
CD2411	6,30	46,30	8,50	135,00	25,30	63,00	1590,00	-	39,20 €
CD2412	6,30	46,30	12,50	195,00	17,30	95,00	1590,00	-	42,03 €
CD2413	6,30	46,30	18,50	280,00	11,60	137,00	1590,00	-	34,70 €
CD2414	6,30	56,30	3,50	80,00	31,50	42,00	1270,00	-	37,49 €
CD2415	6,30	56,30	5,50	115,00	20,00	62,00	1270,00	-	38,49 €
CD2416	6,30	56,30	8,50	175,00	13,00	100,00	1270,00	-	40,71 €
CD2417	6,30	56,30	12,50	250,00	8,90	145,00	1270,00	-	42,01 €

*Depending on availability - Dimensions in mm

Compression spring DIN 2095


StaDIN


CD Ø6,3-Ø10

Stainless steel piano wire

- ***Material :***
  Piano springs: Stainless steel conforming to DIN17224, Stainless steel 1.4310 (301)
- *Right hand wound*
- *Ends:*
  Wire ≤ 0.8mm squared, not ground
  Wire > 0.8mm, squared and ground
- *Operating temperature : 60°C max*
- *These springs are recommended for static or medium dynamic loads*
- *Tolerances: All the dimensions and load values given conform to DIN2095 (Grade 2)*

25+ pieces Contact us





Info.

- *These springs are not preset*
- *Free length Lo will reduce slightly after first operations under load*
- *For custom made springs, please contact us (Minimum quantity may apply)*

DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-5%	-20%	On request

Part number	Wire Ød	External Ø Do	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Price each 1 to 4
CD2418	6,30	56,30	18,50	365,00	5,90	215,00	1270,00	37,49 €
CD2419	6,30	69,30	3,5	105,00	15,70	65,00	1010,00	38,49 €
CD2420	6,30	69,30	5,5	155,00	10,50	99,00	1010,00	40,71 €
CD2421	6,30	69,30	8,5	253,00	6,50	155,00	1010,00	41,92 €
CD2422	6,30	69,30	12,5	340,00	4,40	227,00	1010,00	44,48 €
CD2423	6,30	69,30	18,5	500,00	3,00	339,00	1010,00	38,49 €
CD2424	6,30	86,30	3,5	145,00	7,70	103,00	800,00	38,09 €
CD2425	6,30	86,30	5,5	220,00	4,90	160,00	800,00	40,66 €
CD2426	6,30	86,30	8,5	335,00	3,20	260,00	800,00	44,48 €
CD2427	6,30	86,30	12,5	490,00	2,20	370,00	800,00	47,93 €
CD2428	6,30	86,30	18,5	720,00	1,50	548,00	800,00	38,02 €
CD2429	8,00	48,00	3,5	65,00	159,00	21,00	3030,00	39,87 €
CD2430	8,00	48,00	5,5	90,00	102,20	29,00	3030,00	42,18 €
CD2431	8,00	48,00	8,5	135,00	66,10	48,00	3030,00	44,66 €
CD2432	8,00	48,00	12,5	190,00	44,70	68,00	3030,00	46,41 €
CD2433	8,00	48,00	18,5	275,00	30,10	101,00	3030,00	41,84 €
CD2434	8,00	58,00	3,5	75,00	81,90	30,00	2425,00	39,83 €
CD2435	8,00	58,00	5,5	110,00	52,20	46,00	2425,00	43,39 €
CD2436	8,00	58,00	8,5	160,00	33,70	70,00	2425,00	44,65 €
CD2437	8,00	58,00	12,5	230,00	22,90	103,00	2425,00	48,44 €

Dimensions in mm

Part number	Wire Ød	External Ø Do	N° active coils	Free length Lo	Rate C N/mm	Max. deflection Sn (mm)	Max. load Fn (N)	Price each 1 to 4
CD2438	8,00	71,00	3,50	95,00	41,00	48,00	1920,00	40,71 €
CD2439	8,00	71,00	5,50	140,00	26,00	74,00	1920,00	42,01 €
CD2440	8,00	71,00	8,50	205,00	16,80	112,00	1920,00	44,98 €
CD2441	8,00	71,00	12,50	300,00	11,40	169,00	1920,00	47,83 €
CD2442	8,00	71,00	18,50	435,00	8,00	248,00	1920,00	74,57 €
CD2443	8,00	88,00	3,50	125,00	19,90	76,00	1515,00	42,01 €
CD2444	8,00	88,00	5,50	180,00	12,70	111,00	1515,00	44,98 €
CD2445	8,00	88,00	8,50	285,00	8,30	186,00	1515,00	46,00 €
CD2446	8,00	88,00	12,50	410,00	5,60	271,00	1515,00	53,38 €
CD2447	8,00	88,00	18,50	600,00	3,80	401,00	1515,00	116,46 €
CD2448	8,00	108,00	3,50	170,00	10,20	118,00	1210,00	43,78 €
CD2449	8,00	108,00	5,50	260,00	6,50	187,00	1210,00	44,48 €
CD2450	8,00	108,00	8,50	390,00	4,20	286,00	1210,00	48,19 €
CD2451	8,00	108,00	12,50	570,00	2,80	423,00	1210,00	100,95 €
CD2452	8,00	108,00	18,50	835,00	2,00	625,00	1210,00	153,39 €
CD2453	10,00	60,00	3,50	75,00	200,00	20,00	4470,00	39,69 €
CD2454	10,00	60,00	5,50	110,00	127,00	34,00	4470,00	44,40 €
CD2455	10,00	60,00	8,50	165,00	82,20	56,00	4470,00	46,91 €
CD2456	10,00	60,00	12,50	230,00	55,90	78,00	4470,00	53,04 €
CD2457	10,00	60,00	18,50	335,00	37,80	118,00	4470,00	96,37 €
CD2458	10,00	73,00	3,50	96,00	99,60	39,00	3540,00	43,78 €
CD2459	10,00	73,00	5,50	135,00	63,60	56,00	3540,00	44,98 €
CD2460	10,00	73,00	8,50	200,00	41,10	88,00	3540,00	50,02 €
CD2461	10,00	73,00	12,50	285,00	28,00	120,00	3540,00	83,82 €
CD2462	10,00	73,00	18,50	410,00	18,90	185,00	3540,00	118,92 €
CD2463	10,00	90,00	3,50	115,00	49,00	56,00	2790,00	44,48 €
CD2464	10,00	90,00	5,50	175,00	30,90	92,00	2790,00	48,19 €
CD2465	10,00	90,00	8,50	255,00	20,10	136,00	2790,00	79,83 €
CD2466	10,00	90,00	12,50	370,00	13,70	203,00	2790,00	101,27 €
CD2467	10,00	90,00	18,50	540,00	9,30	302,00	2790,00	144,21 €
CD2468	10,00	110,00	3,50	150,00	24,90	87,00	2230,00	46,25 €
CD2469	10,00	110,00	5,50	230,00	16,30	141,00	2230,00	46,42 €
CD2470	10,00	110,00	8,50	345,00	10,30	217,00	2230,00	93,61 €
CD2471	10,00	110,00	12,50	500,00	7,00	320,00	2230,00	118,92 €
CD2472	10,00	110,00	18,50	730,00	4,70	472,00	2230,00	153,39 €
CD2473	10,00	135,00	3,50	205,00	12,80	138,00	1790,00	50,02 €
CD2474	10,00	135,00	5,50	315,00	8,20	220,00	1790,00	83,82 €
CD2475	10,00	135,00	8,50	475,00	5,20	338,00	1790,00	118,92 €
CD2476	10,00	135,00	12,50	690,00	3,60	497,00	1790,00	144,21 €
CD2477	10,00	135,00	18,50	1015,00	2,40	738,00	1790,00	153,39 €

Dimensions in mm

Our other products


DPAR_DKON


Conical elasto buffer, Steel


LVT

Miniature motorised actuator 2A, 2 ampers


SLB

Indexing plunger, stainless steel


LAT4

4A motorised linear actuator, 4 amperes


DOMI50

Connecting kits, XY linking kit


PSG05HC

Skive hobbed spur gears - precision range, Case hardened steel 20NCD2


CHB

Feet, For CHB gearbox


MRASSeco

Low cost stainless steel quick link, Stainless steel


RPP5

RPP heavy duty timing belt, RPP5


BIM

Indexing plunger mini, miniature


KB_UU

Closed linear precision bearing, Precision - steel


EML

Stainless steel hexagonal headed thumb nut, Lobed handscrew

Complementary products


D19_D29

Compression springs in metre length steel, by the metre


R206

Die spring ISO10243, Extra-heavy


CDC

Conical compression spring, Conical


R205

Die spring ISO10243, Heavy