Decorative asymetric screwed hinge

Pla

CHAEA Polyamide

- ***Screwed hinge***
- *Materials :*
  hinges glass fibre reinforced polyamide (30%)
  sealed pin : stainless steel 316L
- *Square and symetrical versions also available*



Advantage

- *Aesthetic design*
- *Max opening angle 270°*





Part number	Tensile strength	Shear strength	Screw torque (Nm)
CHAE4060A/PA	2200	2300	4
CHAE4080A/PA	2200	2300	4
CHAE5075A/PA	3600	2500	8
CHAE6090A/PA	5100	4200	8

Dimensions en mm

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	E	F	G	H	ØS	For screw	Stock*	Price each 1 to 5
CHAE4060A/PA	40	60	5,2	4	5,7	13,5	25	19	5,3	M4	✔	7,94 €
CHAE4080A/PA	40	80	5,2	4	5,7	14,5	25	38	5,3	M4	✔	8,15 €
CHAE5075A/PA	50	75	5,9	5	6,4	16	30	24	6,4	M6	✔	10,09 €
CHAE6090A/PA	60	90	6,5	6	7	18	36	30	6,4	M6	✔	14,14 €

Dimensions in mm

Our other products

PW_PWG05

Wheel - precision range, Bronze

BEF

Bearing housing for miniature ballscrew, Bearing housing

COA-COG

Surface mounting plate, Surface mounting plate for ball joint



PMC150_M16

Anti-vibration machine mount, Square base plate



NSB

Standard linear bearing housing, Closed - Long

CAMTH

Thermal camera for use with smartphone, iOS and Android

CHARcav

Spring hinge, to install

PM2

Worm and wheel set, Bronze

SHW

Plain washer, A2 Stainless steel

HLA19

Right angle spiro bevel gearbox, Up to

PR125

Articulated foot Ø123, Ø 123

LC

Friction clutch, 190 to 1800 Nm

Complementary products

CHAE6555

Decorative screwed hinge, Aluminium

CHAM5270SS

Marine hinge for welding/screw mounting, Marine

CHAEpac

Square decorative screwed hinges, carbon fibre reinforced