


Our other products



LAT4
4A motorised linear actuator, 4 amperes



RBS
Dynamic washer
DIN2093, Steel



MDB_MTB
Moulded plastic bevel gear (nylon), 3:1



SLBE
Indexing plunger -
Spacer, Spacer for
SLB and SLBS index
bolts



AXTR
Axle for tensioner pulley, Shaft



Gal-cardan
Single universal joint
eco series, Low duty



BABFCFO
Ball pin socket,
Mounting collar with a
oval flange



PTKFss
Fixable foot for the
food industry,
Stainless steel - 3-A
standard



M
Bellows cover,
Accessory:



NT63
Spur gear coaxial
gearbox, from 8 to 20
Nm - Inline



WW10
Drylin® W slide, slide
assembly



BLHB30
Right angled gearbox,
bored shafts, up to
4.4 Nm

Complementary products



CHMX_CHMDX
Shaft for worm and
wheel reducer CHMR
and CHM, CHMR and
CHM gearbox...



CHMBR
Reaction arm, CHM
and CHMR gear
reducers reaction arm



P30
Worm and wheel gear
reducer, up to 8.80
Nm