

Plastic clamping lever



PCLAM
PCLAMSS

With threaded insert

- Clamping lever with threaded insert

- Materials:


Insert: steel (class 5.8) or stainless steel (303)

Handle: glass fibre reinforced polyamide plastic

Mechanism: splined diecast zinc

- Finish: Blackened steel

- Color : black



Uses

- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Thread	X	T	ØD	ØD1	H	H1	H2
PCLA01M4	M4	9	10.0	13.0	24.5	4.0	15.0	
PCLA01M5	M5	9	10.0	13.0	24.5	4.0	15.0	
PCLA01M6	M6	9	10.0	13.0	24.5	4.0	15.0	
PCLA02M6	M6	12	13.5	18.0	28.5	6.5	17.5	
PCLA02M8	M8	12	13.5	18.0	28.5	6.5	17.5	
PCLA03M8	M8	14	16.0	21.5	37.0	10.0	24.0	
PCLA03M10	M10	14	16.0	21.5	37.0	10.0	24.0	
PCLA04M10	M10	17	19.0	25.5	43.0	10.0	26.0	
PCLA04M12	M12	17	19.0	25.5	43.0	10.0	26.0	
PCLA05M12	M12	23	23.0	30.0	49.0	12.0	33.0	
PCLA05M16	M16	23	23.0	30.0	49.0	12.0	33.0	

Part number	Thread		H3	H4	A	A1	B	Stock*		Price each 1 to 5	
	Steel	Stainless						Steel	StS	Steel	Stainless
PCLA01M4	-	-	30,0	33,5	40	47,0	7,5	✓	-	9,23 €	-
PCLA01M5	PCLA01M5SS	-	30,0	33,5	40	47,0	7,5	✓	-	9,23 €	14,39 €
PCLA01M6	PCLA01M6SS	-	30,0	33,5	40	47,0	7,5	✓	-	9,23 €	14,39 €
PCLA02M6	PCLA02M6SS	-	41,5	45,5	65	75,0	9,5	✓	-	10,91 €	16,95 €
PCLA02M8	PCLA02M8SS	-	41,5	45,5	65	75,0	9,5	✓	✓	10,91 €	16,95 €
PCLA03M8	PCLA03M8SS	-	53,5	58,0	80	91,5	11,0	✓	-	13,39 €	20,89 €
PCLA03M10	PCLA03M10SS	-	53,5	58,0	80	91,5	11,0	✓	-	13,39 €	20,89 €
PCLA04M10	PCLA04M10SS	-	61,0	66,0	95	109,0	13,0	✓	-	17,15 €	30,19 €
PCLA04M12	PCLA04M12SS	-	61,0	66,0	95	109,0	13,0	✓	-	17,15 €	30,19 €
PCLA05M12	PCLA05M12SS	-	72,0	77,0	110	126,0	15,5	✓	-	20,69 €	36,41 €
PCLA05M16	PCLA05M16SS	-	72,0	77,0	110	126,0	15,5	✓	-	20,69 €	36,41 €

*Depending on availability - Dimensions in mm



Plastic clamping lever

With threaded spindle

PCLAT
PCLATss

- Clamping lever with threaded spindle and tapered tip as per DIN 78

- Materials:

Spindle: steel (class 5.8)

or stainless steel (303)

Handle: glass fibre reinforced polyamide plastic

Mechanism: splined diecast zinc

- Finish: Blackened steel, fine grained surface

- Fine grained mat surface finish

- Colour: black

- Working temp.: -50°C to +130°C

Uses


- The lever is normally in a locked position

- Raise the handle to release the lever and turn to required position

- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number		Threaded bolt X	H1	L			ØD	ØD1	H
Steel	Stainless			Steel	Stainless				
PCLA01T5	PCLA01T5SS	M5	4,0	50	25	10,0	13,0	24,5	
PCLA01T6	PCLA01T6SS	M6	4,0	50	50	10,0	13,0	24,5	
PCLA02T8	PCLA02T8SS	M8	6,5	60	60	13,5	18,0	28,5	
PCLA02T10	PCLA02T10SS	M10	6,5	60	60	13,5	18,0	28,5	
PCLA03T10	PCLA03T10SS	M10	10,0	60	60	16,0	21,5	37,0	
PCLA04T10	-	M10	10,0	90	-	19,0	25,5	43,0	
PCLA04T12	PCLA04T12SS	M12	10,0	90	60	19,0	25,5	43,0	
PCLA05T12	-	M12	12,0	90	-	23,0	30,0	49,0	
PCLA05T16	PCLA05T16SS	M16	12,0	90	60	23,0	30,0	49,0	

Part number		Stock*							Price each 1 to 5		
Steel	Stainless	A	H2	H3	H4	A1	B	Steel	Stainless		
PCLA01T5	PCLA01T5SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	11,21 €	15,35 €
PCLA01T6	PCLA01T6SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	11,21 €	16,59 €
PCLA02T8	PCLA02T8SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	13,07 €	19,85 €
PCLA02T10	PCLA02T10SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	13,07 €	19,85 €
PCLA03T10	PCLA03T10SS	80	24,0	53,5	58,0	91,5	11,0	✓	✓	16,13 €	24,59 €
PCLA04T10	-	95	26,0	61,0	66,0	109,0	13,0	✓	-	21,37 €	-
PCLA04T12	PCLA04T12SS	95	26,0	61,0	66,0	109,0	13,0	✓	✓	21,37 €	35,99 €
PCLA05T12	-	110	33,0	72,0	77,0	126,0	15,5	-	-	26,47 €	-
PCLA05T16	PCLA05T16SS	110	33,0	72,0	77,0	126,0	15,5	-	-	26,47 €	42,55 €

*Depending on availability - Dimensions in mm

Zamak clamping lever



CLB_M CLB_{MSS}

With threaded insert

- Clamping lever with threaded insert

- Materials:


Insert: steel (class5.8)
or stainless steel (303)

Handle: diecast zinc, complies
with DIN 1743

- Finish:

Steel: blackened steel

Handle : black plastic coating



Uses

- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Thread		H3	H4	A	A1	B	N° of teeth	H	H1	H2
	X	T									
CLB01M4	M4	9	10,0	13,0	14,5	24,5	4,0	15,0			
CLB01M5	M5	9	10,0	13,0	14,5	24,5	4,0	15,0			
CLB01M6	M6	9	10,0	13,0	14,5	24,5	4,0	15,0			
CLB02M6	M6	12	13,5	18,0	19,5	28,5	6,5	17,5			
CLB02M8	M8	12	13,5	18,0	19,5	28,5	6,5	17,5			
CLB03M8	M8	14	16,0	21,5	23,0	37,0	10,0	24,0			
CLB03M10	M10	14	16,0	21,5	23,0	37,0	10,0	24,0			
CLB04M10	M10	17	19,0	25,5	27,5	43,0	10,0	26,0			
CLB04M12	M12	17	19,0	25,5	27,5	43,0	10,0	26,0			
CLB05M12	M12	23	23,0	30,0	32,5	49,0	12,0	33,0			
CLB05M16	M16	23	23,0	30,0	32,5	49,0	12,0	33,0			

Part number	Steel		H3	H4	A	A1	B	N° of teeth	Stock*		Price each 1 to 5	
	Steel	Sts							Steel	Sts		
CLB01M4	-	-	30,0	33,5	40	47,0	7,5	16	-	-	13,04 €	-
CLB01M5	CLB01M5SS	-	30,0	33,5	40	47,0	7,5	16	✓	-	13,04 €	18,32 €
CLB01M6	CLB01M6SS	-	30,0	33,5	40	47,0	7,5	16	✓	-	13,04 €	18,32 €
CLB02M6	CLB02M6SS	-	41,5	45,5	65	75,0	9,5	20	✓	-	16,48 €	22,78 €
CLB02M8	CLB02M8SS	-	41,5	45,5	65	75,0	9,5	20	✓	-	16,48 €	22,78 €
CLB03M8	CLB03M8SS	-	53,5	58,0	80	91,5	11,0	22	✓	-	18,05 €	25,82 €
CLB03M10	CLB03M10SS	-	53,5	58,0	80	91,5	11,0	22	✓	-	18,05 €	25,82 €
CLB04M10	CLB04M10SS	-	61,0	66,0	95	109,0	13,0	24	✓	-	20,43 €	33,59 €
CLB04M12	CLB04M12SS	-	61,0	66,0	95	109,0	13,0	24	✓	-	20,43 €	33,59 €
CLB05M12	CLB05M12SS	-	72,0	77,0	110	126,0	15,5	26	✓	-	25,36 €	40,91 €
CLB05M16	CLB05M16SS	-	72,0	77,0	110	126,0	15,5	26	✓	-	25,36 €	41,00 €

*Depending on availability - Dimensions in mm

With threaded spindle

CLBT CLBTss

- Clamping lever with threaded spindle and flat end as per DIN78


- Materials:

Spindle: steel (class 5.8) or stainless steel (303)

Handle: diecast zinc, complies with DIN 1743

- Finish: Blackened steel

With threaded spindle



Uses


- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

Options

- Alternate lengths of threaded spindle available for orders of more than 10 pieces

Info.

- H4 = clearance height required for handle



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number		Threaded rod X	H1	L		ØD	ØD1	ØD2
Steel	Stainless			Steel	Stainless			
CLB01T5	CLB01T5SS	M5	4,0	50	25	10,0	13,0	14,5
CLB01T6	CLB01T6SS	M6	4,0	50	50	10,0	13,0	14,5
CLB02T8	CLB02T8SS	M8	6,5	60	60	13,5	18,0	19,5
CLB02T10	CLB02T10SS	M10	6,5	60	60	13,5	18,0	19,5
CLB03T10	CLB03T10SS	M10	10,0	60	60	16,0	21,5	23,0
CLB04T10	-	M10	10,0	90	-	19,0	25,5	27,5
CLB04T12	CLB04T12SS	M12	10,0	90	60	19,0	25,5	27,5
CLB05T12	-	M12	12,0	90	-	23,0	30,0	32,5
CLB05T16	CLB05T16SS	M16	12,0	90	60	23,0	30,0	32,5

Part number		H	H2	H3	H4	A	A1	B	N° of teeth	Stock*		Price each 1 to 5	
Steel	Stainless									Steel	Sts	Steel	Stainless
CLB01T5	CLB01T5SS	24,5	15,0	30,0	33,5	40	47,0	7,5	16	✓	✓	15,13 €	19,43 €
CLB01T6	CLB01T6SS	24,5	15,0	30,0	33,5	40	47,0	7,5	16	✓	✓	15,13 €	20,93 €
CLB02T8	CLB02T8SS	28,5	17,5	41,5	45,5	65	75,0	9,5	20	✓	✓	18,70 €	25,89 €
CLB02T10	CLB02T10SS	28,5	17,5	41,5	45,5	65	75,0	9,5	20	✓	-	18,70 €	25,82 €
CLB03T10	CLB03T10SS	37,0	24,0	53,5	58,0	80	91,5	11,0	22	✓	-	20,67 €	29,52 €
CLB04T10	-	43,0	26,0	61,0	66,0	95	109,0	13,0	24	✓	-	24,77 €	-
CLB04T12	CLB04T12SS	43,0	26,0	61,0	66,0	95	109,0	13,0	24	✓	✓	24,77 €	37,95 €
CLB05T12	-	49,0	33,0	72,0	77,0	110	126,0	15,5	26	✓	-	31,16 €	-
CLB05T16	CLB05T16SS	49,0	33,0	72,0	77,0	110	126,0	15,5	26	✓	-	31,16 €	48,43 €

* Depending on availability - Dimensions in mm

CLass

With threaded insert

- **Stainless steel indexing handle with threaded insert**

- **Materials:**

Precision cast handle: stainless steel 304


Other components: stainless steel 303

- **Finish:**

Handle: electrolytically polished stainless steel

Other components: polished stainless steel

stainless steel



Pull the handle to unlock



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Thread		D	D1	D2	H	H1	H2	H3	H4	A	A1	B	N° of teeth	Price each	
	X	T													Stock*	1 to 5
CLA01M5/SS	M5	9	10,0	13,0	14,0	24,5	4,0	14,5	31,0	34,0	40	47,0	7	16	-	25,97 €
CLA01M6/SS	M6	9	10,0	13,0	14,0	24,5	4,0	14,5	31,0	34,0	40	47,0	7	16	-	25,97 €
CLA02M6/SS	M6	12	13,5	18,5	19,0	28,5	6,5	17,5	42,5	45,5	65	74,5	10	20	✓	34,98 €
CLA02M8/SS	M8	12	13,5	18,5	19,0	28,5	6,5	17,5	42,5	45,5	65	74,5	10	20	✓	34,98 €
CLA03M8/SS	M8	14	16,0	21,0	22,0	37,0	10,0	24,0	54,5	58,5	80	91,0	11	22	✓	42,17 €
CLA03M10/SS	M10	14	16,0	21,0	22,0	37,0	10,0	24,0	54,5	58,5	80	91,0	11	22	-	42,17 €
CLA04M10/SS	M10	17	19,0	27,0	27,5	43,0	10,0	27,0	63,0	67,5	95	109,0	13	24	✓	49,37 €
CLA04M12/SS	M12	17	19,0	27,0	27,5	43,0	10,0	27,0	63,0	67,5	95	109,0	13	24	-	49,37 €

*Subject to availability - Dimensions in mm

- Stainless steel indexing handle with threaded spindle

- Materials:


Precision cast handle: stainless steel 304

Other components: stainless steel 303

- Finish:

Handle: electrolytically polished stainless steel

Other components: polished stainless steel



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Thread				H	H1	H2	H3	H4	A	A1	B	N° of teeth	Thread length L	Price each	
	X	D	D1	D2												Stock*
CLA01T5/SS	M5	10,0	13,0	14,0	24,5	4,0	14,5	31,0	34,0	40	47,0	7	16	20	-	26,71 €
CLA01T6/SS	M6	10,0	13,0	14,0	24,5	4,0	14,5	31,0	34,0	40	47,0	7	16	30	✓	26,71 €
CLA02T6/SS	M6	13,5	18,5	19,0	28,5	6,5	17,5	42,5	45,5	65	74,5	10	20	50	✓	37,15 €
CLA02T8/SS	M8	13,5	18,5	19,0	28,5	6,5	17,5	42,5	45,5	65	74,5	10	20	50	✓	37,15 €
CLA02T10/SS	M10	13,5	18,5	19,0	28,5	6,5	17,5	42,5	45,5	65	74,5	10	20	50	✓	37,15 €
CLA03T8/SS	M8	16,0	21,0	22,0	37,0	10,0	24,0	54,5	58,5	80	91,0	11	22	50	✓	44,57 €
CLA03T10/SS	M10	16,0	21,0	22,0	37,0	10,0	24,0	54,5	58,5	80	91,0	11	22	50	✓	44,57 €
CLA04T12/SS	M12	19,0	27,0	27,5	43,0	10,0	27,0	63,0	67,5	95	109,0	13	24	50	✓	52,35 €

*Subject to availability - Dimensions in mm