

With male thread

CLBT
CLBTss

- Clamp lever with male thread and flattened end according to DIN 78


Materials:

Insert: steel (class 5.8) or

stainless steel (303)

Handle: diecast zinc,
complies with DIN 1743

- Finish: Blackened steel

With threaded
shaft

Uses


- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

Options

- Alternate lengths of threaded shaft available for orders of more than 10 pieces

Info.

- H4 = clearance height required for handle



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number		Threaded rod X	H1	L		ØD	ØD1	ØD2
Steel	Stainless			Steel	Stainless			
CLB01T5	CLB01T5SS	M5	4,0	50	25	10,0	13,0	14,5
CLB01T6	CLB01T6SS	M6	4,0	50	50	10,0	13,0	14,5
CLB02T8	CLB02T8SS	M8	6,5	60	60	13,5	18,0	19,5
CLB02T10	CLB02T10SS	M10	6,5	60	60	13,5	18,0	19,5
CLB03T10	CLB03T10SS	M10	10,0	60	60	16,0	21,5	23,0
CLB04T10	-	M10	10,0	90	-	19,0	25,5	27,5
CLB04T12	CLB04T12SS	M12	10,0	90	60	19,0	25,5	27,5
CLB05T12	-	M12	12,0	90	-	23,0	30,0	32,5
CLB05T16	CLB05T16SS	M16	12,0	90	60	23,0	30,0	32,5

Part number		H	H2	H3	H4	A	A1	B	N° of teeth	Stock*		Price each 1 to 5	
Steel	Stainless									Steel	Sts	Steel	Stainless
CLB01T5	CLB01T5SS	24,5	15,0	30,0	33,5	40	47,0	7,5	16	✓	✓	13,26 €	17,02 €
CLB01T6	CLB01T6SS	24,5	15,0	30,0	33,5	40	47,0	7,5	16	✓	✓	13,26 €	18,30 €
CLB02T8	CLB02T8SS	28,5	17,5	41,5	45,5	65	75,0	9,5	20	✓	✓	16,40 €	22,71 €
CLB02T10	CLB02T10SS	28,5	17,5	41,5	45,5	65	75,0	9,5	20	✓	✓	16,40 €	22,63 €
CLB03T10	CLB03T10SS	37,0	24,0	53,5	58,0	80	91,5	11,0	22	✓	✓	18,15 €	25,85 €
CLB04T10	-	43,0	26,0	61,0	66,0	95	109,0	13,0	24	✓	-	21,68 €	-
CLB04T12	CLB04T12SS	43,0	26,0	61,0	66,0	95	109,0	13,0	24	✓	✓	21,68 €	33,25 €
CLB05T12	-	49,0	33,0	72,0	77,0	110	126,0	15,5	26	✓	-	27,29 €	-
CLB05T16	CLB05T16SS	49,0	33,0	72,0	77,0	110	126,0	15,5	26	✓	-	27,29 €	42,42 €

*Depending on availability - Dimensions in mm

Our other products



Steel bevel gear, 2:1



Revolving handle for handwheel, Stainless steel 316



Miniature motorised actuator 2A, 2 amperes




Screw block, Panel addition and fastening



Asynchronous AC Motor 1.1 to 1.85kW, 1.1 to 1.85kW




Wheel, Polyamide



High rigidity linear slide, Chariot - from 9320 N to 71300 N



Stainless/Polymer pillow block bearing, Polymer and stainless steel



Guide for aluminium profile, Parallel rails



Rigid manual tensioner, Fixed



Bearing housing for miniature ballscrew, Bearing housing



Folding lifting ring for welding, Folding - for welding

Complementary products



Technopolymer clamping lever - male, Plastic



Stainless steel indexing handle - male, Stainless steel



Die cast zinc clamping lever - female, Zamak



Stainless steel indexing handle - female, Stainless steel