

## CLB<sub>M</sub> CLB<sub>MS</sub>

### With threaded insert

#### - Clamp lever with threaded insert


#### - Materials:

Handle: diecast zinc, complies with DIN 1743

#### - Finish:

Steel: blackened steel

Handle: black plastic coating




### Uses

- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

### Info.

- H4 = clearance height required for handle



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Thread		ØD	ØD1	ØD2	H	H1	H2
	X	T						
CLB01M4	M4	9	10,0	13,0	14,5	24,5	4,0	15,0
CLB01M5	M5	9	10,0	13,0	14,5	24,5	4,0	15,0
CLB01M6	M6	9	10,0	13,0	14,5	24,5	4,0	15,0
CLB02M6	M6	12	13,5	18,0	19,5	28,5	6,5	17,5
CLB02M8	M8	12	13,5	18,0	19,5	28,5	6,5	17,5
CLB03M8	M8	14	16,0	21,5	23,0	37,0	10,0	24,0
CLB03M10	M10	14	16,0	21,5	23,0	37,0	10,0	24,0
CLB04M10	M10	17	19,0	25,5	27,5	43,0	10,0	26,0
CLB04M12	M12	17	19,0	25,5	27,5	43,0	10,0	26,0
CLB05M12	M12	23	23,0	30,0	32,5	49,0	12,0	33,0
CLB05M16	M16	23	23,0	30,0	32,5	49,0	12,0	33,0

Part number	Steel		H3	H4	A	A1	B	N° of teeth	Stock*		Prix Uni. 1 à 5	
	Steel	Sts							Steel	Sts		
CLB01M4	-	-	30,0	33,5	40	47,0	7,5	16	✓	-	11,46 €	-
CLB01M5	CLB01M5SS	-	30,0	33,5	40	47,0	7,5	16	✓	-	11,46 €	16,07 €
CLB01M6	CLB01M6SS	-	30,0	33,5	40	47,0	7,5	16	✓	-	11,46 €	16,07 €
CLB02M6	CLB02M6SS	✓	41,5	45,5	65	75,0	9,5	20	✓	✓	14,48 €	19,93 €
CLB02M8	CLB02M8SS	✓	41,5	45,5	65	75,0	9,5	20	✓	-	14,48 €	19,93 €
CLB03M8	CLB03M8SS	✓	53,5	58,0	80	91,5	11,0	22	✓	-	15,82 €	22,63 €
CLB03M10	CLB03M10SS	✓	53,5	58,0	80	91,5	11,0	22	✓	-	15,82 €	22,63 €
CLB04M10	CLB04M10SS	✓	61,0	66,0	95	109,0	13,0	24	✓	-	17,90 €	29,44 €
CLB04M12	CLB04M12SS	✓	61,0	66,0	95	109,0	13,0	24	✓	✓	17,90 €	29,44 €
CLB05M12	CLB05M12SS	✓	72,0	77,0	110	126,0	15,5	26	✓	-	22,23 €	35,83 €
CLB05M16	CLB05M16SS	✓	72,0	77,0	110	126,0	15,5	26	✓	-	22,23 €	35,90 €

\*Depending on availability - Dimensions in mm

## Our other products



DOMI50

Accessories, Fixing kit



PLM-SC

Magnetic stud with central countersunk hole, With milled bore



CMM\_SS

Male rod ends DIN ISO12240-4, Stainless steel / bronze - Economy range



LVT

Miniature motorised actuator 2A, 2 amperes



DOMI80

Accessories, Turntable



BDP2R

Adjustable support arm, Increased grip



M1

Worm and wheel set, Machined plastic (delrin)



PCLA\_M

Technopolymer clamping lever - female, Plastic



VT

Vari-Tork® slip friction clutch, 0.53 to 1.32 Nm



BPLF

Ball transfer unit light duty, Light



MDB\_MTB

Moulded plastic bevel gear (nylon), 2:1



CLR

Straight clevis, Straight clevis for use with a male clevis

## Complementary products



PCLA\_M

Technopolymer clamping lever - female, Plastic



CLASS

Stainless steel indexing handle - female, Stainless steel



CLB\_T

Die cast zinc clamping lever - male, Zamak



CLASS

Stainless steel indexing handle - male, Stainless steel