


- Moulded gear for use in food applications
- Pressure angle: 20°
- Material:

Blue glass-fibre reinforced Polyamide

Info

- *Pre-bore after de-moulding, must be machined before installation.
- Alternative numbers of teeth (up to 160) possible but minimum quantity applies.
- We are unable to modify these products



Food industry

DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	Net	-10%	-15%	-25%	On request

Part N°	Z	ØP PCD	ØD External	ØM Hub	ØA* Pre-bore	ØDA	Transmissible torque (Nm)	Price each. 1 to 9
CLG1-12/ALI	12	12	14	9	4	-	2,3	4,10 €
CLG1-15/ALI	15	15	17	10	4	-	2,9	4,35 €
CLG1-16/ALI	16	16	18	13	5	-	3,1	4,38 €
CLG1-20/ALI	20	20	22	16	5	-	3,9	4,78 €
CLG1-24/ALI	24	24	26	20	6	-	4,7	5,12 €
CLG1-25/ALI	25	25	27	20	6	-	4,9	5,15 €
CLG1-28/ALI	28	28	30	22	6	-	5,4	5,51 €
CLG1-30/ALI	30	30	32	25	6	-	5,8	6,53 €
CLG1-32/ALI	32	32	34	25	6	-	6,2	6,86 €
CLG1-35/ALI	35	35	37	30	8	-	6,8	7,05 €
CLG1-40/ALI	40	40	42	30	8	-	7,8	8,24 €
CLG1-45/ALI	45	45	47	35	10	-	8,7	9,01 €
CLG1-50/ALI	50	50	52	35	10	-	9,7	10,27 €
CLG1-55/ALI	55	55	57	35	14	44	10,7	10,85 €
CLG1-60/ALI	60	60	62	40	14	51	11,7	11,65 €
CLG1-70/ALI	70	70	72	40	20	61	13,6	12,75 €
CLG1-80/ALI	80	80	82	50	20	66	15,5	15,51 €

All dimensions in mm

Our other products



CABtool
Fitting cable tools,
Cutting tools



AC156-157
Strike for toggle latch,
25.5mm




BPHF
Ball transfer unit push
fit, Heavy



PW_PWG2
Worm - precision
range, Stainless steel



HLA19
Right angle spiro
bevel gearbox, Up to
43Nm



BMM
Knurled knob - male,
Knurled



SLBWSS
Indexing plunger,
weldable, Stainless steel



PSG15
Spur gear - precision
range, Pre-hardened
Steel 35NCD6



AT5-16ECO
AT type timing pulley,
Economy range - AT5
aluminium



HLUT
Spoked handwheel
with handle,
Aluminium



RDE-B
Sealing washer
Hygienic Usit®,
Stainless steel - Blue
EPDM



BPM-Z
Plastic slotted spring
plunger with ball tip,
Plastic body +
stainless steel

Complementary products



CLG1
Moulded plastic spur
gear, Moulded plastic
(nylon)



ZG1
Plastic spur gear,
Machined plastic
(delrin)