

- Kit of assorted precision feelers for adjusting, equalising, fixing or positioning
- To be cut to form required
- Materials:
  - Steel 1.1274
  - Stainless steel 1.4310
  - Brass 2.0321

### Advantage

- Wide range of thicknesses in each box allows accurate positioning for all applications

### Applications

- Aligning workpieces before machining, aligning differently sized/shaped pieces, adjusting valve lash, wedging tools, adjusting bearings



### DISCOUNTS

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number	Number		Material	Contents of box	Stock*	Price each 1 to 2
	Format	Sheets				
CLQ25-300-21/A	25x300	21	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/ 0,07/0,08/0,09/0,10/0,15/0,20/ 0,25/0,30/0,40/0,50/0,60/0,70/ 0,80/0,90/1,00	✓	48,05 €
CLQ50-300-25/A	50x300	25	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/ 0,08/0,09/0,10/0,12/0,15/0,18/0,20/ 0,25/0,30/0,35/0,40/0,45/0,50/ 0,60/0,70/0,80/0,90/1,00	✓	83,20 €
CLQ50-300-23/A	50x300	23	steel 1.1274	0,03/0,04/0,05/0,06/0,07/0,08/ 0,09/0,10/0,12/0,15/0,18/0,20/ 0,25/0,30/0,35/0,40/0,45/0,50/ 0,60/0,70/0,80/0,90/1,00	✓	68,99 €
CLQ100-500-9/SS	100x500	9	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,30/ 0,40/0,50/1,00	✓	99,51 €
CLQ100-500-11/SS	100x500	11	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,25/ 0,30/0,35/0,40/0,45/0,50	✓	100,78 €
CLQ100-500-11/SS2	100x500	11	s/steel 1.4310	0,50/0,55/0,60/0,70/0,75/0,80/ 0,85/0,90/0,95/1,00	-	227,97 €
CLQ150-500-10/SS	150x500	10	s/steel 1.4310	0,025/0,05/0,075/0,1/0,15/0,20/ 0,25/0,30/0,50	-	143,19 €
CLQ150-500-10/BR	150x500	10	brass 2.0321	0,025/0,05/0,075/0,1/0,15/0,20/ 0,25/0,30/0,50	-	167,98 €

\*Depending on availability - Dimensions in mm

## Our other products



TRM  
Spur round rack, Steel  
- module 1-6



CHB  
Single output shaft,  
For CHB gearbox



T10\_21N1F  
T type timing pulley,  
Economy range - T10  
moulded plastic  
(nylon)



DOG319  
Motor-gearbox 12V  
and 24V DC, from 4 to  
9 Nm




BEAB  
Knob star grip  
antibacterial, Star,  
anti-bacterial



CAP881  
Side flexing slim slat  
top chain stainless  
steel, Narrow range  
881



GAC  
Lock for latch clamp,  
Strike plate



RPP8  
RPP heavy duty  
timing belt, RPP8



BOX-CS  
Hose clamp, Box set  
of steel hose clamps



PRES7HR  
Manual workbench  
press, Force up to  
700kg



MSP3815  
Masterplate®  
glueable insert  
rectangular,



PGNT  
Thermoplastic T  
handle, With threaded  
spindle

## Complementary products



CLQ  
12.7mm wide steel  
feeler strip on rolls,  
Feeler strip on rolls