

12.7mm wide steel feeler strip on rolls **SteSta**


CLQ Steel or stainless steel

- Rolls of precision feeler strip for adjusting, straightening, positioning or levelling
- Width 12.7mm
- Length per roll: 5 metres
(*except CLQ12-10-001 which is supplied on a 10 metre roll)
- Strip to be cut to form required
- Materials:
Steel 1.1274
Stainless steel 1.4310




Applications

- Aligning workpieces before machining
- Aligning differently sized/shaped pieces
- Adjusting valve lash
- Wedging tools
- Adjusting bearings
- Aligning a motor and a pump before coupling



Incorrectly aligned



Wedge adjustment

DISCOUNTS

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number		Thickness (mm)	Stock*		Price each 1 to 2	
Steel	Stainless steel		Steel	S/Steel	Steel	S/Steel
CLQ12-10-001	CLQ12-5-001/SS	0,01	-	✓	115,00 €	75,96 €
CLQ12-5-002	CLQ12-5-002/SS	0,02	-	✓	48,25 €	51,11 €
CLQ12-5-003	CLQ12-5-003/SS	0,03	-	-	19,57 €	24,35 €
CLQ12-5-004	CLQ12-5-004/SS	0,04	-	-	18,40 €	18,71 €
CLQ12-5-005	CLQ12-5-005/SS	0,05	✓	✓	19,47 €	17,86 €
CLQ12-5-006	CLQ12-5-006/SS	0,06	-	-	14,02 €	15,78 €
CLQ12-5-007	CLQ12-5-007/SS	0,07	-	-	13,12 €	15,78 €
CLQ12-5-008	CLQ12-5-008/SS	0,08	-	-	12,56 €	15,78 €
CLQ12-5-010	CLQ12-5-010/SS	0,10	✓	✓	14,13 €	18,83 €
CLQ12-5-015	CLQ12-5-015/SS	0,15	-	✓	12,56 €	20,77 €
CLQ12-5-020	CLQ12-5-020/SS	0,20	✓	✓	15,43 €	21,75 €
CLQ12-5-025	CLQ12-5-025/SS	0,25	✓	-	20,57 €	21,11 €
CLQ12-5-030	CLQ12-5-030/SS	0,30	✓	✓	14,61 €	25,62 €
CLQ12-5-040	CLQ12-5-040/SS	0,40	✓	✓	16,56 €	28,25 €
CLQ12-5-050	CLQ12-5-050/SS	0,50	✓	✓	27,32 €	27,19 €

*Depending on availability - Dimensions in mm

Steel, stainless steel and brass feelers **CLQ**

- Kit of assorted precision feelers for adjusting, equalising, fixing or positioning
- To be cut to form required
- Materials:
 - Steel 1.1274
 - Stainless steel 1.4310
 - Brass 2.0321

Advantage

- Wide range of thicknesses in each box allows accurate positioning for all applications

Applications

- Aligning workpieces before machining, aligning differently sized/shaped pieces, adjusting valve lash, wedging tools, adjusting bearings

**DISCOUNTS**

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number	Number		Material	Contents of box	Stock*	Price each 1 to 2
	Format	Sheets				
CLQ25-300-21/A	25x300	21	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,15/0,20/0,25/0,30/0,40/0,50/0,60/0,70/0,80/0,90/1,00	✓	76,30 €
CLQ50-300-25/A	50x300	25	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,12/0,15/0,18/0,20/0,25/0,30/0,35/0,40/0,45/0,50/0,60/0,70/0,80/0,90/1,00	✓	104,55 €
CLQ50-300-23/A	50x300	23	steel 1.1274	0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,12/0,15/0,18/0,20/0,25/0,30/0,35/0,40/0,45/0,50/0,60/0,70/0,80/0,90/1,00	✓	90,25 €
CLQ100-500-9/SS	100x500	9	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,30/0,40/0,50/1,00	✓	150,02 €
CLQ100-500-11/SS	100x500	11	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,25/0,30/0,35/0,40/0,45/0,50	✓	175,01 €
CLQ100-500-11/SS2	100x500	11	s/steel 1.4310	0,50/0,55/0,60/0,70/0,75/0,80/0,85/0,90/0,95/1,00	-	315,21 €
CLQ150-500-10/SS	150x500	10	s/steel 1.4310	0,025/0,05/0,075/0,1/0,15/0,20/0,25/0,30/0,50	-	162,13 €
CLQ150-500-10/BR	150x500	10	brass 2.0321	0,025/0,05/0,075/0,1/0,15/0,20/0,25/0,30/0,50	-	190,18 €

*Depending on availability - Dimensions in mm