



## CTss

## Industrial range

- **Stainless steel range**
- Plain pins and bushes
- Max. misalignment angle 45°
- Materials:
  - 304 stainless steel
- Max. speed: 3600 rpm
- Transmissible torque, see universal joint JCD




### Uses

- Food and pharmaceutical industries

### Accessories

- Optional rubber cover M (v.2, page 96)



### Modifiable bore



Part number	L		ØA (H7)	ØD	L1	L2	B	Stroke	E	F	ØDE	Price each
	min/	max										
CT10-130/150/SS	130/150		10	22	76	25	30	20	11	14	21,2	On request
CT10-140/170/SS	140/170		10	22	76	25	30	30	11	14	21,2	On request
CT10-160/200/SS	160/200		10	22	76	25	30	40	11	14	21,2	On request
CT10-170/230/SS	170/230		10	22	76	25	30	60	11	14	21,2	On request
CT10-180/240/SS	180/240		10	22	76	25	30	60	11	14	21,2	On request
CT10-230/330/SS	230/330		10	22	76	25	30	100	11	14	21,2	On request
CT12-140/170/SS	140/170		12	25	86	29	35	30	13	16	26,5	On request
CT12-160/200/SS	160/200		12	25	86	29	35	40	13	16	26,5	On request
CT12-180/225/SS	180/225		12	25	86	29	35	45	13	16	26,5	On request
CT12-200/270/SS	200/270		12	25	86	29	35	70	13	16	26,5	On request
CT12-220/300/SS	220/300		12	25	86	29	35	80	13	16	26,5	On request
CT12-250/355/SS	250/355		12	25	86	29	35	105	13	16	26,5	On request
CT12-280/420/SS	280/420		12	25	86	29	35	140	13	16	26,5	On request
CT12-300/450/SS	300/450		12	25	86	29	35	150	13	16	26,5	On request
CT14-160/190/SS	160/190		14	29	90	30	35	30	13	16	26,5	On request
CT14-170/200/SS	170/200		14	29	90	30	35	30	13	16	26,5	On request
CT14-180/220/SS	180/220		14	29	90	30	35	40	13	16	26,5	On request
CT14-210/280/SS	210/280		14	29	90	30	35	70	13	16	26,5	On request
CT14-220/300/SS	220/300		14	29	90	30	35	80	13	16	26,5	On request
CT14-250/350/SS	250/350		14	29	90	30	35	100	13	16	26,5	On request
CT14-280/420/SS	280/420		14	29	90	30	35	140	13	16	26,5	On request
CT14-300/450/SS	300/450		14	29	90	30	35	150	13	16	26,5	On request
CT14-350/550/SS	350/550		14	29	90	30	35	200	13	16	26,5	On request
CT14-400/650/SS	400/650		14	29	90	30	35	250	13	16	26,5	On request

Dimensions in mm

Part number	L		ØA (H7)	ØD	L1	L2	B	Stroke	E	F	ØDE	Price each
	min/ max											
CT16-190/220/SS	190/220	16	32	95	30	40	30	16	20	32,5	On request	
CT16-210/250/SS	210/250	16	32	95	30	40	40	16	20	32,5	On request	
CT16-240/320/SS	240/320	16	32	95	30	40	80	16	20	32,5	On request	
CT16-250/350/SS	250/350	16	32	95	30	40	100	16	20	32,5	On request	
CT16-275/390/SS	275/390	16	32	95	30	40	115	16	20	32,5	On request	
CT16-300/430/SS	300/430	16	32	95	30	40	130	16	20	32,5	On request	
CT16-380/590/SS	380/590	16	32	95	30	40	210	16	20	32,5	On request	
CT16-400/630/SS	400/630	16	32	95	30	40	230	16	20	32,5	On request	
CT18-195/225/SS	195/225	18	37	108	35	40	30	16	20	32,5	On request	
CT18-230/280/SS	230/280	18	37	108	35	40	50	16	20	32,5	On request	
CT18-250/320/SS	250/320	18	37	108	35	40	70	16	20	32,5	On request	
CT18-270/370/SS	270/370	18	37	108	35	40	100	16	20	32,5	On request	
CT18-290/400/SS	290/400	18	37	108	35	40	110	16	20	32,5	On request	
CT18-300/415/SS	300/415	18	37	108	35	40	115	16	20	32,5	On request	
CT18-400/620/SS	400/620	18	37	108	35	40	220	16	20	32,5	On request	
CT18-500/820/SS	500/820	18	37	108	35	40	320	16	20	32,5	On request	
CT20-220/250/SS	220/250	20	40	108	32	48	30	18	22	41,5	429,21 €	
CT20-250/300/SS	250/300	20	40	108	32	48	50	18	22	41,5	439,22 €	
CT20-270/340/SS	270/340	20	40	108	32	48	70	18	22	41,5	On request	
CT20-290/380/SS	290/380	20	40	108	32	48	90	18	22	41,5	On request	
CT20-320/440/SS	320/440	20	40	108	32	48	120	18	22	41,5	On request	
CT20-380/560/SS	380/560	20	40	108	32	48	180	18	22	41,5	404,45 €	
CT20-420/640/SS	420/640	20	40	108	32	48	220	18	22	41,5	On request	
CT20-500/800/SS	500/800	20	40	108	32	48	300	18	22	41,5	On request	
CT22-250/280/SS	250/280	22	47	127	38	48	30	21	25	47,5	On request	
CT22-270/320/SS	270/320	22	47	127	38	48	50	21	25	47,5	On request	
CT22-290/350/SS	290/350	22	47	127	38	48	60	21	25	47,5	On request	
CT22-330/430/SS	330/430	22	47	127	38	48	100	21	25	47,5	On request	
CT22-350/470/SS	350/470	22	47	127	38	48	120	21	25	47,5	On request	
CT22-470/710/SS	470/710	22	47	127	38	48	240	21	25	47,5	On request	
CT25-270/320/SS	270/320	25	50	140	44	48	50	23	28	47,5	On request	
CT25-295/350/SS	295/350	25	50	140	44	48	55	23	28	47,5	On request	
CT25-310/375/SS	310/375	25	50	140	44	48	65	23	28	47,5	On request	
CT25-350/450/SS	350/450	25	50	140	44	48	100	23	28	47,5	On request	
CT25-380/500/SS	380/500	25	50	140	44	48	120	23	28	47,5	On request	
CT25-420/590/SS	420/590	25	50	140	44	48	170	23	28	47,5	On request	
CT25-460/660/SS	460/660	25	50	140	44	48	200	23	28	47,5	On request	
CT25-500/745/SS	500/745	25	50	140	44	48	245	23	28	47,5	On request	
CT30-320/390/SS	320/390	30	58	178	58	48	70	26	32	60,0	On request	
CT30-350/420/SS	350/420	30	58	178	58	48	70	26	32	60,0	On request	
CT30-370/455/SS	370/455	30	58	178	58	48	85	26	32	60,0	On request	
CT30-400/510/SS	400/510	30	58	178	58	48	110	26	32	60,0	On request	
CT30-450/620/SS	450/620	30	58	178	58	48	170	26	32	60,0	On request	
CT30-500/720/SS	500/720	30	58	178	58	48	220	26	32	60,0	On request	
CT30-540/795/SS	540/795	30	58	178	58	48	255	26	32	60,0	On request	

Dimensions in mm

## Our other products



PW\_PWG15

Wheel - precision range, Bronze



CHAGC-AL

Screw-in garnet hinge, Screw-on



PSG25

Spur gear - precision range, Stainless steel 303



BLH30

Right angled gearbox, from 1.32 to 4.40 Nm



R\_RR

Rack, rectangular section, Steel



CHTRP

Single and dual output gearboxes, Up to 9,1 Nm



AKN

Bellows coupling Gerwah®, from 22 to 180Nm



PITAss

Locking bolt, with T handle



PRES

Accessories for PRES-3HR and PRES-4HR presses,



PPRss

Pad eye on mounting plate, Stainless steel



DT

Pinion shaft, Steel 20NCD2



MHWC

Flexible coupling, Double disk

## Complementary products



M

Bellows cover, Standard