Diabolo-shaped elasto mount

CT-ZY — Female / female mounting


- ***Radial elasticity greater than axial elasticity***
- *Cylinder worked under compression or shearing*
- *Materials:*
  core: Steel plates
  cylinder: Rubber
- ***Hardness: NK 55-60 shore A***
- *Working temp: -40°C to +70°C*



Uses

- *Dampens sound and vibrations*





DISCOUNTS

Qty	1+	6+	20+	40+	100+	200+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØG	ØD	H	L	Stock*	Price each 1 to 5
CT-ZY4-10-10	M4	10	10	4	✔	1,85 €
CT-ZY8-30-20	M8	30	20	8	✔	5,45 €
CT-ZY8-40-48	M8	40	48	8	✔	10,98 €
CT-ZY10-50-30	M10	50	30	10	-	19,25 €

**Depending on availability - Dimensions in mm*

Our other products



F7-P-AM

Multifunction display, Magnetic band



SLB

Indexing plunger, steel class 5.8



ZDB

Machined plastic bevel gear , 2:1



BABS

630 Stainless steel compact ball pin, Hardened stainless steel



HLU

Spoked handwheel without handle, Aluminium



ERT

Sliding nut, For T slot



BAGSS

Stainless steel Clamping collar, Stainless steel



ZB

Shaft for linear guides, Hardened ground stainless steel



PTA80

Articulated levelling foot, pressed base



HTD3M_09

HTD Heavy duty timing pulley, HTD3



PSG08

Spur gear - precision range, Case hardened



NDS20

Double cross clamp, Parallel

Complementary products



ATZY

Diabolo shaped elasto mount, Steel



CTZYSS

Stainless steel diabolo shaped elasto mount, Stainless steel



BZY

Cylindrical elasto mount, Steel



BZY_SS

Stainless steel cylindrical elasto mount, Stainless steel