Sta Diabolo shaped stainless steel elasto mount

Female / female mounting

CT-ZYss


- ***Radial elasticity greater than axial elasticity***
- *Cylinder works under both compression and shear*
- *Materials :*
  Core: Stainless steel (A2)
  Cylinder: Rubber
- ***Hardness NK55-60 Shore A***
- *Working temp: -40°C to +70°C*



Uses

- *Dampens sound and vibrations*





DISCOUNTS

Qty	1+	6+	20+	40+	100+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØG	ØD	H	L	Stock*	Price each 1 to 5
CT-ZY4-10-10/SS	M4	10	10	4	✔	3,61 €
CT-ZY8-30-20/SS	M8	30	20	8	✔	8,17 €
CT-ZY8-40-48/SS	M8	40	48	8	✔	16,93 €
CT-ZY10-50-30/SS	M10	50	30	10	-	26,63 €

**Depending on availability - Dimensions in mm*

Our other products


GTCSS

Belt tensioner, For use in hostile environments


SGL

Lifting sling, 2 eyelinks


ERC

Quick fitting cable terminal, Eye version


PRF-SCL

Lock for aluminium profile, Lock for sliding doors


BH01

Single housed bearing, Bearing fitted with adhesive


CHA1056-UPA

Molded polyamide face-mounted hinge, Black polyamide


SH2

Parallel axis helical gear, Machined plastic (delrin)


F7-SF-SM

Multifunction display, Mounting bracket for front mounting


BOXbeta

Box of assorted hitch pins, Boxed set - hitch


PSG3

Spur gear - precision range, Pre-hardened Steel 35NCD6


Q1

Self-aligning radial ball bearing, Steel


BH02

Single housed bearing assembly, Bearing secured with circlips

Complementary products


CTZY

Diabolo shaped elasto mount, Steel


ATZYSS

Stainless steel diabolo shaped elasto mount, Stainless steel


AZY

Cylindrical elasto mount, Steel