





- **Multidirectional flexibility**
- High precision
- **Space saving**
- Good torsional rigidity
- Single piece construction
- Backlash free
- For use in restricted spaces
- 3 beams
- Working temperature: -40°C to +120°C
- Max. speed: 5,000 rpm
- Material: Aluminium 6082
- Pre-bore is not tolerated

Clamp  
fixing



### Applications

- Encoders, optical systems
- Automated systems, step motors

### Assembly

- Dimension "C" must not be exceeded



### DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	ØD	L	C	Vis	radial (mm)	angular	Torsional rigidity (Nm/rad)	Max torque (Nm)		
								Shock and reversing	non reversing	Peak torque
DBC3	12,7	19,1	6,0	M2	0,127	5°	28	0,45	0,60	0,9
DBC3.5	15,9	20,3	6,5	M2,5	0,127	5°	38	0,75	1,00	1,5
DBC4	19,1	22,9	6,5	M2,5	0,127	5°	65	1,25	1,66	2,5
DBC5	25,4	31,8	9,0	M3	0,127	5°	121	2,00	2,66	4,0
DBC6	31,8	44,5	12,0	M4	0,127	5°	238	3,00	4,00	8,0

Part number	ØA1 x ØA2		ØA1 x ØA2		ØA1 x ØA2 Standard Bores (H8)	Stock*	Price each 1 to 4	
	Pre-bores	Min.	Max.	Std. bores and pre-bores			Std. bores and pre-bores	Modified bore
DBC3	2,5 x 3,95	3 x 4	5 x 5	-	✓	47,80 €	69,44 €	
DBC3.5	2,5 x 3,95	3 x 4	6,35 x 6,35	5 x 5	✓	47,80 €	76,34 €	
DBC4	2,5 x 5,8	4 x 4,76	8 x 8	6 x 6	✓	50,87 €	61,05 €	
DBC5	3,8 x 5,95	5 x 6	10 x 10	10 x 10	✓	57,59 €	69,11 €	
DBC6	5,1 x 9,2	6 x 8	14 x 14	-	✓	86,68 €	133,07 €	


\*Depending on availability - Dimensions in mm

## Our other products




RFK28B

Hypoid gearbox -  
Stainless steel, up to  
130 Nm



PRZ

Wear strip for slat top  
chain, Z profile to be  
clipped



GPLso

Brush, silk



GRP2-14-A

Spring pin ISO8745,  
splined ISO 8745



FBL4004\_K32

Brush strip per metre,  
Black striated  
polypropylene (PP)



GP75

Spring loaded toggle  
latch, Standard  
(GP75)



GRP2-14-C

Spring pin ISO8742,  
splined ISO 8742



PRF1932

Standard aluminium  
profile, 19 x 32 mm




CMA

Eye bolt, Steel




CAP805

Slat top chain  
stainless steel, Large



KSM

Cylindrical steel nut,  
Steel - 1 thread



EZY

Cylindrical stop, Steel

## Complementary products



B3PAN

Panamech, Multi-  
Beam stainless steel,  
Stainless steel - with  
clampin...



BC3

Panamech, Multi-  
Beam stainless steel,  
Stainless steel - with  
clampin...