
Idler for plate chain

DBL805

For chain range 805

- ***For use with CAP805/SS plate chains***
- *Materials:*
  Low friction acetal
- *Operating temp.: -40°C to +85°C (+70°C in humid environments)*
- *For dimensions and bore tolerances, please refer to technical pages*





DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDE	Bore ØA	Weight (kg)	Price each 1 to 4
DBL805-19-25	117	25	0,3	15,69 €
DBL805-19-30	117	30	0,3	15,69 €
DBL805-19-35	117	35	0,3	15,69 €
DBL805-19-40	117	40	0,3	15,69 €
DBL805-21-25	129	25	0,3	16,14 €
DBL805-21-30	129	30	0,3	16,14 €
DBL805-21-35	129	35	0,3	16,14 €
DBL805-21-40	129	40	0,3	16,14 €
DBL805-23-25	141	25	0,3	17,36 €
DBL805-23-30	141	30	0,3	17,36 €
DBL805-23-35	141	35	0,3	17,36 €
DBL805-23-40	141	40	0,3	17,36 €
DBL805-25-25	153	25	0,4	18,07 €
DBL805-25-30	153	30	0,4	18,07 €
DBL805-25-35	153	35	0,4	18,07 €
DBL805-25-40	153	40	0,4	18,07 €

Dimensions in mm

Our other products



Extension for articulated foot Ø123, articulated foot PR125



Small 6 lobe threaded handle - female, Duroplast - Stainless steel



Locking bolt, with T handle



Pull handle, Reinforced PA thermoplastic



Worm, Non hardened steel



Mushroom headed button Hygienic Usit®, With female thread and high ...



Optional shaft for E-type gear reducers, E Gearboxes single sided ou...



Decorative hinge, Stainless steel



Detectable plastic palm grip, blue thermoplastic



Stainless/Polymer pillow block bearing, Cast iron - Split pillow



Hexagonal spacer, Stainless steel 303



Square tube connector, Fixed angle

Complementary products



Slat top chain stainless steel, Large range 805



Idler sprocket for slat top chain, Ranges 821 and 805