
Idler for plate chain

For chain range 821

DBL821

- ***For use with CAP821 plate chains***
- *Materials:*
  Low friction acetal
- *Operating temp.: -40°C to +85°C (+70°C in humid environments)*
- *For dimensions and bore tolerances, please refer to technical pages*





DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDE	Bore ØA	Weight (kg)	Price each 1 to 4
DBL821-19-25	118,0	25	0,3	29,21 €
DBL821-19-30	118,0	30	0,3	29,21 €
DBL821-19-35	118,0	35	0,3	29,21 €
DBL821-19-40	118,0	40	0,3	29,21 €
DBL821-21-25	129,8	25	0,3	29,73 €
DBL821-21-30	129,8	30	0,3	29,73 €
DBL821-21-35	129,8	35	0,3	29,73 €
DBL821-21-40	129,8	40	0,3	29,73 €
DBL821-23-25	142,2	25	0,3	31,01 €
DBL821-23-30	142,2	30	0,3	31,01 €
DBL821-23-35	142,2	35	0,3	31,01 €
DBL821-23-40	142,2	40	0,3	31,01 €
DBL821-25-25	154,7	25	0,4	31,74 €
DBL821-25-30	154,7	30	0,4	31,74 €
DBL821-25-35	154,7	35	0,4	31,74 €
DBL821-25-40	154,7	40	0,4	31,74 €

Dimensions in mm

Our other products



Hexagonal nut
DIN934, Brass



Chain link, Steel



Multifunction display,
With external sensor



Wormwheel, Bronze



Fixed tube carrier,
Fixed Ø14 to Ø20



Internal gear,
Machined plastic
(delrin)



Worm - precision
range, Steel



Pressed stainless
steel articulating foot
Ø85, Ø 85



Joining plate for
aluminium profile,
Right angled



Spur gear - precision
range, Stainless steel
303



Latch for aluminium
profile, Spring
operated latch



Molded polyamide
face-mounted hinge,
Black polyamide

Complementary products



Slat top chain acetal,
Large range 821



Idler sprocket for slat
top chain, Ranges 821
and 805