

- For locking one part to another
- Relative positioning
- 15° chamfer
- Material: hardened steel 100 Cr6 rectified 58-60HRC
- Conforms to DIN 6325 (ISO 8734)
- For information on shear strength, please see technical information
- Sold by the packet




DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-20%	-30%	On request

Part number	ØD m6	Length L	Qty per packet	Stock*	Price each per packet
DH1-5/B	1,0	5	100	✓	6,41 €
DH1-6/B	1,0	6	100	✓	6,41 €
DH1.5-5/B	1,5	5	100	✓	4,72 €
DH1.5-6/B	1,5	6	100	✓	6,41 €
DH1.5-8/B	1,5	8	100	✓	5,34 €
DH1.5-10/B	1,5	10	100	✓	5,58 €
DH2-6/B	2,0	6	100	✓	5,34 €
DH2-8/B	2,0	8	100	✓	5,66 €
DH2-10/B	2,0	10	100	✓	5,89 €
DH2-12/B	2,0	12	100	✓	6,23 €
DH2-14/B	2,0	14	100	✓	6,65 €
DH2-16/B	2,0	16	100	✓	7,01 €
DH2-30/B	2,0	30	100	✓	18,48 €
DH2.5-10/B	2,5	10	100	✓	6,25 €
DH2.5-12/B	2,5	12	100	✓	6,41 €
DH3-6/B	3,0	6	100	✓	5,58 €
DH3-8/B	3,0	8	100	✓	5,37 €
DH3-10/B	3,0	10	100	✓	5,66 €
DH3-12/B	3,0	12	100	✓	5,98 €
DH3-16/B	3,0	16	100	✓	6,77 €
DH3-18/B	3,0	18	100	✓	7,18 €
DH3-20/B	3,0	20	100	✓	7,46 €
DH3-24/B	3,0	24	100	✓	8,16 €
DH3-30/B	3,0	30	100	✓	9,32 €
DH3-32/B	3,0	32	100	✓	9,66 €
DH3-40/B	3,0	40	100	✓	14,52 €
DH4-6/B	4,0	6	100	✓	6,80 €
DH4-8/B	4,0	8	100	✓	6,74 €

Part number	ØD m6	Length L	Qty per packet	Stock*	Price each per packet
DH4-10/B	4,0	10	100	✓	7,37 €
DH4-12/B	4,0	12	100	✓	7,55 €
DH4-14/B	4,0	14	100	✓	7,90 €
DH4-16/B	4,0	16	100	✓	8,38 €
DH4-18/B	4,0	18	100	✓	8,81 €
DH4-20/B	4,0	20	100	✓	9,28 €
DH4-28/B	4,0	28	100	-	11,04 €
DH4-30/B	4,0	30	100	✓	11,45 €
DH4-32/B	4,0	32	100	-	11,89 €
DH4-40/B	4,0	40	100	✓	14,23 €
DH4-50/B	4,0	50	100	✓	21,25 €
DH4-60/B	4,0	60	100	✓	29,47 €
DH5-8/B	5,0	8	25	✓	5,11 €
DH5-10/B	5,0	10	25	✓	5,13 €
DH5-12/B	5,0	12	25	✓	5,21 €
DH5-14/B	5,0	14	25	✓	5,34 €
DH5-16/B	5,0	16	25	✓	5,50 €
DH5-20/B	5,0	20	25	✓	5,69 €
DH5-24/B	5,0	24	25	✓	5,98 €
DH5-26/B	5,0	26	25	✓	6,15 €
DH5-28/B	5,0	28	25	✓	6,23 €
DH5-30/B	5,0	30	25	✓	6,33 €
DH5-36/B	5,0	36	25	✓	6,80 €
DH5-40/B	5,0	40	25	✓	7,01 €
DH5-50/B	5,0	50	25	✓	7,90 €
DH6-10/B	6,0	10	25	✓	5,58 €
DH6-12/B	6,0	12	25	✓	5,61 €
DH6-14/B	6,0	14	25	✓	5,78 €

*Depending on availability - Dimensions in mm



DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-20%	-30%	On request

Part number	ØD m6	Length L	Qty per packet	Stock*	Price each per packet
DH6-16/B	6,0	16	25	✓	5,78 €
DH6-18/B	6,0	18	25	✓	5,93 €
DH6-20/B	6,0	20	25	✓	6,15 €
DH6-24/B	6,0	24	25	✓	6,33 €
DH6-26/B	6,0	26	25	✓	6,61 €
DH6-28/B	6,0	28	25	✓	6,74 €
DH6-30/B	6,0	30	25	✓	6,90 €
DH6-36/B	6,0	36	25	✓	7,35 €
DH6-40/B	6,0	40	25	✓	7,68 €
DH6-50/B	6,0	50	25	✓	8,81 €
DH6-60/B	6,0	60	25	✓	10,11 €
DH8-16/B	8,0	16	25	✓	8,18 €
DH8-18/B	8,0	18	25	✓	8,23 €
DH8-20/B	8,0	20	25	✓	8,28 €
DH8-24/B	8,0	24	25	✓	8,76 €
DH8-30/B	8,0	30	25	✓	9,52 €

Part number	ØD m6	Length L	Qty per packet	Stock*	Price each per packet
DH8-40/B	8,0	40	25	✓	10,71 €
DH8-50/B	8,0	50	25	✓	12,19 €
DH8-80/B	8,0	80	25	✓	20,51 €
DH10-20/B	10,0	20	25	✓	9,66 €
DH10-26/B	10,0	26	25	✓	11,01 €
DH10-30/B	10,0	30	25	✓	11,82 €
DH10-36/B	10,0	36	25	✓	13,14 €
DH10-40/B	10,0	40	25	-	13,93 €
DH10-45/B	10,0	45	25	✓	14,79 €
DH10-50/B	10,0	50	25	✓	15,79 €
DH10-60/B	10,0	60	25	✓	17,92 €
DH10-80/B	10,0	80	25	-	24,81 €
DH12-20/B	12,0	20	25	-	14,69 €
DH12-30/B	12,0	30	25	✓	16,87 €
DH12-40/B	12,0	40	25	✓	19,50 €

*Depending on availability - Dimensions in mm