

EKN **GERWAH** Couplings for servo-motors Torque: 0.5 to 12Nm

- Backlash and maintenance free
- Materials:
 - Hub: anodised aluminium
 - Bellows: stainless steel
- Angular misalignment from 1.2° to 2° depending on the length
- High torsional rigidity
- Low moment of inertia
- Shaft/bore link without backlash
- Recommended assembly tolerances H7/g6
- Max speed: 15,000 rpm
- Working temperature -30°C to +100°C
- **Please specify bore size on order (between min and max Ø)**

Set screw fixing



Miniature


Options

- Keyway according to DIN6885 on request (tolerance JS9)
- Orientation of the keyways at 180° to each other
- Stainless steel version on request

Part number	Misalignment		Torsional stiffness C _T dyn (10 ³ Nm/rad)	Moment of inertia J (g cm ²)	Tightening torque screw (Nm)	Weight (g)
	radial (ΔKr) (mm)	axial (ΔKa) (mm)				
EKN4-20	0,10	0,20	0,25	2,0	0,5	5
EKN4-23	0,15	0,30	0,19	2,0	0,5	6
EKN4-26	0,20	0,40	0,50	2,0	0,5	7
EKN9-21	0,10	0,20	0,50	2,0	0,5	6
EKN9-25	0,15	0,30	0,38	2,3	0,5	7
EKN9-28	0,20	0,40	0,30	2,6	0,5	8
EKN15-25	0,10	0,25	0,75	7,5	1,5	12
EKN15-30	0,15	0,40	0,70	8,0	1,5	14
EKN20-26	0,10	0,30	1,50	14,0	1,5	16
EKN20-32	0,20	0,40	1,30	16,0	1,5	18
EKN20-36	0,25	0,50	1,00	17,0	1,5	20
EKN45-39	0,10	0,30	6,50	68,0	3,0	48
EKN45-48	0,20	0,50	4,00	73,0	3,0	52
EKN100-44	0,15	0,40	8,10	200,0	3,0	48
EKN100-54	0,25	0,50	6,70	220,0	3,0	58

Dimensions in mm

High Precision



DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-6%	On request

Part number	ØD1/ØD2 (H7)		ØA	C	L	G (DIN 916)	E (mm)	Nominal torque (Nm)	Price each	
	No keyway	With keyway							No keyway	With keyway
EKN4-20	3-9	6-8	16	6	20	M3	2,0	0,5	59,48 €	59,48 €
EKN4-23	3-9	6-8	16	6	23	M3	2,0	0,5	59,48 €	59,48 €
EKN4-26	3-9	6-8	16	6	26	M3	2,0	0,5	59,48 €	59,48 €
EKN9-21	3-9	6-8	16	6	21	M3	2,0	1,1	59,48 €	59,48 €
EKN9-25	3-9	6-8	16	6	25	M3	2,0	1,1	59,48 €	59,48 €
EKN9-28	3-9	6-8	16	6	28	M3	2,0	1,1	59,48 €	59,48 €
EKN15-25	3-12	6-10	20	10	25	2 x M4	3,0	1,75	59,48 €	59,48 €
EKN15-30	3-12	6-10	20	10	30	2 x M4	3,0	1,75	59,48 €	59,48 €
EKN20-26	3-16	6-14	25	11	26	2 x M3	2,0	2,4	59,48 €	59,48 €
EKN20-32	3-16	6-14	25	11	32	2 x M3	2,0	2,4	59,48 €	59,48 €
EKN20-36	3-16	6-14	25	11	36	2 x M3	2,0	2,4	59,48 €	59,48 €
EKN45-39	6-22	6-16	33	16	39	2 x M6	4,0	5,5	84,85 €	84,85 €
EKN45-48	6-22	6-16	33	16	48	2 x M6	4,0	5,5	84,85 €	84,85 €
EKN100-44	6-28	6-25	40	20	44	2 x M6	4,0	12	120,07 €	120,07 €
EKN100-54	6-28	6-25	40	20	54	2 x M6	4,0	12	120,07 €	120,07 €

Dimensions in mm

DKN GERWAH Couplings for servo-motors Torque: 0.4 to 10Nm

- Backlash and maintenance free
- Materials:
 - Hub: anodised aluminium
 - Bellows: stainless steel
- Angular misalignment from 1.2° to 2° depending on the length
- High torsional rigidity
- Low moment of inertia
- Shaft/bore link without backlash
- Max speed: 15,000 rpm
- Recommended assembly tolerances H7/g6
- Working temperature -30°C to +100°C
- **Please specify bore size on order (between min and max \varnothing)**

Options

- Keyway according to DIN6885 on request (tolerance JS9)
- Orientation of the keyways at 180° to each other

Info.

- The DK series is no longer available and has been replaced by the DKN range




Clamp hub

Part number	Nominal torque (Nm)	Misalignment			Torsional stiffness C _t (Nm/rad)	Moment of inertia J (g cm ²)	Tightening torque (Nm)	Weight (g)
		radial (ΔK) (mm)	axial (ΔK) (mm)	Angulaire (°)				
DKN4/21	0,5	0,10	0,20	1,2	0,25	2,6	0,3	5
DKN4/24	0,5	0,15	0,30	2,0	0,19	2,6	0,3	6
DKN4/28	0,5	0,20	0,40	2,0	0,15	2,6	0,3	7
DKN9/23	1,1	0,10	0,20	1,2	0,50	2,6	0,3	6
DKN9/26	1,1	0,15	0,30	2,0	0,38	2,9	0,3	7
DKN9/30	1,1	0,20	0,40	2,0	0,30	3,2	0,3	8
DKN15/26	1,75	0,10	0,25	1,2	0,75	11,0	0,8	12
DKN15/30	1,75	0,15	0,40	2,0	0,70	12,0	0,8	14
DKN20/32	2,4	0,10	0,30	1,2	1,50	25,0	1,5	20
DKN20/38	2,4	0,20	0,40	2,0	1,30	27,0	1,5	22
DKN20/42	2,4	0,25	0,50	2,0	1,00	28,0	1,5	24
DKN45/41	5,5	0,10	0,30	1,2	6,50	98,0	3,0	58
DKN45/50	5,5	0,20	0,50	2,0	4,00	103,0	3,0	62
DKN100/47	12,0	0,15	0,40	1,2	8,10	231,0	3,0	60
DKN100/57	12,0	0,25	0,50	2,0	6,70	250,0	3,0	70

Dimensions in mm

High Precision



DISCOUNTS

Qty	1+	2+	4+
Disc. List	-6%	On request	

Part number	D/D (H7)	ØA	C	L	F	øH undercut	G (DIN 912)	K	Price each	
									No keyway	With keyway
DKN4/21	3-8	16	7	21	2	18	M2	5	79,66 €	79,66 €
DKN4/24	3-8	16	7	24	2	18	M2	5	79,66 €	79,66 €
DKN4/28	3-8	16	7	28	2	18	M2	5	79,66 €	79,66 €
DKN9/23	3-8	16	7	23	2	18	M2	5	79,66 €	79,66 €
DKN9/26	3-8	16	7	26	2	18	M2	5	79,66 €	79,66 €
DKN9/30	3-8	16	7	30	2	18	M2	5	79,66 €	79,66 €
DKN15/26	3-10	20	9	26	3	21	M2,5	7	79,66 €	79,66 €
DKN15/30	3-10	20	9	30	3	21	M2,5	7	79,66 €	79,66 €
DKN20/32	3-14	25	11	32	4	27	M3	9	84,85 €	84,85 €
DKN20/38	3-14	25	11	38	4	27	M3	9	84,85 €	84,85 €
DKN20/42	3-14	25	11	42	4	27	M3	9	84,85 €	84,85 €
DKN45/41	5-17	33	13	41	5	34	M4	12	125,40 €	125,40 €
DKN45/50	5-17	33	13	50	5	34	M4	12	125,40 €	125,40 €
DKN100/47	5-24	40	14	47	5	42	M4	16	156,98 €	156,98 €
DKN100/57	5-24	40	14	57	5	42	M4	16	156,98 €	156,98 €

Dimensions in mm