


- Supplied with 2 nuts
- Material:
Zinc plated steel
- Not sold individually,
please contact us for details



DISCOUNTS




Qty	1+	101+	201+	301+	401+	501+
Disc. Prix	-5%	-10%	-15%	-20%	On request	

Part number	Nominal Ø DN	For tube external ØD	Internal tube Ød	Thread Ød	A (mm)	B (mm)	C (mm)	Stock*	Price each 1 to 100
EBM013	8	13	1/4	M6	28	18	19	✓	0,35 €
EBM017	10	17	3/8	M6	39	22	23	✓	0,38 €
EBM021	15	21	1/2	M6	41	24	27	✓	0,43 €
EBM027	20	27	3/4	M8	50	30	35	✓	0,60 €
EBM034	25	34	1	M8	55	32	42	✓	0,68 €
EBM042	32	42	1 ^{1/4}	M8	68	35	50	✓	0,70 €
EBM049	40	49	1 ^{1/2}	M8	70	36	57	✓	0,74 €
EBM060	50	60	2	M8	80	36	68	✓	0,85 €
EBM070	60	70	2 ^{1/4}	M8	100	40	78	✓	1,32 €
EBM076	65	76	2 ^{1/2}	M8	110	40	84	✓	1,42 €
EBM089	80	89	3	M10	116	40	99	✓	1,94 €
EBM102	90	102	3 ^{1/4}	M10	130	40	112	✓	2,24 €
EBM108	-	108	3 ^{1/2}	M10	135	40	118	-	3,02 €
EBM114	100	114	4	M10	156	40	124	-	3,25 €
EBM133	-	133	4 ^{3/4}	M10	175	40	143	✓	3,96 €
EBM139	125	139	5	M10	195	55	149	✓	5,25 €
EBM159	-	159	5 ^{1/2}	M12	195	50	171	✓	6,08 €
EBM168	150	168	6	M12	200	55	180	-	6,20 €
EBM219	200	219	8	M14	270	50	233	-	11,15 €

*Depending on availability - Dimensions in mm

- Supplied with 2 nuts
- Material:
Stainless steel 304
- Not sold individually,
please contact us for details

Stainless steel



DISCOUNTS

Qty	1+	101+	201+	301+	401+
Disc. Prix	-5%	-10%	-15%	On request	

Part number	Nominal Ø DN	For tube external ØD	Internal tube Ød	Thread Ød	A (mm)	B (mm)	C (mm)	Stock*	Price each 1 to 100
EIM013	8	13	1/4	M6	28	20	19	✓	1,37 €
EIM017	10	17	3/8	M6	36	22	23	-	1,68 €
EIM021	15	21	1/2	M6	40	20	27	✓	1,76 €
EIM027	20	27	3/4	M8	50	30	35	✓	3,25 €
EIM034	25	34	1	M8	55	30	42	✓	3,56 €
EIM042	32	42	1 ^{1/4}	M8	68	35	50	✓	4,03 €
EIM049	40	49	1 ^{1/2}	M8	70	35	57	✓	4,17 €
EIM060	50	60	2	M8	80	35	68	✓	4,33 €
EIM076	65	76	2 ^{1/2}	M8	110	45	84	-	5,20 €
EIM089	80	89	3	M10	115	45	99	-	9,37 €
EIM114	100	114	4	M10	156	55	124	-	10,59 €

*Depending on availability - Dimensions in mm