Well nut

ECF

Elastomer

- ***Flanged chloroprene elastomer moulded into a nut***





Advantages

- *Cost effective*
- *Isolation of noise and resonance*
- *Oil, fats, and ozone-resistant*
- *Simple and tool free installation*
- *Can be mounted in:*
  Compression - shearing
  Compression/shearing
- *Working temperature range: -30°C to +80°C*
- *Isolated vibrations from 120 to 150Hz*

Info.

- ***Not sold individually, please contact us for details***





Mounting type 1



Mounting type 2

DISCOUNTS

Qty	1+	13+	29+	41+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	Thread	ØD	ØE	L	K	Stock*	Price each 1 to 12
ECF3	M3	9	7,2	9,0	2,5	✔	1,74 €
ECF4	M4	12	9,3	11,5	3,0	✔	1,92 €
ECF5	M5	15	10,2	14,5	3,5	✔	2,22 €
ECF6	M6	18	12,7	17,0	4,0	✔	2,48 €
ECF8	M8	24	16,6	22,0	5,0	✔	2,75 €

**Depending on availability - Dimensions in mm*

Our other products


BOX-TOR-A

Box set of Nitrile O-rings in nitrile, 2.90 x 1.78mm to 28.17 x 3.53


PDD

Spring plunger, With sensor adaptor


FR

Steel thread inserts, Steel


BSM_LOK


Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...


INStool


Insertion tool for self tapping inserts, Insertion tool


PRF3232

Standard aluminium profile, 32 x 32 mm


PM2

Wormwheel , Machined plastic (delrin)


LAT2

2A motorised linear actuator, 2 amperes


RTE

Rotex®, jaw coupling, Aluminium


AT5P_AT10P

Connecting plate for AT type timing belts,


JCDss

Double universal joint - Stainless steel, Low


BOX-CS

Hose clamp, Box set of steel hose clamps

Complementary products