
# Tee nuts with pronge

## EGRM

## Steel

- **Socket nut that easily inserts into soft materials**
- Remains in place without turning
- Material :
  Steel zinc plated




### Advantages

- Tee nuts with pronge increase clamping quality in soft materials (wood, panels, chipboard, plastics)
- Repeated tightening without damaging the surface

### Info

- Sold by the packet




**DISCOUNTS**

| Qty | 1+ | 6+ | 10+ |
|---|---|---|---|
| Disc. | List | -10% | On request |

| Part number | Thread ØM | ØD2 | ØD3 | H | A | Qty per packet | Price per packet |
|---|---|---|---|---|---|---|---|
| EGRM4-6/B | M4 | 15 | 5 | 6 | 5 | 200 | |
| EGRM5-8/B | M5 | 17 | 6,5 | 8 | 7 | 200 | |
| EGRM6-9/B | M6 | 19 | 7,5 | 9 | 7 | 200 | |
| EGRM6-12/B | M6 | 19 | 7,5 | 12 | 8 | 200 | |
| EGRM8-11/B | M8 | 22 | 10 | 11 | 9 | 100 | |
| EGRM8-15/B | M8 | 22 | 10 | 15 | 10 | 100 | |
| EGRM10-13/B | M10 | 25 | 11,5 | 13 | 11 | 100 | |

*Dimensions in mm*

# Our other products



BLH50

Right angled gearbox, from 7.70 to 20 Nm



VAP

Magnetic stud with central hole, With central hole



HCSS

Set screw with hexagonal socket, Cup point



METC

Flanged sintered bronze bush, Self-lubricating sintered bronze



Q6

Deep groove ball bearing, Steel



VAB

Flanged nut for ball screw, For VAB ballscrew



IN2

Internal gear, Steel 20NCD2



CLM

Male clevis end, Stainless steel short



RPCtcss

Swivel castor with central hole, Stainless



SH0

Parallel axis helical gear, Steel 20NCD2



PLM-20SC

Cylindrical magnet, Cylindrical magnet



BAP25

Plastic clamping collar, Ø25 - Ø40

## Complementary products



INS100

Self tapping inserts-coarse thread, Coarse thread



INS150

Self tapping insert with collar-coarse thread, With collar-coarse t...



BOX-INS-W

Box set of self tapping inserts, Boxed set - For wood



MSP3815

Masterplate® glueable insert rectangular, rectangular with

tapped i...