Antistatic knurled nut

EMAS Prevents occurrence of electrostatic spark

Eliminates electrical charges


- *Materials :*
  Reinforced PA thermoplastic, graphite black
  Tapped bush in steel trivalent blue passivated

Advantages

- *These products can be used for electrostatic discharge applications or areas where electrostatic discharge protection (EPA) in accordance with DIN EN61340-5-1*
- *The knurled nuts can be tightened or loosened without tools*



Antistatic



DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØD	ØD1	ØD3	H	K	T	Price each 1 to 9
EMAS18-M4	M4	18	11	13	8	10	6,33 €
EMAS20-M5	M5	20	13,6	15	9	10	6,85 €
EMAS25-M6	M6	25	14	17	10	10	7,48 €
EMAS32-M8	M8	32	18	22	13	14	8,57 €
EMAS40-M10	M10	40	19	25	14	14	9,33 €

Dimensions in mm


Tightening knurled nut

Threads M5-M12


EMR


- ***For use in applications that do not require very high clamping forces***
- *Material: hardened steel*
- *Finish: hardened and blackened*






Threaded rod should be much longer than dimension “H”






1) Tilt, and slide down.



2) Level and tighten or loosen.



3) Tilt, and slide back up.

DISCOUNTS

Qty	1+	6+	20+	40+	60+	101+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØD1	ØD2	ØD3	ØD4	H	K	Weight (g)	Stock*	Price each 1 to 5
EMR-5	M5	20	14	5,2	12	8	25	✔	10,12 €
EMR-6	M6	24	16	6,2	14	10	38	✔	10,91 €
EMR-8	M8	30	20	8,2	17	12	75	✔	14,10 €
EMR-10	M10	36	28	10,3	20	14	130	✔	15,52 €
EMR-12	M12	40	32	12,3	24	16	185	✔	19,46 €


**Depending on availability - Dimensions in mm*


Stainless steel knurled thumb nut

EMSH
EMSB

Threads M3 to M12

- ***One-piece knurled nut***
- *Material: stainless steel 18.9*





Long version EMS-H



Short version EMS-B

DISCOUNTS

Qty	1+	6+	20+	40+	60+	101+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØD1	ØD2	ØD3	H	K	Stock*	Price each 1 to 5
Long version							
EMS-3H	M3	12	6	7,5	2,5	✔	1,18 €
EMS-4H	M4	16	8	9,5	3,5	✔	1,81 €
EMS-5H	M5	20	10	11,5	4,0	✔	2,10 €
EMS-6H	M6	24	12	15,0	5,0	✔	3,31 €
EMS-8H	M8	30	16	18,0	6,0	✔	7,27 €
EMS-10H	M10	36	20	23,0	8,0	✔	11,88 €
EMS-12H	M12	36	20	23,0	8,0	✔	23,03 €
Short version							
EMS-4B	M4	16	8	4,0	3,5	✔	1,36 €
EMS-5B	M5	20	10	5,0	4,0	✔	1,86 €
EMS-6B	M6	24	12	6,0	5,0	✔	2,93 €
EMS-8B	M8	30	16	8,0	6,0	✔	7,15 €
EMS-10B	M10	36	20	10,0	8,0	✔	12,92 €
EMS-12B	M12	36	20	10,0	8,0	✔	19,46 €

**Subject to availability - Dimensions in mm*


Stainless steel knurled thumb screw

Threads M4 to M10


VMS

- ***One-piece threaded screw***
- *Material: Polished stainless steel 303*
- *Operating element*
- *Conforms to DIN 464*
- *** These thumb screws are supplied with shaft threaded along the entire length (no undercut)*





Typical application



DISCOUNTS

Qty	1+	6+	20+	40+	60+	101+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØD1	ØD2	ØD3	H	K	L	Stock*	Price each 1 to 5
VMS4-10	M4	16	8	9,5	3,5	10	✔	2,81 €
VMS4-16	M4	16	8	9,5	3,5	16	✔	3,12 €
VMS4-20	M4	16	8	9,5	3,5	20**	✔	3,41 €
VMS5-10	M5	20	10	11,5	4,0	10	✔	3,47 €
VMS5-16	M5	20	10	11,5	4,0	16	✔	4,13 €
VMS5-20	M5	20	10	11,5	4,0	20**	✔	4,99 €
VMS6-10	M6	24	12	15,0	5,0	10	✔	7,50 €
VMS6-16	M6	24	12	15,0	5,0	16	✔	5,83 €
VMS6-20	M6	24	12	15,0	5,0	20	✔	10,57 €
VMS6-25	M6	24	12	15,0	5,0	25**	✔	8,59 €
VMS8-16	M8	30	16	18,0	6,0	16	✔	13,38 €
VMS8-20	M8	30	16	18,0	6,0	20	✔	14,51 €
VMS8-25	M8	30	16	18,0	6,0	25	✔	13,79 €
VMS10-20	M10	36	20	23,0	8,0	20	✔	24,37 €
VMS10-25	M10	36	20	23,0	8,0	25	✔	27,43 €

**Subject to availability - Dimensions in mm*

Stainless steel hexagonal headed thumb nut Stock*

EML


Threads M5 to M12

- ***One piece construction***
- *Material: stainless steel 304*
- *Finish: polished*

Advantages

- *Does not retain dirt or dust*





Polished finish

DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	ØF	ØD	ØD1	H	H1	G	Stock*	Price each 1 to 5
EML5-27	M5	27	15	19	10,0	10	✔	26,09 €
EML6-33	M6	33	19	23	12,0	12	✔	32,73 €
EML8-40	M8	40	21	27	15,0	13	✔	40,85 €
EML10-50	M10	50	25	33	17,5	17	✔	53,69 €
EML12-60	M12	60	27	37	20,0	20	✔	70,12 €

**Subject to availability - Dimensions in mm*

Sta Stock Stainless steel hexagonal headed thumb screw

Threads M6 to M12

VML

- **One piece construction**
- Operating elements
- Material: stainless steel 304
- Finish: polished

Advantages

- Does not retain dirt or dust


Applications

- Chemical, pharmaceutical and food industries

Polished finish



Solid stainless steel



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	ØF	ØD	ØD1	H	H1	G	Stock*	Price each 1 to 5
VML6-27	M6	27	15	30	10,0	10	✔	30,35 €
VML8-33	M8	33	19	43	11,0	20	✔	37,33 €
VML8-40	M8	40	21	47	15,0	20	✔	51,37 €
VML10-50	M10	50	25	63	17,5	30	✔	60,69 €
VML12-60	M12	60	27	77	20,0	40	✔	84,20 €

*Subject to availability - Dimensions in mm