

Flanged nut for high helix lead-screw

EPRF

Up to 40mm
of travel per rotation




- Nut only
- Right handed thread
- Lubricant free, low wear
- Material:
Iglidur J

Accessories

- Used efficiency irrespective of speed

Advantages

- High efficiency irrespective of speed
- Low wear
- Excellent coefficient of friction
- High speed



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	Pitch P	ØD1 (mm)	ØD2	ØD3	ØD4	ØD5	B1	B2	Max axial static force (N)	Stock*	Price each
										1 to 4	
EPRF6.35-2.54	6,35	2,54	13	25	19	3,2	15	5	125	-	34,86 €
EPRF6.35-25.4	6,35	25,4	13	25	19	3,2	15	5	125	-	34,86 €
EPRF10-12	10	12	25	42	34	5	25	10	845	✓	47,08 €
EPRF10-25	10	25	25	42	34	5	25	10	780	-	43,84 €
EPRF10-50	10	50	25	42	34	5	25	10	453	-	51,89 €
EPRF14-25	14	25	28	48	38	6	35	12	1428	✓	56,89 €
EPRF14-30	14	30	28	48	38	6	35	12	1428	-	59,75 €
EPRF18-40	18	40	28	48	38	6	35	12	1910	✓	71,71 €

Dimensions in mm

Our other products



PRF4590
Standard aluminium
profile, 45 x 90 mm



PITA
Locking bolt, with T
handle



AK
Bellows coupling
Gerwah®, from 36 to
800Nm



SHA_PT
Handwheel with
handle, Polyamide



SLV
Vertical toggle clamp,
Vertical Lever Clamp -
steel




BTCW
Cap for square tube to
be welded, To be
welded



PV2R
Adjustable suction-
cup support,
Increased grip



GG1
Ground spur gear,
Heat treated steel



PRZ
Wear strip for slat top
chain, Z profile to be
welded



RBG
Wheel, Grey rubber -
Polypropylene rim




CHTRP
Single and dual
output gearboxes, Up
to 400Nm



BRI
Panel holder, Panel
holder

Complementary products



TPR
High helix leadscrew,
Leadscrew only - up
to 40mm per rotation



EPRC
High helix leadscrew,
Cylindrical nut - up to
40mm per rotation