Stainless steel cable terminal

Sta

EVC


Fork version

- ***Cable terminal to be screwed***
- *Material :*
  Stainless steel 316

Accessories

- **CAB** *cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	A	ØB	C	L	Weight (g)	Price each 1 to 3
EVC2-37/SS	2	4,5	8	7	37	16,5	
EVC3-50/SS	3	5,5	10	8	50	30,0	
EVC4-52/SS	4	6,5	12	8	52	46,0	

Dimensions in mm

Stainless steel cable terminal

Threaded rod version


EVF

- ***Cable terminal to be screwed***
- *Thread ISO pitch right hand*
- *Delivered with a nut*
- *Material :*
  Stainless steel 316

Accessories

- ***CAB** cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	ØM	ØB	E	L	Weight (g)	Price each 1 to 3
EVF2-50-M4/SS	2	M4	8	20	50	11,0	
EVF3-56-M4/SS	3	M4	10	20	56	19,0	
EVF4-80-M5/SS	4	M5	12	40	80	51,5	

Dimensions in mm

Stainless steel cable terminal

Sta

EVY


Eye version

- ***Cable terminal to be screwed***
- *Material :*
  Stainless steel 316

Accessories

- **CAB** *cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	ØA	ØB	L	Weight (g)	Price each 1 to 3
EVY2-37/SS	2	4,5	8	37	13	
EVY3-50/SS	3	5,5	10	50	27	
EVY4-52/SS	4	6,5	12	52	41	

Dimensions in mm

Stainless steel cable terminal


Threaded hole version


EVT

- ***Cable terminal to be screwed***
- *Thread ISO pitch right hand*
- *Delivered with a nut*
- *Material :*
  Stainless steel 316

Accessories

- **CAB** *cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	ØM	ØB	P	L	Weight (g)	Price each 1 to 3
EVT2-55-M5/SS	2	M5	8	20	55	16,0	
EVT3-65-M5/SS	3	M5	10	25	65	33,0	
EVT4-70-M6/SS	4	M6	12	25	70	51,5	

Dimensions in mm

Our other products



Protective cap, Safety cap



Horizontal toggle clamp, Horizontal toggle clamp / vertical foot



Silicone conical elasto buffer, Male mounting



Nut for aluminium profile, Steel square nut with tab



RPP heavy duty timing belt, RPP5



Cable clip for aluminium profile, For cable chute



Parallel axis helical gear, Steel 20NCD2



Crossed helical gear crossed axis at 90°, Steel 20NCD2




Split shaft collar with clamp lever, Steel



Magnetic stud with central hole, With



Wing screw, hand tightened DIN316,



Worm and wheel gear reducer, up to 5 Nm

Complementary products



Quick fitting cable terminal, Fork



Quick fitting cable terminal, Eye version



Quick fitting threaded cable terminal, Cable terminal with threaded ...



Galvanised steel cable, Galvanised steel