

Ratio 4:1

Steel C43


- Module 1 to 5
- Teeth conform to DIN 3967 except for Module 1 models which are Gleason
- Pressure angle: 20°
- Material: steel C43
- A pair requires 2 gears

New module 1



Info.

- **Pilot bore dimensions given as a guide only and are subject to change.



**CANNOT BE MODIFIED
BUDGET
RANGE
BY OURSELF**

DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-5%	On request

Part number	Teeth		ØD _n	ØD _e	F	L	ØD _m	Pilot bore not guaranteed		V	S	Lm	Stock*	Price each 1 to 3
	Z	mod						ØA**	V					
FB1-15/ECO	15	1	15	17,8	9,3	17,2	13,3	4	20,8	-	7,7	-	19,77 €	
FB1-60/ECO	60	1	60	60,3	9,3	17,1	30,3	8	4,9	1,9	10	-	76,44 €	
FB1.5-16/ECO	16	1,5	24	26,91	12	25,0	18	10	36,02	1,0	12,2	✓	20,28 €	
FB1.5-64/ECO	64	1,5	96	96,73	12	22,0	70	15	8,53	3,0	10,0	✓	89,49 €	
FB2-16/ECO	16	2	32	35,88	15	24,0	25	12	49,07	1,0	8,2	✓	25,07 €	
FB2-64/ECO	64	2	128	128,97	15	24,0	80	20	11,79	4,0	10,0	✓	121,36 €	
FB2.5-16/ECO	16	2,5	40	44,85	18	30,5	30	12	61,99	1,5	11,7	-	38,27 €	
FB2.5-64/ECO	64	2,5	160	161,21	18	29,0	90	20	13,77	5,0	10,0	-	144,78 €	
FB3-16/ECO	16	3	48	53,82	22	34,0	40	15	74,05	2,0	11,0	-	46,72 €	
FB3-64/ECO	64	3	192	193,45	22	30,0	100	20	16,41	6,0	10,0	-	280,30 €	
FB3.5-16/ECO	16	3,5	56	62,80	25	45,0	48	15	87,13	2,0	19,1	-	54,42 €	
FB3.5-64/ECO	64	3,5	224	225,70	25	50,0	100	20	19,32	7,0	22,0	-	429,77 €	
FB4-16/ECO	16	4	64	71,76	30	50,0	50	20	98,21	2,0	18,5	-	63,85 €	
FB4-64/ECO	64	4	256	257,94	30	50,0	120	20	21,72	8,0	20,0	-	523,20 €	
FB4.5-16/ECO	16	4,5	72	80,73	32	53,0	55	20	112,08	2,5	19,0	-	70,54 €	
FB4.5-64/ECO	64	4,5	288	290,18	32	53,0	130	20	24,83	9,0	23,0	-	814,44 €	
FB5-16/ECO	16	5	80	89,70	35	58,0	60	20	125,06	2,5	20,6	-	80,10 €	
FB5-64/ECO	64	5	320	322,42	35	58,0	150	20	27,65	10,0	25,0	-	1 009,12 €	

*Depending on availability - Dimensions in mm

Our other products



PTA100
Articulated levelling
foot, pressed base
Ø100, Ø 100



VTAP
Magnetic head screw,
With rubber coating
With rubber coating




RBGpl
Fixed castor with
plate, Steel - grey
rubber



DOMI80
Domino 80 adjustable
slide, Slide DOMILINE
80



SH2
Parallel axis helical
gear, Steel 20NCD2



TBL
Mini leadscrew table
with metric thread,
Base plate




UGH25
H Type Guide units,
For Ø25 actuators



KKP-AR
Linear bearing with
inclined ball tracks,
Heavy loads / -20°
+200°



BOX-TOR-ORFS
Box set of Nitrile O-
rings NBR90Sh A, 7.65
x 1.78mm to 37.82 x



HCV
V-rail guidance
Simple Select®
system, on rail



ASL
45° Hoist ring for
welding, for 45° lifts -
for welding



SVT20
Screwjack with
travelling screw, with
translating screw

Complementary products