Sealing brush strips

FBL

Advantages and applications

Advantages



- No wastage, only the length required is removed from the roll.
- Reduced storage/transport space, each box contains 25 metres.



- Special scissors allow the strip to be cut to the required length.




- Flexible in terms of positioning and fitting.


Applications



- Splash guard for wheel arches on a lorry



- Waterproofness of floor cleaning machines




- Guiding PET bottles

Brush strip horsehair fibres Ø0.2

For ensuring a seal up to 125°C

FBL6000
FBL6001

Brush strip to cut to desired length.



Horsehair fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Horsehair. No risk of static charge, excellent for dusting, brushing, sealing and for applying liquids (can be used as paintbrush)*
  Maximum temperature: +150°C
- ***Support:*** *Thermoplastic rubber.*
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length* **FBL-TOOL**



FBL6001
90° profile



FBL6000
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black horsehair								
FBL6000-K19	-	0,2	15	5m	✔	-	63,64 €	-
FBL6000-K20	-	0,2	20	5m	✔	-	68,86 €	-
FBL6000-K21	FBL6001-K21	0,2	25	5m	-	✔	74,33 €	74,33 €
FBL6000-K23	FBL6001-K23	0,2	40	5m	✔	-	92,79 €	92,79 €
FBL6000-K24	FBL6001-K24	0,2	50	5m	✔	✔	108,10 €	108,10 €
Tools								
FBL-TOOL		Cutting scissors						193,51 €

**Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 **cial2@hpceurope.com**

Brush strip PA6 fibres Ø0.2 to Ø0.3

Stock*

FBL6000
FBL6001

For ensuring an internal seal

Brush strip to cut to desired length.



PA6 fibres

Uses


- Sealing
- Cable entries
- Guiding parts

Materials

- ***Fibres:*** Polyamide PA6. Standard material for brushes used for cleaning, transporting, guiding or sealing moving pieces.
  Working temperature: -20 to 100°C
- ***Support:*** Thermoplastic rubber.
  Good UV and ozone resistance.
  Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length*
  FBL-TOOL



FBL6001
90° profile

FBL6000
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	Part number 90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	Price each 90° profile
Black Polyamide 6 (PA6) fibres								
FBL6000-K1	FBL6001-K1	0,2	10	5m	✔	✔	48,53 €	48,53 €
FBL6000-K2	FBL6001-K2	0,2	15	5m	✔	✔	49,78 €	49,78 €
FBL6000-K3	FBL6001-K3	0,2	20	5m	✔	✔	51,26 €	51,26 €
FBL6000-K4	-	0,2	25	5m	✔	-	52,74 €	-
FBL6000-K5	FBL6001-K5	0,2	30	5m	✔	✔	54,21 €	54,21 €
FBL6000-K7	-	0,3	15	5m	✔	-	49,78 €	-
FBL6000-K8	-	0,3	20	5m	✔	-	51,26 €	-
FBL6000-K9	-	0,3	25	5m	✔	-	52,74 €	-
FBL6000-K10	-	0,3	30	5m	✔	-	54,21 €	-
FBL6000-K11	-	0,3	40	5m	✔	-	57,33 €	-
FBL6000-K12	-	0,3	50	5m	✔	-	60,29 €	-
Tools								
FBL-TOOL	Cutting scissors							193,51 €


**Depending on availability - Dimensions in mm*

Stock Brush strip PA6 fibres Ø0.3 to Ø0.5

For ensuring an internal seal

FBL4004
FBL4005

Brush strip to cut to desired length.



PA6 fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Polyamide PA6. Standard material for brushes used for cleaning, transporting, guiding or sealing moving pieces.*
  Working temperature: -20 to 100°C
- ***Support:*** *Thermoplastic rubber. Good UV and ozone resistance. Practically unaffected by most chemicals.*
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length* **FBL-TOOL**



FBL4005
90° profile



FBL4004
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black Polyamide 6 (PA6) fibres								
FBL4004-K8	-	0,3	20	5m	✔	-	140,75 €	-
FBL4004-K9	-	0,3	30	5m	✔	-	147,61 €	-
FBL4004-K13	-	0,5	30	5m	✔	-	147,61 €	-
FBL4004-K14	-	0,5	40	5m	✔	-	154,69 €	-
FBL4004-K15	-	0,5	50	5m	✔	-	161,80 €	-
FBL4004-K18	FBL4005-K15	0,5	80	5m	✔	✔	193,81 €	193,81 €
Tools								
FBL-TOOL	Cutting scissors							193,51 €

**Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 **cial2@hpceurope.com**


Brush strip PP fibres Ø0.2

Stock*

FBL6000
FBL6001

For ensuring an external seal

Brush strip to cut to desired length.



Uses


- Sealing
- Cable entries
- Guiding parts

Materials

- **Fibres:** Polypropylene. No water absorption, good resistance to chemicals...
  Working temperature: -20 (occasional) to 80°C
- **Support:** Thermoplastic rubber.
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- **Sold in 5 metre lengths.**
- Maximum length of a single brush is 25 metres.
- Special scissors for cutting to length
  FBL-TOOL



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	Part number 90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	Price each 90° profile
Black horsehair								
FBL6000-K13	FBL6001-K13	0,2	10	5m	✔	✔	44,56 €	44,56 €
FBL6000-K14	FBL6001-K14	0,2	15	5m	✔	✔	44,98 €	44,98 €
FBL6000-K15	FBL6001-K15	0,2	20	5m	✔	✔	45,38 €	45,38 €
FBL6000-K17	FBL6001-K17	0,2	30	5m	✔	-	46,66 €	46,66 €
FBL6000-K18	FBL6001-K18	0,2	40	5m	✔	✔	47,69 €	47,69 €
Tools								
FBL-TOOL		Cutting scissors						193,51 €

*Depending on availability - Dimensions in mm

Brush strip PP fibres Ø0.3

For ensuring an external seal

FBL4004
FBL4005

Brush strip to cut to desired length.



PP fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Polypropylene. No water absorption, good resistance to chemicals...*
  Working temperature: -20 (occasional) to 80°C
- ***Support:*** *Thermoplastic rubber.*
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length*
  FBL-TOOL



FBL4005
90° profile



FBL4004
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black Polyamide 6 (PA6) fibres								
FBL4004-K34	-	0,3	30	5m	✔	-	130,13 €	-
FBL4004-K35	-	0,3	40	5m	✔	-	132,49 €	-
FBL4004-K36	FBL4005-K31	0,3	50	5m	✔	✔	134,99 €	134,99 €
FBL4004-K37	FBL4005-K32	0,3	60	5m	✔	-	137,47 €	137,47 €
FBL4004-K38	-	0,3	70	5m	✔	-	151,08 €	-
Tools								
FBL-TOOL				Cutting scissors				193,51 €

**Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 **cial2@hpceurope.com**

WEB 04/2021

HPC

Our other products


T5M_T10M

T type timing belt per metre, T5 Steel cored polyurethane


GE1006

Elastic ringed latch, Hooks into a slot


PCS50SS

Chain sprocket - Stainless steel, 12.7mm (DIN 08B-1)


EHD12

Internal epicyclic servo reducers, from 60 to 140 Nm


UTKpwrr

V shaped channel UtiliTrak®, V rail


CHMR75

Worm and wheel gear reducer, up to 298 Nm


BPTR

End cap for round tube, Standard


RPP8

RPP heavy duty timing belt, RPP8


PDR-RD

Mounting feet with integrated castors,


PW_PWG2

Worm - precision range, Steel


ESCON

Speed controller 5A accessories, Kit of 4


PM4

Worm and wheel set, Hardened steel

Complementary products


STRIP

Sealing brush strip, 3m length


STRIPF

Sealing brush strip, 1m length


Our other products



Decorative hinge, Stainless steel



Right angle spiro bevel gearbox, Up to 43Nm



Wormwheel , Machined plastic (delrin)



Articulated foot with solid base foot Ø 40, 3000N



Horizontal hook toggle clamp, Horizontal Hook clamp - steel



Conical compression spring, Conical



Miniature cam follower, Miniature




T type timing belt per metre, T10 Steel cored polyurethane



Slotted spring plunger with ball tip, Stainless



Quick link, Steel



Stainless steel/Polymer flanged




Fixed levelling foot, Flanged plate

Complementary products



Sealing brush strip, 3m length



Sealing brush strip, 1m length