
Brush strip horsehair fibres Ø0.2

For ensuring a seal up to 125°C

FBL6000
FBL6001

Brush strip to cut to desired length.



Horsehair fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Horsehair. No risk of static charge, excellent for dusting, brushing, sealing and for applying liquids (can be used as paintbrush)*
  Maximum temperature: +150°C
- ***Support:*** *Thermoplastic rubber.*
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length* **FBL-TOOL**



FBL6001
90° profile



FBL6000
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number		Bristle diameter			Stock*	Stock*	Price each	
Straight profile	90° profile	(mm)	BH	Length	Straight profile	90° profile	Straight profile	90° profile
Black horsehair								
FBL6000-K19	-	0,2	15	5m	✔	-	69,53 €	-
FBL6000-K20	-	0,2	20	5m	-	-	On request	-
FBL6000-K21	FBL6001-K21	0,2	25	5m	-	-	On request	On request
FBL6000-K23	FBL6001-K23	0,2	40	5m	-	-	On request	On request
FBL6000-K24	FBL6001-K24	0,2	50	5m	-	-	On request	On request
Tools								
FBL-TOOL		Cutting scissors						211,41 €

**Depending on availability - Dimensions in mm*

Brush strip PA6 fibres Ø0.2 to Ø0.3

Stock

FBL6000
FBL6001

For ensuring a sealing indoor

Brush strip to cut to desired length.



PA6 fibres

Uses


- Sealing
- Cable entries
- Guiding parts

Materials

- **Fibres:** Polyamide PA6. Standard material for brushes used for cleaning, transporting, guiding or sealing moving pieces.
  Working temperature: -20 to 100°C
- **Support:** Thermoplastic rubber.
  Good UV and ozone resistance.
  Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- **Sold in 5 metre lengths.**
- Maximum length of a single brush is 25 metres.
- Special scissors for cutting to length **FBL-TOOL**



FBL6001 90° profile | **FBL6000 Straight profile**

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	Part number 90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	Price each 90° profile
Black Polyamide 6 (PA6) fibres								
FBL6000-K1	FBL6001-K1	0,2	10	5m	✔	-	53,03 €	On request
FBL6000-K2	FBL6001-K2	0,2	15	5m	✔	✔	54,39 €	54,39 €
FBL6000-K3	FBL6001-K3	0,2	20	5m	✔	-	56,00 €	On request
FBL6000-K4	-	0,2	25	5m	✔	-	57,62 €	-
FBL6000-K5	FBL6001-K5	0,2	30	5m	✔	-	59,23 €	On request
FBL6000-K7	-	0,3	15	5m	-	-	On request	-
FBL6000-K8	-	0,3	20	5m	-	-	On request	-
FBL6000-K9	-	0,3	25	5m	-	-	On request	-
FBL6000-K10	-	0,3	30	5m	✔	-	59,23 €	-
FBL6000-K11	-	0,3	40	5m	✔	-	62,63 €	-
FBL6000-K12	-	0,3	50	5m	✔	-	65,87 €	-
Tools								
FBL-TOOL	Cutting scissors							211,41 €


*Depending on availability - Dimensions in mm

Brush strip PA6 fibres Ø0.3 to Ø0.5

For ensuring a sealing indoor

FBL4004
FBL4005

Brush strip to cut to desired length.



PA6 fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Polyamide PA6. Standard material for brushes used for cleaning, transporting, guiding or sealing moving pieces.*
  Working temperature: -20 to 100°C
- ***Support:*** *Thermoplastic rubber. Good UV and ozone resistance. Practically unaffected by most chemicals.*
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length* **FBL-TOOL**



FBL4005
90° profile



FBL4004
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black Polyamide 6 (PA6) fibres								
FBL4004-K8	-	0,3	20	5m	-	-	On request	-
FBL4004-K9	-	0,3	30	5m	-	-	On request	-
FBL4004-K13	-	0,5	30	5m	✔	-	161,27 €	-
FBL4004-K14	-	0,5	40	5m	-	-	On request	-
FBL4004-K15	-	0,5	50	5m	-	-	On request	-
FBL4004-K18	FBL4005-K15	0,5	80	5m	✔	✔	211,75 €	211,75 €
Tools								
FBL-TOOL	Cutting scissors							211,41 €

**Depending on availability - Dimensions in mm*


Brush strip PP fibres Ø0.2

Stock*

FBL6000
FBL6001

For ensuring a sealing outdoor

Brush strip to cut to desired length.



Uses


- Sealing
- Cable entries
- Guiding parts

Materials

- **Fibres:** Polypropylene. No water absorption, good resistance to chemicals...
  Working temperature: -20 (occasional) to 80°C
- **Support:** Thermoplastic rubber.
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- **Sold in 5 metre lengths.**
- Maximum length of a single brush is 25 metres.
- Special scissors for cutting to length
  FBL-TOOL



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black horsehair								
FBL6000-K13	FBL6001-K13	0,2	10	5m	✔	✔	48,68 €	48,68 €
FBL6000-K14	FBL6001-K14	0,2	15	5m	✔	-	49,15 €	On request
FBL6000-K15	FBL6001-K15	0,2	20	5m	✔	-	49,58 €	On request
FBL6000-K17	FBL6001-K17	0,2	30	5m	-	-	On request	50,97 €
FBL6000-K18	FBL6001-K18	0,2	40	5m	✔	✔	52,11 €	52,11 €
Tools								
FBL-TOOL				Cutting scissors				211,41 €

*Depending on availability - Dimensions in mm

Brush strip PP fibres Ø0.3

For ensuring a sealing outdoor

FBL4004
FBL4005

Brush strip to cut to desired length.



PP fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Polypropylene. No water absorption, good resistance to chemicals...*
  Working temperature: -20 (occasional) to 80°C
- ***Support:*** *Thermoplastic rubber.*
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length*
  FBL-TOOL



FBL4005
90° profile



FBL4004
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number		Bristle diameter			Stock*	Stock*	Price each	
Straight profile	90° profile	(mm)	BH	Length	Straight profile	90° profile	Straight profile	90° profile
Black Polyamide 6 (PA6) fibres								
FBL4004-K34	-	0,3	30	5m	-	-	On request	-
FBL4004-K35	-	0,3	40	5m	-	-	On request	-
FBL4004-K36	FBL4005-K31	0,3	50	5m	-	✔	On request	147,48 €
FBL4004-K37	FBL4005-K32	0,3	60	5m	✔	-	150,19 €	On request
FBL4004-K38	-	0,3	70	5m	✔	-	165,05 €	-
Tools								
FBL-TOOL			Cutting scissors					211,41 €

**Depending on availability - Dimensions in mm*