

Countersunk screw **DIN 7991**



FHCss

Stainless steel A2


- Material: Stainless steel 302/304 - A2
- Hexagonal socket
- Sold by the packet

Uses

- Suitable for harsh environments

Info.


- Dimension B is for information only and can vary depending on manufacture
- Supplied by pack



Designer's Note

Countersunk heads

Thread	ØF (H13)		T
	num.	max.	
M3	6,60	6,82	1,60
M4	9,80	10,02	2,65
M5	10,90	11,17	2,70
M6	13,20	13,47	3,30
M8	18,10	18,43	4,55
M10	21,00	21,33	5,00
M12	25,20	25,53	5,85



DISCOUNTS

N° packets	1+	2+	4+
Disc.	List	-20%	On request

Part number	Thread		Total length L	B	DK	K	S	Qty per packet	Stock*	Price per packet
	ØM	Pitch								
FHC3-8/SS/B	M3	0,50	8	-	6	1,6	2,0	500	✓	22,22 €
FHC3-12/SS/B	M3	0,50	12	-	6	1,6	2,0	500	✓	33,94 €
FHC3-16/SS/B	M3	0,50	16	-	6	1,6	2,0	500	✓	34,22 €
FHC3-20/SS/B	M3	0,50	20	-	6	1,6	2,0	500	✓	26,45 €

*Depending on availability - Dimensions in mm

DISCOUNTS

N° packets	1+	2+	4+
Disc.	List	-20%	On request

Part number	Thread		Total length L	B	DK	K	S	Qty per packet	Stock*	Price per packet
	ØM	Pitch								
FHC4-10/SS/B	M4	0,70	10	-	8	2,3	2,5	500	✓	23,71 €
FHC4-12/SS/B	M4	0,70	12	-	8	2,3	2,5	500	✓	27,21 €
FHC4-16/SS/B	M4	0,70	16	-	8	2,3	2,5	500	✓	21,48 €
FHC4-20/SS/B	M4	0,70	20	-	8	2,3	2,5	500	✓	21,48 €
FHC4-25/SS/B	M4	0,70	25	-	8	2,3	2,5	500	✓	32,70 €
FHC4-30/SS/B	M4	0,70	30	20	8	2,3	2,5	200	✓	18,79 €
FHC5-10/SS/B	M5	0,80	10	-	10	2,8	3,0	500	✓	27,37 €
FHC5-12/SS/B	M5	0,80	12	-	10	2,8	3,0	500	✓	23,32 €
FHC5-16/SS/B	M5	0,80	16	-	10	2,8	3,0	500	✓	30,86 €
FHC5-20/SS/B	M5	0,80	20	-	10	2,8	3,0	500	✓	36,55 €
FHC5-25/SS/B	M5	0,80	25	-	10	2,8	3,0	500	✓	38,20 €
FHC5-30/SS/B	M5	0,80	30	-	10	2,8	3,0	200	✓	18,80 €
FHC5-35/SS/B	M5	0,80	35	22	10	2,8	3,0	200	-	24,09 €
FHC6-10/SS/B	M6	1,00	10	-	12	3,3	4,0	500	✓	44,88 €
FHC6-12/SS/B	M6	1,00	12	-	12	3,3	4,0	500	✓	36,92 €
FHC6-16/SS/B	M6	1,00	16	-	12	3,3	4,0	500	✓	51,06 €
FHC6-20/SS/B	M6	1,00	20	-	12	3,3	4,0	200	✓	17,12 €
FHC6-25/SS/B	M6	1,00	25	-	12	3,3	4,0	200	✓	21,17 €
FHC6-30/SS/B	M6	1,00	30	-	12	3,3	4,0	200	✓	24,70 €
FHC6-35/SS/B	M6	1,00	35	-	12	3,3	4,0	200	✓	24,24 €
FHC6-40/SS/B	M6	1,00	40	-	12	3,3	4,0	200	-	32,04 €
FHC6-45/SS/B	M6	1,00	45	-	12	3,3	4,0	100	-	14,40 €
FHC6-60/SS/B	M6	1,00	60	20	12	3,3	4,0	100	-	22,34 €
FHC6-70/SS/B	M6	1,00	70	20	12	3,3	4,0	100	-	31,78 €
FHC8-16/SS/B	M8	1,25	16	-	16	4,4	5,0	200	✓	28,58 €
FHC8-20/SS/B	M8	1,25	20	-	16	4,4	5,0	200	✓	42,80 €
FHC8-25/SS/B	M8	1,25	25	-	16	4,4	5,0	100	✓	18,04 €
FHC8-30/SS/B	M8	1,25	30	-	16	4,4	5,0	100	✓	21,24 €
FHC8-40/SS/B	M8	1,25	40	-	16	4,4	5,0	100	✓	26,23 €
FHC8-50/SS/B	M8	1,25	50	-	16	4,4	5,0	100	-	36,66 €
FHC10-35/SS/B	M10	1,50	35	-	20	5,5	6,0	100	✓	38,83 €
FHC10-40/SS/B	M10	1,50	40	-	20	5,5	6,0	100	-	34,60 €
FHC10-50/SS/B	M10	1,50	50	32	20	5,5	6,0	100	-	42,35 €
FHC12-30/SS/B	M12	1,75	30	-	24	6,5	8,0	50	-	21,01 €
FHC12-40/SS/B	M12	1,75	40	36	24	6,5	8,0	50	-	26,31 €
FHC12-50/SS/B	M12	1,75	50	36	24	6,5	8,0	50	-	31,15 €
FHC12-60/SS/B	M12	1,75	60	36	24	6,5	8,0	50	-	40,71 €
FHC12-70/SS/B	M12	1,75	70	36	24	6,5	8,0	50	-	45,59 €
FHC12-80/SS/B	M12	1,75	80	36	24	6,5	8,0	50	-	52,93 €

*Depending on availability - Dimensions in mm