


- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

### Option

- Alternative number of teeth, up to 198

Torque and power indication			
For 50 teeth at 1000 rpm			
	20NCD2	20NCD2	
	Z10CNF18.09	hardened	brass
Nm	0.990	4.570	0.480
kW	0.104	0.477	0.057



### DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5	
						G	PG	G	PG
G0.75-11	11	9,00	10,50	10,50	4	0,007	0,002	27,70 €	On request
G0.75-13	13	9,75	11,25	11,25	5	0,008	0,003	28,29 €	
G0.75-14	14	10,50	12,00	12,00	5	0,009	0,003	28,92 €	
G0.75-15	15	11,25	12,75	12,00	5	0,009	0,004	29,67 €	
G0.75-17	17	12,75	14,25	12,00	5	0,011	0,005	31,28 €	
G0.75-18	18	13,50	15,00	12,00	5	0,011	0,006	31,91 €	
G0.75-20	20	15,00	16,50	12,00	5	0,013	0,007	32,48 €	
G0.75-22	22	16,50	18,00	12,00	5	0,015	0,009	33,17 €	
G0.75-24	24	18,00	19,50	12,00	5	0,017	0,011	33,82 €	
G0.75-25	25	18,75	20,25	12,00	5	0,017	0,012	34,17 €	
G0.75-28	28	21,00	22,50	12,00	5	0,021	0,015	34,88 €	
G0.75-30	30	22,50	24,00	12,00	5	0,023	0,017	35,18 €	
G0.75-40	40	30,00	31,50	16,00	6	0,042	0,031	35,90 €	
G0.75-45	45	33,75	35,25	16,00	6	0,050	0,040	36,51 €	
G0.75-60	60	45,00	46,50	16,00	6	0,082	0,072	39,14 €	
G0.75-70	70	52,50	54,00	16,00	8	0,106	0,097	41,04 €	
G0.75-72	72	54,00	55,50	16,00	8	0,112	0,103	42,22 €	
G0.75-100	100	75,00	76,50	16,00	8	0,210	0,201	69,47 €	
G0.75-150	150	112,50	114,00	20,00	10	0,470	0,454	113,65 €	
G0.75-180	180	135,00	136,50	30,00	12	0,671	0,655	154,78 €	
↓ <b>Gears available up to this size</b>									
G0.75-184	184	138,00	139,50	Dimensions: contact us					

Dimensions in mm