Decorative rigid latch clamp


GAE

With or without key


- ***Snap closing***
- *Supplied with 2 identical keys for the key versions*
- *Supplied with catch plate*
- *Material:*
  Die cast zinc black coating











DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-3%	-5%	On request

Part number	A	B	C	E	F	G	Weight (g)	Price each 1 to 9
Without key								
GAE17-64	64,5	26,5	17,3	13	12	30	72	
GAE21-76	76	32	21	16,8	16	35,5	118	
With key								
GAE17-64/K	64,5	26,5	17,3	13	12	30	72	
GAE21-76/K	76	32	21	16,8	16	35,5	118	

Dimensions in mm

Our other products


GPLso

Brush, silk


BOX-TOR-DRING

Box set of Nitrile D-rings NBR90Sh A, Flange seals


LRM

Trapezoidal bronze nut, Bronze - 1 thread


PW_PWG15


Wheel - precision range, Bronze


NT63

Spur gear coaxial gearbox, from 8 to 20 Nm - Inline


WSRM

Cylindrical polymer nut, Polymer (Iglidur®) - 1 thread


LAT2

2A motorised linear actuator, 2 amperes


NDS14C

Angular connector, Universal angular connector


ZBconique

Machined plastic bevel gear, 1:1


EBH

Cap nut Hygienic Design®, With collar


ACLBDB

Closing mechanism for aluminium profile,


M0

Worm, Machined plastic (delrin)

Complementary products


GEC

Rubber latch clamp with strike plate, Lockable


GE

Toggle latches, Miniature


GE14

Toggle latches, With padlock-holder


GE32

Sprung toggle latch with connecting link, Standard