

Conveyor wheel



GAL22



Zinc plated steel


- **Load capacity:** 200N static, 200N dynamic
- Single row ball bearing
- **Materials:**
 - roller: zinc plated steel
 - bearings: steel balls on zinc plated steel hub
- **Maximum conveyor speed:** 0.3m/s
- **Working temp range:** -30°C à +40°C

Info.

- **Not sold individually, please contact us for details**

Advantages

- Smooth rotation
- Treated steel hub for long life expectancy.



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Static load (N)	Dynamic load (N)	Stock*	Price each 1 to 49
GAL22-01	200	200	✓	4.07 €

*Depending on availability - Dimensions in mm

Plastic



GAL21




- **Load capacity:** 150N static, 150N dynamic
- Double row ball bearing
- Colour: black
- Materials:
roller: black polypropylene
bearings: steel balls on hub
- Maximum conveyor speed: 0.3m/s
- Working temp range: 0°C ÷ +40°C

Info.

- Not sold individually, please contact us for details

Advantages

- Shock resistant
- Low noise bearing



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Static load (N)	Dynamic load (N)	Weight (g)	Stock*	Price each 1 to 49
GAL21-64	150	150	27	✓	5,47 €

*Depending on availability - Dimensions in mm