Flexible toggle latche

GE1006

Slot fastening

- **Hook fastening**
- Ring is slightly flexible
- Material:
  White zinc steel or stainless steel 303

Steel or stainless steel





Assembly


- Approx mounting dimension:
  X = 56.6mm to withstand a tension of 400N

Info.

- **Not sold individually, please contact us for details**







DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request


Part number	Wire Ø	Lever thickness	Back-plate thickness	Max. Tension (N)	Weight (g)	Stock*	Price each 1 to 50
Steel							
GE1006-ZB	2,7	15/10th	20/10th	550	25	✔	2,00 €
Stainless steel							
GE1006-SS	2,5	15/10th	20/10th	550	24	✔	9,58 €

Subject to availability - Dimensions in mm

Standard and miniature versions

GE5
GE18

- **Hook *fastening***
- *Material:*
  White zinc steel or stainless steel 303



Assembly

- **GE5-ZB** *and* **GE5-SS** *are used with* **AC121-ZB** *and* **AC121-SS** *hooks, dimension X = 77.5mm to withstand a tension up to 350N*
- **GE18-ZB** *and* **GE18-SS** *are used with* **AC118-ZB** *and* **AC118-SS** *hooks, dimension X = 31.1mm to withstand a tension up to 150N*
- *Dimension X taken on the first hole of the hook.*

Advantages

- *Very flexible*


steel or stainless steel


Info.

- ***Not sold individually, please contact us for details***

Accessories

- Hooks **AC121, AC118** *(tome 1 p.174)*





DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	Material	wireØ	Lever thickness mm	Back-plate thickness	Max tension (N)	Weight (g)	Stock*	Price each 1 to 50
Standard								
GE5-ZB	steel	2,0	20/10th	20/10th	500	36,0	✔	3,64 €
GE5-SS	stainless steel	2,0	20/10th	20/10th	500	36,0	✔	7,35 €
Miniature								
GE18-ZB	steel	1,5	8/10th	10/10th	300	6,5	✔	2,15 €
GE18-SS	stainless steel	1,5	8/10th	10/10th	300	6,5	✔	3,47 €

**Subject to availability - Dimensions in mm*


Flexible toggle latche

With padlock-holder

Stock Sta Ste

GE14

- ***Hook fastening***
- *Material:*
  White zinc steel



Assembly

- **GE14-ZB** *is used with* **AC101-ZB** *hook, dimension X = 53.9mm to withstand a tension up to 350N*
- *Dimension X taken on the first hole of the hook.*

Advantages


- *Flexible positioning*
- *Can be operated many times without loss of clamping force*
- *Extended tolerance on positioning*


Info.

- ***Not sold individually, please contact us for details***

Accessory

- *Hooks* **AC101** **(tome 1 p.173)**





DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	Wire Ø	Lever thickness	Back-plate thickness	Max. tension (N)	Weight (g)	Stock*	Price each 1 to 50
With padlock-holder							
GE14-ZB	2,5	15/10th	2mm	500	21,9	✔	3,84 €

**Subject to availability - Dimensions in mm*

Hook for latch

Widths: 12, 13, 18 and 20mm

ACZB
ACSS

- **Hook fastening**
- Material:
  White zinc steel or stainless steel 303




Selection


- Choose your own hook/latch combination by simply verifying the interior width of the ring and selecting a hook with a smaller width

Info.


- **Not sold individually, please contact us for details**




AC122



AC103-ZB



AC118



AC121

DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	Suitable for latch	Weight (g)	Stock*	Price each 1 to 50
Steel				
AC103-ZB	-	3,4	-	0,30 €
AC118-ZB	GE18-ZB	1,5	✔	0,22 €
AC121-ZB	GE5-ZB	9,4	✔	0,49 €
AC122-ZB	GP22-ZB and GP23-ZB	1,9	✔	0,93 €
Stainless steel				
AC118-SS	GE18-SS	1,5	✔	0,45 €
AC121-SS	GE5-SS	9,4	✔	1,33 €
AC122-SS	GP22-SS and GP23-SS	1,9	✔	2,60 €

*Subject to availability - Dimensions in mm

Hook for latch

Stock Sta Ste

ACZB
ACSS

15mm wide versions

- **Hook fastening**
- Material:
  White zinc steel or stainless steel 303

Selection


- Choose your own hook/latch combination by simply verifying the interior width of the ring and selecting a hook with a smaller width

Info.


- **Not sold individually, please contact us for details**

steel or stainless steel







AC101



AC106-ZB



AC109-ZB



AC111-ZB

DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request


Part number	Suitable for latch	Weight (g)	Stock*	Price each 1 to 50
Steel				
AC101-ZB	GE14-ZB	4,7	✔	0,68 €
AC106-ZB	GE14-ZB	5,2	✔	1,08 €
AC109-ZB	GE14-ZB	6,2	✔	0,93 €
AC111-ZB	GE14-ZB	6,8	✔	1,44 €
Stainless steel				
AC101-SS	GE1006-SS	4,7	✔	0,68 €

*Subject to availability - Dimensions in mm

Recommended in case of vibration

GP22
GP23

- **Wide positioning tolerances**
- Very adaptable
- Suitable for vibrations
- Materials:
  White zinc steel or stainless steel 303



Assembly


- When used with **AC122** hook, dimension X= 87mm to withstand a tension of 350N
- Dimension X taken on the first hole of the hook.

Info

- **Not sold individually, please contact us for details**

Accessory

- Hooks **AC122** **(tome 1 p.174)**



DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	Material	Wire Ø	Lever thickness	Back-plate thickness	Max. tension (N)	Weight (g)	Stock*	Price each 1 to 50
With padlock holder								
GP22-ZB	Steel	1,7	20/10th	25/10th	450	75	✔	8,59 €
GP22-SS	Stainless steel	2,7	20/10th	25/10th	450	75	✔	17,71 €
Without padlock holder								
GP23-ZB	Steel	2,5	20/10th	25/10th	450	75	✔	8,83 €
GP23-SS	Stainless steel	3,5	20/10th	25/10th	450	75	✔	18,23 €

**Subject to availability - Dimensions in mm*

Sprung toggle latch with connecting link

Sta Ste

GP75 Recommended in case of vibration

- ***High retaining strength for a spring latch***
- *Lever can be locked to the mounting bracket by retractable handle*
- *Easy operation of the release handle*
- *Can be locked*
- *Large spring range*
- *Wide positioning tolerance*
- *Suitable for vibrations*
- *Materials:*
  White zinc plated steel
  18/8 stainless steel, natural finish




Steel or stainless steel

Installation

- *Approximate mounting dimension: Using an AC144 catch plate, X = 82.5 mm for a tension of about 550N*
- *Dimension X taken on the first hole of the hook.*

Accessories

- **AC144-ZZB** *and* **AC144-SS** *catch plates* **(tome 1 p.177)**



DISCOUNTS

Qty	1+	51+	101+	250+	400+
Disc.	List	-10%	-15%	-20%	On request

Part number	Material	Wire Ø	Lever thickness	Mounting plate thickness	Max tension (N)	Weight (g)	Stock*	Price each 1 to 50
GP75-ZB	Steel	5,00	20/10th	20/10th	750	125	✔	12,31 €
GP75-SS	Stainless steel	5,00	20/10th	20/10th	750	125	✔	21,06 €

**Depending on availability - Dimensions in mm*

Sta Ste Flat catch plate for toggle latch

22mm wide version


AC144

- **Closed by latching**
- Materials:
  White zinc plated steel
  18/8 stainless steel, natural finish

Accessories

- **GP75-ZB** and **GP75-SS** toggle latches
  (tome 1 p.176)





DISCOUNTS

Qty	1+	51+	101+	250+	400+
Disc.	List	-10%	-15%	-20%	On request

Part number	Material	Suitable for latch	Weight (g)	Stock*	Price each 1 to 50
Flat					
AC144-ZB	Steel	GP75-ZB	35	✔	0,98 €
AC144-SS	Stainless steel	GP75-SS	35	✔	3,10 €

**Depending on availability - Dimensions in mm*

Rigid toggle latch

GE32 For bonnet closures with crushable seals

Sta Ste

- **Closed by latching**
- High strength
- Lever locks on the mounting bracket
- Can be locked
- "Ammunition box" style clasp
- Materials:
  White zinc plated steel
  18/8 stainless steel, natural finish

Steel or stainless steel





Installation

- Approximate mounting dimension: Using an AC157 catch plate, X = 94 mm for a tension of about 150daN (for the long version)
- Dimension X taken on the first hole of the hook.

Accessories

- **AC156-ZB**, **AC156-SS**, **AC157-ZB** and **AC157-SS** catch plates
  (tome 1 p.179





DISCOUNTS

Qty	1+	51+	101+	250+	400+
Disc.	List	-10%	-15%	-20%	On request

Part number	Material	Wire Ø	Lever thickness	Mounting plate thickness	Max tension (N)	Weight (g)	Stock*	Price each 1 to 50
GE32-ZB	Steel	5,00	20/10th	20/10th	2500	103	✔	3,17 €
GE32-SS	Stainless steel	5,00	20/10th	20/10th	2500	109	✔	13,02 €

*Depending on availability - Dimensions in mm

Catch plate for toggle latch

25.5mm wide version


AC156
AC157

- **Closed by latching**
- Materials:
  White zinc plated steel
  18/8 stainless steel, natural finish


Accessories

- **GE32-ZB** and **GE32-SS** toggle latches
  (tome 1 p.178)





AC156



AC157

DISCOUNTS

Qty	1+	51+	101+	250+	400+
Disc.	List	-10%	-15%	-20%	On request

Part number	Material	Suitable for latch	Weight (g)	Stock*	Price each 1 to 50
Right angled					
AC156-ZB	Steel	GE32-ZB	59	✔	1,24 €
AC156-SS	Stainless steel	GE32-SS	59	✔	4,67 €
Flat					
AC157-ZB	Steel	GE32-ZB	59	✔	1,01 €
AC157-SS	Stainless steel	GE32-SS	59	✔	4,67 €

**Depending on availability - Dimensions in mm*