

Recommended in absence of seal

GP22
GP23

- Wide positioning tolerances
- Very adaptable
- Suitable for vibrations
- Materials:
White zinc steel or stainless steel 303

Assembly



- When used with AC122 hook, dimension X= 87mm to withstand a tension of 350N
- Dimension X taken on the first hole of the hook.

Info

- Not sold individually, please contact us for details

Accessory

- Hooks AC122 (t.imagetome1 p.125)



DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	Material	Wire Ø	Lever thickness	Back-plate thickness	Max. tension (N)	Weight (g)	Stock*	Price each 1 to 50
With padlock holder								
GP22-ZB	Steel	1,7	20/10th	25/10th	450	75	✓	7,58 €
GP22-SS	Stainless steel	2,7	20/10th	25/10th	450	75	✓	15,64 €
Without padlock holder								
GP23-ZB	Steel	2,5	20/10th	25/10th	450	75	✓	7,80 €
GP23-SS	Stainless steel	3,5	20/10th	25/10th	450	75	✓	16,11 €

*Subject to availability - Dimensions in mm

Our other products



S20

Short housing for open linear bearing, Opened - slim



PCS62SS

Chain sprocket - Stainless steel, 15.875mm (DIN 08B-1)



BZY

Cylindrical elasto mount, Steel




AT5-BAR

AT type tooth bar stock, AT5



CHTRP

Single and dual output gearboxes, Up to 9,1 Nm



METEB

Self-lubricating blanks, Bronze BP25



GLT2-17

Telescopic drawer runners for groove mounting, Partial extension



VAB

Flanged nut for ball screw, For VAB ballscrew



WS16

Drylin® W rail, Rail



DB

Steel bevel gear, 2:1



BRI

Panel holder, Panel holder



SCR

Suction cup threaded insert, Adaptor for insert

Complementary products



AC

Strike for toggle latch, 12,13,18 and 20mm