
Hand brushes

GPL

Technical data




- Hand brushes are used for manual cleaning, scouring, dust removal, stripping, descaling, honing or deburring operations on cylindrical surfaces: inside tubes, bottles, pin holes, rivet holes, tapped holes, secant holes, etc.
- These brushes can be used in a wide range of industries: mechanical (machine tools, maintenance), food processing, pharmaceutical and medical.

In practice

- Scrub the walls of the element to be cleaned using a rotating and back-and-forth motion.

Advice

- To prevent the bristles of the brush from twisting, we recommend that you choose one that the diameter is 10 to 15% larger than the diameter of the hole you wish to clean.



It's the end of the brush that works, not the edge.
It needs room to stand up straight

Deburring and stripping stainless steel


GPLss


- ***Stainless steel deburring brushes***
- *Materials:*
  Twisted galvanised steel
  Stainless steel covering



Applications

- *Deburring of pin holes, rivet holes, tapped holes, intersecting holes*
- *Cleaning of hollow containers (tubes, bottles, holes)*
- *Cleaning of hard-to-reach areas*
- *Removing rust*
- *Cleaning*
- *Stripping*





Deburring a gear bore

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request


Part number	Brush diameter ØD	Brush length L1	Overall length L2	Stock*	Price each 1 to 9
GPL5-100/SS	5	100	300	✔	12,23 €
GPL8-100/SS	8	100	300	✔	10,46 €
GPL10-100/SS	10	100	300	✔	9,55 €
GPL12-100/SS	12	100	300	✔	9,55 €
GPL15-100/SS	15	100	300	✔	9,67 €
GPL20-100/SS	20	100	300	✔	10,70 €
GPL25-100/SS	25	100	300	✔	10,11 €

**Depending on availability - Dimensions in mm*

Steel brush


GPLAC — For deburring and stripping


- ***Deburring and cleaning brush for all materials***
- *Materials:*
  Twisted galvanised steel
  Galvanized steel twist
  Steel covering



Applications

- *Deburring of pin holes, rivet holes, tapped holes, intersecting holes*
- *Cleaning of hollow containers (tubes, bottles, holes)*
- *Cleaning of hard-to-reach areas*
- *Removing rust*
- *Cleaning*
- *Stripping*





Stripping of a pulley bore

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL5-100/AC	5	100	300	✔	12,42 €
GPL8-100/AC	8	100	300	-	8,07 €
GPL10-100/AC	10	100	300	✔	8,07 €
GPL12-100/AC	12	100	300	-	8,22 €
GPL15-100/AC	15	100	300	-	8,53 €
GPL20-100/AC	20	100	300	-	10,08 €
GPL25-100/AC	25	100	300	-	10,08 €

**Depending on availability - Dimensions in mm*

For deburring and stripping softer materials


GPLBR


- ***Deburring and stripping brushes for aluminium, bronze and brass***
- *Materials:*
  Twisted galvanised steel
  Brass covering




Applications

- *Deburring of pin holes, rivet holes, tapped holes, intersecting holes*
- *Cleaning of hollow containers (tubes, bottles, holes)*
- *Cleaning of hard-to-reach areas*
- *Removing rust*
- *Cleaning*
- *Stripping*







Deburring a trapezoidal nut

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL5-100/BR	5	100	300	✔	12,23 €
GPL8-100/BR	8	100	300	-	10,24 €
GPL10-100/BR	10	100	300	-	9,22 €
GPL12-100/BR	12	100	300	✔	9,28 €
GPL15-100/BR	15	100	300	✔	9,28 €
GPL20-100/BR	20	100	300	✔	9,84 €
GPL25-100/BR	25	100	300	✔	9,84 €


**Depending on availability - Dimensions in mm*

Nylon brush

GPLNY


For mechanical and soft cleaning


- ***Deburring brushes for soft materials***
- *Materials:*
  Twisted galvanised steel
  Nylon covered



Applications

- *Gentle cleaning of hollow containers (tubes, bottles, holes)*
- *Gentle cleaning of hard-to-reach areas*





Cleaning the cooling fins of a gearbox

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL4-100/NY	4	100	300	✔	7,76 €
GPL6-100/NY	6	100	300	✔	5,11 €
GPL8-100/NY	8	100	300	✔	5,14 €
GPL10-100/NY	10	100	300	✔	5,18 €
GPL12-100/NY	12	100	300	✔	5,21 €
GPL15-100/NY	15	100	300	✔	5,27 €
GPL20-100/NY	20	100	300	✔	5,32 €
GPL25-100/NY	25	100	300	✔	5,41 €
GPL30-100/NY	30	100	300	✔	5,59 €
GPL40-100/NY	40	100	300	✔	5,79 €

**Depending on availability - Dimensions in mm*

Hog bristle brush

Cleaning and removal of dust

GLPso

- ***Brushes for the cleaning and removal of dust***
- *Materials:*
  Twisted galvanised steel
  Hog bristle silk covering





Application

- *Cleaning of hollow containers (tubes, bottles, holes)*
- *Cleaning of hard-to-reach areas*

Advantage

- *Anti-static*





Cleaning of hard-to-reach areas

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL15-100/SO	15	80	300	✔	8,53 €
GPL20-100/SO	20	80	300	-	10,08 €
GPL25-100/SO	25	80	300	✔	8,99 €

**Depending on availability - Dimensions in mm*

Our other products



Mounting bracket for bonnet fastener, Hook



Threaded stud - DIN976A, Steel



Single housed bearing assembly, Bearing secured with circlips



Storage bin, 8mm



Closed polymer Drylin® R bearing, Drylin® R



Right angled gearbox, bored shafts, up to 30 Nm



RPP heavy duty timing belt, RPP5



Spring loaded toggle latch, With padlock-holder



Domino 80 adjustable slide, Slide DOMILINE 80



T type timing belt, T2.5 Steel cored polyurethane



Adjustable latch clamp with strike plate, Stroke from 82mm to 92mm



Clevis components, short version, Stainless steel - short range

Complementary products



Brush, stainless steel



Brush, brass



Brush, nylon



Brush, silk