




- Hand brushes are used for manual cleaning, scouring, dust removal, stripping, descaling, honing or deburring operations on cylindrical surfaces: inside tubes, bottles, pin holes, rivet holes, tapped holes, secant holes, etc.
- These brushes can be used in a wide range of industries: mechanical (machine tools, maintenance), food processing, pharmaceutical and medical.

### In practice

- Scrub the walls of the element to be cleaned using a rotating and back-and-forth motion.

### Advice

- To prevent the bristles of the brush from twisting, we recommend that you choose one that the diameter is 10 to 15% larger than the diameter of the hole you wish to clean.



It's the end of the brush that works, not the edge.  
It needs room to stand up straight

## Deburring and stripping stainless steel

GPLSS



**- Stainless steel deburring brushes**

**- Materials:**

- Twisted galvanised steel
- Stainless steel covering

### Applications

- Deburring of pin holes, rivet holes, tapped holes, intersecting holes
- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas
- Removing rust
- Cleaning
- Stripping



Deburring a gear bore

### DISCOUNTS

Qty	1+	10+	25+	50+
Disc. List		-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Overall length L2	Stock*	Price each 1 to 9
GPL5-100/SS	5	100	300	✓	12,23 €
GPL8-100/SS	8	100	300	✓	10,46 €
GPL10-100/SS	10	100	300	✓	9,55 €
GPL12-100/SS	12	100	300	✓	9,55 €
GPL15-100/SS	15	100	300	✓	9,67 €
GPL20-100/SS	20	100	300	✓	10,70 €
GPL25-100/SS	25	100	300	✓	10,11 €

\*Depending on availability - Dimensions in mm

### - Deburring and cleaning brush for all materials

#### - Materials:

Twisted galvanised steel



Galvanized steel twist

Steel covering



### Applications

- Deburring of pin holes, rivet holes, tapped holes, intersecting holes
- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas
- Removing rust
- Cleaning
- Stripping



Stripping of a pulley bore

### DISCOUNTS

Qty	1+	10+	25+	50+
Disc. List	-5%	-10%	On request	

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL5-100/AC	5	100	300	✓	12,42 €
GPL8-100/AC	8	100	300	-	8,07 €
GPL10-100/AC	10	100	300	✓	8,07 €
GPL12-100/AC	12	100	300	-	8,22 €
GPL15-100/AC	15	100	300	-	8,53 €
GPL20-100/AC	20	100	300	-	10,08 €
GPL25-100/AC	25	100	300	-	10,08 €

\*Depending on availability - Dimensions in mm

## For deburring and stripping softer materials

GPL<sub>BR</sub>

- **Deburring and stripping brushes for aluminium, bronze and brass**




- Materials:

Twisted galvanised steel

Brass covering

### Applications

- Deburring of pin holes, rivet holes, tapped holes, intersecting holes
- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas
- Removing rust
- Cleaning
- Stripping



Deburring a trapezoidal nut

### DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL5-100/BR	5	100	300	✓	12,23 €
GPL8-100/BR	8	100	300	-	10,24 €
GPL10-100/BR	10	100	300	-	9,22 €
GPL12-100/BR	12	100	300	✓	9,28 €
GPL15-100/BR	15	100	300	✓	9,28 €
GPL20-100/BR	20	100	300	✓	9,84 €
GPL25-100/BR	25	100	300	✓	9,84 €

\*Depending on availability - Dimensions in mm




### - Deburring brushes for soft materials

#### - Materials:

- Twisted galvanised steel
- Nylon covered

### Applications

- Gentle cleaning of hollow containers (tubes, bottles, holes)
- Gentle cleaning of hard-to-reach areas



Cleaning the cooling fins of a gearbox

### DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL4-100/NY	4	100	300	✓	7,76 €
GPL6-100/NY	6	100	300	✓	5,11 €
GPL8-100/NY	8	100	300	✓	5,14 €
GPL10-100/NY	10	100	300	✓	5,18 €
GPL12-100/NY	12	100	300	✓	5,21 €
GPL15-100/NY	15	100	300	✓	5,27 €
GPL20-100/NY	20	100	300	✓	5,32 €
GPL25-100/NY	25	100	300	✓	5,41 €
GPL30-100/NY	30	100	300	✓	5,59 €
GPL40-100/NY	40	100	300	✓	5,79 €

\*Depending on availability - Dimensions in mm

**- Brushes for the cleaning and removal of dust**

**- Materials:**




Twisted galvanised steel  
Hog bristle silk covering

**Application**

- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas

**Advantage**

- Anti-static



Cleaning of hard-to-reach areas

**DISCOUNTS**

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL15-100/SO	15	80	300	✓	8,53 €
GPL20-100/SO	20	80	300	-	10,08 €
GPL25-100/SO	25	80	300	✓	8,99 €

\*Depending on availability - Dimensions in mm

## Our other products



Locking bolt, with T handle




Chain link, Steel



Crossed helical gear  
crossed axis at 90°,  
Machined plastic  
(delrin)



Stainless steel  
indexing plunger,  
Stainless steel



Steel bevel gear, 1:1



Die cast zinc clamping  
lever - female, Zamak



Ball transfer unit in  
blue certified plastic,  
for foodstuff sector



Flat suction cup,  
silicon



Storage bin, 8mm



Rotex®, jaw coupling,  
Aluminium




Magnetic head screw,  
With rubber coating



Stainless steel bevel  
gear, 1,5:1 2:1 3:1


## Complementary products




Brush, steel



Brush, brass



Brush, nylon



Brush, silk