

Belt tensioner



GTC


For standard applications

- Belt tensioner for use with BTE tender arm or fixed TMR and TFR tensioners
- Integrated bearings
- Greased for life
- Materials :
Nut, screw and spacer : Galvanised steel
Roller : Polyamide
- Max working temp : 70°C

Accessories

- TMR and TFR rigid tensioner (tome 4 p.144, p.145)
- BTE tension arm (tome 4 p.142)

Good price/
quality ratio



Typical application : used with BTE tender arm



Typical application : used with TFR tensioner

DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-10%	On request

Part number	A	B	C	ØD	ØM	Max speed (rpm)	Weight (kg)	Arm ref	Stock*	Price each 1 to 3
GTC-2	35	3,0	51	30	M8	8000	0,08	BTE2	✓	27,65 €
GTC-3/4	45	6,0	67	40	M10	8000	0,17	BTE3-BTE4	✓	32,57 €
GTC-5	60	7,5	89	60	M12	6000	0,40	BTE5	✓	58,30 €
GTC-6	90	9,0	127	80	M20	5000	1,20	BTE6-BTE7	✓	99,12 €
GTC-7	135	7,0	169	90	M20	4500	1,70	BTE7	-	195,53 €

*Depending on availability - Dimensions in mm



Belt tensioner

For applications in hostile environments

GTCss

- Belt tensioner
 - Sealing caps not fitted
- Integrated bearings
- Max working temp : 70°C
- Materials :
 - Nut, screw and spacer : 304L stainless steel
 - Roller : Polyamide


Accessories

- TMR/SS et TFR/SS rigid tensioner (tome 4 p.144, p.145)
- BTE/SS tension arm (tome 4 p.143)



stainless steel

Corrosion resistant materials



DISCOUNTS

Qty	1+	3+	5+
Disc.	List -10%	On request	

Part number	A	B	C	ØD	E	ØM	Arm size	Max speed (rpm)	Stock*	Price each 1 to 2
GTC-2/SS	38	35	3	30	13	M8	BTE2	8000	✓	36,60 €
GTC-3/4/SS	51	45	6	40	16	M10	BTE3-BTE4	8000	✓	50,51 €
GTC-5/SS	67,5	60	7,5	60	21,5	M12	BTE5	6000	✓	103,16 €

*Depending on availability - Dimensions in mm