





- **HBM-X:** Adjustable support bush with eccentric mounting hole. By rotating the bush, any play between the guide wheel and the rail can be eliminated.
- **HBM:** Fixed bush with a concentric mounting hole. They should be mounted on the side carrying most of the load.



Info.

- * fits into the bore of the corresponding wheel
- ** assumes eccentric bush will be mounted in its central position thus allowing adjustment from +X to -X



HBM-X : Adjustable eccentric support bush

HBM: Fixed concentric bush

DISCOUNTS

Qty	1+	4+	8+
Disc.	List -10%	On request	

Part number	Steel	Stainless	H	ØK*	L	ØN	For ØM screw	X**	S	Weight (g)	Stock*	Price each 1 to 3	Steel	Stainless
Eccentric support bush														
HBM-1X	HBM-1X/SS		13,97	4,75	11,11	3,6	M3,5	0,30	6,30	5	✓	12,84 €	23,82 €	
-	HBM-1-M4/SS		13,8	4,76	12	4	M4	0,25	6,22	-	-			
HBM-2X	HBM-2X/SS		17,93	9,51	14,28	6,1	M6,0	0,60	7,13	11	✓	13,75 €	28,43 €	
HBM-3X	HBM-3X/SS		25,14	11,99	19,05	8,1	M8,0	1,06	9,52	26	✓	19,57 €	39,11 €	
HBM-4X	HBM-4X/SS		29,90	14,99	22,22	10,1	M10,0	1,52	11,09	45	✓	21,59 €	52,10 €	
Concentric support bush														
HBM-1	HBM-1/SS		13,97	4,75	11,11	3,6	M3,5	-	6,30	5	✓	7,02 €	11,92 €	
-	HBM-1-M4/SS		13,8	4,76	11,2	4	M4	-	6,22	-	-			
HBM-2	HBM-2/SS		17,93	9,51	14,28	6,1	M6,0	-	7,13	11	✓	7,87 €	15,60 €	
HBM-3	HBM-3/SS		25,14	11,99	19,05	8,1	M8,0	-	9,52	26	✓	12,10 €	22,47 €	
HBM-4	HBM-4/SS		29,90	14,99	22,22	10,1	10,0	-	11,09	45	✓	13,29 €	35,15 €	

*Depending on availability - Dimensions in mm

Our other products



PSG125HC

Skive hobbed spur gears - precision range, Case hardened steel 20NCD2



PARF110

Pressed steel base rigid foot, Swivelling Ø110



CABPVC

PVC covered galvanised steel cable, Galvanised steel with



PRF3232

Standard aluminium profile, 32 x 32 mm



CHAE3030PA

Square decorative screwed hinges, Polyamide



BOXKK

Boxed set of DIN6885A keys, Boxed set - Steel or stainless steel




BIMSS

Indexing plunger mini, miniature - Stainless steel



SH0

Parallel axis helical gear, Steel 20NCD2




KITdog

24V DC motorisation kit, Worm and wheel



ADSR

Backlash free coupling Gerwah®,



SVG

Adjustable latch clamp with strike



BSPM

Miniature ballscrew, Nut+rolled ballscrew

Complementary products



HW_HT

Half-rail guide, Wheel



HW_HT

Half-rail guide, Rail



HW_HT

Half-rail guide, Wheel